

TECHNICAL DATA SHEET

Description: MHF4 – RP SMA Female

Jumper Cable

PART NUMBER: W9037BDXXXX





Features:

- Cable length: See Page 2
- Cable OD 0.81mm
- Connector 1: RP SMA Female
- Connector 2: I-PEX MHF4 or equivalent
- Attenuation 1dB @ 1GHz
- Attenuation 3.5dB @ 6GHz
- RoHS Compliant

Applications:

Jumper Cable

All dimensions are in mm / inches

Issue: 1901

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



TECHNICAL DATA SHEET

Description: MHF4 – RP SMA Female

Jumper Cable

PART NUMBER: W9037BDXXXX

ELECTRICAL SPECIFICATIONS

Frequency $0~8 \, \mathrm{GHz}$ Nominal Impedance $50\pm2~\Omega$ RL of Port-SMA $-12 \, \mathrm{dB}(\mathrm{Max})$ RL of Port-MHF4 $-12 \, \mathrm{dB}(\mathrm{Max})$ Max operating voltage(V) 1000

	Overall Attenuation/dB						
Frequency	W9037BD0100	W9037BD0200	W9037BD0250				
0.1MHz	0.05	0.06	0.07				
1G	0.45	0.75	0.89				
2G	0.63	1.06	1.27				
3G	0.79	1.33	1.58				
4G	0.95	1.58	1.88				
5G	1.08	1.81	2.15				
6G	1.34	2.11	2.45				
7G	1.57	2.42	2.90				
8G	1.91	2.77	3.15				

MECHANICAL SPECIFICATIONS

	Connector Type	Cable Tpye	Overall Length(m m/in)	Cable Length(m m/in)	Weight(g)	Color
W9037BD0100		Ф0.81 MM Coaxial Cable, Black	116/4.57	100/3.94	3	Black
W9037BD0200	I-PEX MHF4 or equivalent + RP SMA Female with Spring Washer		216/8.50	200/7.87	3.3	
W9037BD0250	mur opinig riadile.		266/10.47	250/9.84	3.5	

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature -40~85° C
Storage Temperature -40~85° C
RoHS Compliant Yes

Issue: 1901

ROHS




TECHNICAL DATA SHEET

Description: MHF4 – RP SMA Female Jumper Cable

PART NUMBER: W9037BDXXXX

MECHANICAL DRAWING







TECHNICAL DATA SHEET

Description: MHF4 – RP SMA Female


Jumper Cable

PART NUMBER: W9037BDXXXX

CHARTS

Attenuation of the W9037 vs Frequency

W9037/Attenuation







TECHNICAL DATA SHEET

Description: MHF4 – RP SMA Female


Jumper Cable

PART NUMBER: W9037BDXXXX

CHARTS

Return Loss of Port-SMA vs Frequency

W9037/Port-SMA









TECHNICAL DATA SHEET

Description: MHF4 – RP SMA Female


Jumper Cable

PART NUMBER: W9037BDXXXX

CHARTS

Return Loss of Port-MHF4 vs Frequency

W9037/Port-MHF4







TECHNICAL DATA SHEET

Description: MHF4 – RP SMA Female

Jumper Cable

PART NUMBER: W9037BDXXXX

PACKAGING

Quantity: 20 PCS / Column PE bag, 2000 pcs / Box





TECHNICAL DATA SHEET

Description: MHF4 – RP SMA Female


Jumper Cable

PART NUMBER: W9037BDXXXX


ASSEMBLY

The RP-SMA male connector fits through the assembly hole, the hole size is below. SMA connector thread length: 11mm / 0.43in

Panel cut-out



Option 1



Option 2