

Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of CSTLS8M00G53Z-A0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=CSTLS8M00G53Z-A0

CSTLS8M00G53Z-A0












Appearance & Shape







Applications

Other Usage	Consumer/Industrial
-------------	---------------------



Packaging Information

Packaging		Standard Packing Quantity
A0	Ammo Pack	2000



Features

MURATA's ceramic resonator, CERALOCK(R) with built-in load capacitors, has been widely applied as the most suitable component for clock oscillators in a broad range of microprocessors. The CSTLS series can be used in the design of oscillation circuits not requiring external load capacitors, enabling both high-density mounting and cost reduction.

Features

- 1. Oscillation circuits do not require external load capacitors. There is some variation in built-in capacitance values applicable to
- 2. Stable over a wide temperature range.
- 3. Compact, lightweight and exhibit superior shock resistance performance.
- 4. Enable the design of oscillator circuits requiring no adjustment.
- 5. Cost-effective and reliable availability.

1 of 2

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





Note: This datasheet may be out of date. ${\it Please download the latest datasheet of CSTLS8M00G53Z-A0 from the official website of Murata}$ Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=CSTLS8M00G53Z-A0

CSTLS8M00G53Z-A0



Specifications

	I
Product Type	Ceramic Resonator
Product Type	(CERALOCK)
Series	CSTLS_G
Frequency	8.000MHz
Frequency Tolerance	+/-0.50% max.
Operating Temperature	-40°C~125°C
Range	-40 C~125 C
Frequency Shift by	0.404
Temperature	-0.40 to +0.20%
Frequency Aging	+/-0.20% max.
Resonant Impedance (R1)	25ohm max.
Built-in Load Capacitance	45.5
(CL1/CL2)	15pF
Shape	Lead
Wash	Not available
L x W (size)	9.0x6.0mm
Mass	126mg

2 of 2

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

