BENEFITS OF USING CAPACITOR ARRAYS

KYOCERA AVX capacitor arrays offer designers the opportunity to lower placement costs, increase assembly line output through lower component count per board and to reduce real estate requirements.

Reduced Costs

Placement costs are greatly reduced by effectively placing one device instead of four or two. This results in increased throughput and translates into savings on machine time. Inventory levels are lowered and further savings are made on solder materials, etc.

Space Saving

Space savings can be quite dramatic when compared to the use of discrete chip capacitors. As an example, the 0508 4-element array offers a space reduction of >40% vs. 4 x 0402 discrete capacitors and of >70% vs. 4 x 0603 discrete capacitors. (This calculation is dependent on the spacing of the discrete components.)

Increased Throughput

Assuming that there are 220 passive components placed in a mobile phone:

A reduction in the passive count to 200 (by replacing discrete components with arrays) results in an increase in throughput of approximately 9%.

A reduction of 40 placements increases throughput by 18%.


For high volume users of cap arrays using the very latest placement equipment capable of placing 10 components per second, the increase in throughput can be very significant and can have the overall effect of reducing the number of placement machines required to mount components:

KYOCERa

If 120 million 2-element arrays or 40 million 4-element arrays were placed in a year, the requirement for placement equipment would be reduced by one machine.

During a 20Hr operational day a machine places 720K components. Over a working year of 167 days the machine can place approximately 120 million. If 2-element arrays are mounted instead of discrete components, then the number of placements is reduced by a factor of two and in the scenario where 120 million 2-element arrays are placed there is a saving of one pick and place machine.


Smaller volume users can also benefit from replacing discrete components with arrays. The total number of placements is reduced thus creating spare capacity on placement machines. This in turn generates the opportunity to increase overall production output without further investment in new equipment.



W2A (0508) Capacitor Arrays

The 0508 4-element capacitor array gives a PCB space saving of over 40% vs four 0402 discretes and over 70% vs four 0603 discrete capacitors.


W3A (0612) Capacitor Arrays



The 0612 4-element capacitor array gives a PCB space saving of over 50% vs four 0603 discretes and over 70% vs four 0805 discrete capacitors.

KINCLERA The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.






GENERAL DESCRIPTION


KYOCERA AVX is the market leader in the development and manufacture of capacitor arrays. The array family of products also includes the 0612 4-element device as well as 0508 2-element and 4-element series, all of which have received widespread acceptance in the marketplace.

KYOCERA AVX capacitor arrays are available in X5R, X7R and NP0 (C0G) ceramic dielectrics to cover a broad range of capacitance values. Voltage ratings from 6.3 Volts up to 100 Volts are offered. KYOCERA AVX also now offers a range of automotive capacitor arrays qualified to AEC-Q200 (see separate table).

Key markets for capacitor arrays are Mobile and Cordless Phones, Digital Set Top Boxes, Computer Motherboards and Peripherals as well as Automotive applications, RF Modems, Networking Products, etc.



HOW TO ORDER



KYDECERA The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

020922



SIZE	W	/2 = 05	08	W3 = 0612		2
# Elements		4		4		
Soldering	Re	eflow/Wa	ave	Reflow/Wave		ve
Packaging		per/Embo			er/Embos	
mm	1	1.30 ± 0.1	5		60 ± 0.15	
Length (in.) (0	.051 ± 0.0	06)	(0.0	063 ± 0.00)6)
Width mn		2.10 ± 0.1 .083 ± 0.0			.20 ± 0.20 126 ± 0.00	
Max. mm		0.94	00)	(0.	1.35	,0)
Thickness (in.		(0.037)			(0.053)	
WVDC	16	25	50	16	25	50
	.0					
	.2					
	.5					
	.8 .2					
	.2 .7					
	.7 .3					
	.9					
	.7					
5R6 5	.6					
	.8					
	.2					
	10					
-	12					
	15					
	18 22					
	22					
-	33					
	39					
	47					
560	56					
	58					
820	32					
	00					
	20					
	50					
	30					
	20 70					
	30	+				
	90					
	70					
	50	1	İ			
681 6	30					
	20					
102 10]
122 12						
152 150	_		ļ			
182 18						
222 22 272 27						
332 33		+				
392 39						
472 47						
562 560	_	1				
682 68						
822 82	00					



= Supported Values

The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

Capacitor Array Capacitance Range – X7R



	0175	1		NO -	050	0		r –		10 -	050	0				12 -	061	<u> </u>	
	SIZE				<u>050</u> 2	0			V		<u>050</u> 4	0			V	<u>N3 =</u>		۷	
#	Elements Soldering				∠ v/Wav	0					/Wave					Reflow			
	Packaging				Paper	<u> </u>					mboss					per/Er			
Lengt	mm			1.30	± 0.15					1.30 :	± 0.15					1.60 ±	0.150		
Lengt	(IN.)		(± 0.00						± 0.00	6)			(0).063 ±		5)	
Width	mm (in)				± 0.15						± 0.15	6)			(3.20 ±		2)	
Max.	(in.) 		(<u>± 0.00</u> .94	(0)			(0		± 0.00 94	0)			(().126 ±	<u>5 0.00</u> 35	5)	
Thick					037))37)					(0.0			
	WVDC	6	10	16	25	50	100	6	10	16	25	50	100	6	10	16	25	50	100
101	Cap 100																		
121 151	(PF) 120 150																		
181	130																		
221	220																		
271	270																		
331	330																		
391 471	390 470																		
561	560																		
681	680																		
821	820																		
102 122	1000 1200																		
152	1200																		
182	1800																		
222	2200																		
272	2700 3300						<u> </u>	<u> </u>				<u> </u>	<u> </u>						
332 392	3300																		
472	4700																		
562	5600																		
682	6800																		
822	8200 Cap 0.010						<u> </u>	<u> </u>				<u> </u>	<u> </u>						
123	(μF) 0.012																		
153	0.015																		
183	0.018																		
223	0.022																		
273	0.027																		
393	0.039																		
473	0.047																		
563	0.056																		
683 823	0.068 0.082																		
104	0.082																		
124	0.12																		
154	0.15						<u> </u>					<u> </u>	<u> </u>						
184 224	0.18 0.22																		
274	0.22																		
334	0.33																		
474	0.47																		
564 684	0.56																		
824	0.82																		
105	1.0																		
125	1.2																		
155	1.5																		
185 225	<u>1.8</u> 2.2																		
335	3.3																		
475	4.7																		
106	10																		
226 476	22 47																		
476	47																		
107	100	1	L	L		1	11					L	L			I			

The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

Capacitor Array Automotive Capacitor Array (IPC)







As the market leader in the development and manufacture of capacitor arrays KYOCERA AVX is pleased to offer a range of AEC-Q200 qualified arrays to compliment our product offering to the Automotive industry. Both the KYOCERA AVX 0612 and 0508 4-element capacitor array styles are qualified to the AEC-Q200 automotive specifications.

AEC-Q200 is the Automotive Industry qualification standard and a detailed qualification package is available on request. All KYOCERA AVX automotive capacitor array production facilities are certified to ISO/TS 16949:2002.


HOW TO ORDER



*Contact factory for availability by part number for K = ±10% and J = ±5% tolerance.



ANA



*Not RoHS Compliant




For RoHS compliant products

 Please select correct termination style.
AVAC
Online at www.kvocera-avy.com/disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

020822



PART & PAD LAYOUT DIMENSIONS



PART DIMENSIONS

0508 - 2 Element

L	W	Т	BW	BL	Р	S
1.30 ± 0.15	2.10 ± 0.15	0.94 MAX	0.43 ± 0.10	0.33 ± 0.08	1.00 REF	0.50 ± 0.10
(0.051 ± 0.006)	(0.083 ± 0.006)	(0.037 MAX)	(0.017±0.004)	(0.013 ± 0.003)	(0.039 REF)	(0.020 ± 0.004)

0508 - 4 Element

L	W	Т	BW	BL	Р	Х	S
1.30 ± 0.15	2.10 ± 0.15	0.94 MAX	0.25 ± 0.06	0.20 ± 0.08	0.50 REF	0.75 ± 0.10	0.25 ± 0.10
(0.051 ± 0.006)	(0.083 ± 0.006)	(0.037 MAX)	(0.010 ± 0.003)	(0.008 ± 0.003)	(0.020 REF)	(0.030 ± 0.004)	(0.010 ± 0.004)

0612 - 4 Element

L	w	т	BW	BL	Р	Х	S
1.60 ± 0.20	3.20 ± 0.20	1.35 MAX	0.41 ± 0.10		0.76 REF	1.14 ± 0.10	0.38 ± 0.10
(0.063 ± 0.008)	(0.126 ± 0.008)	(0.053 MAX)	(0.016 ± 0.004)	(0.007+0.010) -0.003	(0.030 REF)	(0.045±0.004)	(0.015±0.004)

PAD LAYOUT DIMENSIONS

0508 - 2 Element

Α	В	С	D	E
0.68	1.32	2.00	0.46	1.00
(0.027)	(0.052)	(0.079)	(0.018)	(0.039)

0508 - 4 Element	0508 -	4 Element
------------------	--------	-----------

Α	В	C	D	E
0.56	1.32	1.88	0.30	0.50
(0.022)	(0.052)	(0.074)	(0.012)	(0.020)

0612 - 4 Element

Α	В	С	D	E
0.89	1.65	2.54	0.46	0.76
(0.035)	(0.065)	(0.100)	(0.018)	(0.030)

KUCERE The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.