


4 A - Triac in DPAK package



DPAK

Product status link

Z0410MB

Product summary			
I _{T(RMS)} 4 A			
V _{DSM} /V _{RSM}	750 V		
I _{GT}	25 mA		
T _j max.	125 °C		

Features

- 4 A Triac
- $V_{DRM} / V_{RRM} = 600 \text{ V}$ and $V_{DSM} / V_{RSM} = 750 \text{ V}$
- 125 °C maximum junction temperature T_j
- DPAK package
- 4 quadrants triacs with I_{GT} = 25 mA
- · Halogen-free molding, lead-free plating
- ECOPACK2 compliant

Applications

- Actuators
- Heating elements
- Inrush current limiting circuits

Description

The Z0410MB series is 4 A Triac housed in compact SMD DPAK. This 4 quadrants device is suited to home appliances or power tools and industrial systems and drives loads up to 4 A.



1 Characteristics

Table 1. Absolute maximum ratings (limiting values)

Symbol	Parameter	Value	Unit		
I _{T(RMS)}	RMS on-state current (full sine wave)	T _c = 107 °C	4	Α	
I	Non repetitive surge peak on-state current (full cycle,	t = 16.7 ms	16	٨	
I _{TSM}	T _j initial = 25 °C)	t = 20 ms	15	Α	
l ² t	I ² t value for fusing	t _p = 10 ms	1.5	A ² s	
dl/dt	Critical rate of rise of on-state current, $I_G = 2 \times I_{GT}$, tr $I_G = 125 ^{\circ}\text{C}$ C $I_G = 120 \text{Hz}$		50	A/µs	
V _{DRM} /V _{RRM}	Repetitive peak off-state voltage T _j = 125 °C		600	V	
V _{DSM} /V _{RSM}	Non Repetitive peak off-state voltage, 10 ms	750	V		
I _{GM}	Maximum peak gate current t_{p} = 20 μ s, T_{i} = 125 °C		1.2	Α	
P _{GM}	Maximum gate power dissipation	0.5	W		
T _{stg}	Storage temperature range	-40 to +125	°C		
Tj	Operating junction temperature range	-40 to +125	°C		
TL	Maximum lead temperature for soldering during 10 s	260	°C		

Table 2. Electrical characteristics (T_j = 25 °C, unless otherwise specified)

Symbol	Test conditions	Value	Unit		
I _{GT} ⁽¹⁾	$V_D = 12 \text{ V}, R_L = 33 \Omega$		Max.	25	mA
V _{GT}	$V_D = 12 \text{ V}, R_L = 33 \Omega$		Max.	1.3	V
V _{GD}	$V_D = V_{DRM}$, $R_L = 3.3 \text{ k}\Omega$ $T_j = 125 \text{ °C}$		Min.	0.2	V
IL	I _G = 1.2 x I _{GT}	I-III-IV	Max.	25	mA
'L	IG - 1.2 \ IG	II	Max.	50	mA
I _H ⁽²⁾	I _T = 500 mA, gate open		Max.	25	mA
dV/dt (2)	V_D = 67 % V_{DRM} ; V_R = 67 % V_{RRM} , gate open T_j = 110 °C		Min.	200	V/µs
(dV/dt)c (2)	$(dI/dt)c = 1.8 \text{ A/ms}$ $T_j = 110 ^{\circ}\text{C}$		Min.	5	V/µs

^{1.} For both polarities of OUT pin referenced to COM pin.

Table 3. Static characteristics

Symbol	Test conditions	Tj		Value	Unit
V _{TM} ⁽¹⁾	$I_{TM} = 5.5 \text{ A}, t_p = 380 \ \mu \text{s}$	25 °C	Max.	2	V
V _{TO} ⁽¹⁾	Threshold voltage	125 °C	Max.	0.95	V
R _D ⁽¹⁾	Dynamic resistance	125 °C	Max.	180	mΩ
I _{DRM} /I _{RRM}	$V_D = V_R = V_{DRM} = V_{RRM}$	25 °C	Max.	5	μΑ
		125°C		0.5	mA

^{1.} For both polarities of A2 referenced to A1.

DS14021 - Rev 1 page 2/11

^{2.} For both polarities of A2 referenced to A1.





Table 4. Thermal resistance

Symbol	Parameter	Value	Unit	
R _{th(j-c)}	Junction to case (AC)	3	°C/W	
$R_{th(j-a)}$	Junction to ambient: S _{CU} = 0.5 cm ²	Тур.	70	°C/W

DS14021 - Rev 1 page 3/11



1.1 Characteristics (curves)

Figure 1. Maximum power dissipation versus on-state RMS current (full cycle)




Figure 2. Average and DC on-state current versus case temperature




Figure 3. On-state RMS current versus ambient temperature (full cycle)




Figure 4. Relative variation of thermal impedance versus pulse duration




Figure 5. Relative variation of gate triggering current and voltage versus junction temperature (typical values)





Figure 6. Surge peak on-state current versus number of cycles



DS14021 - Rev 1 page 4/11



Figure 7. Non repetitive surge peak on-state current for a sinusoidal pulse with width $t_{\rm p}$ < 10 ms and corresponding value of l^2t




Figure 8. On-state characteristics (maximum values)




Figure 9. Relative variation of critical rate of decrease of main current versus (dV/dt)c (typical values)




Figure 10. Relative variation of critical rate of decrease of main current versus junction temperature




Figure 11. Relative variation of static dV/dt immunity versus junction temperature





Figure 12. Thermal resistance junction to ambient versus copper surface under tab (typical values)



DS14021 - Rev 1 page 5/11




Package information


In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.


2.1 DPAK package information


- Molding compouned resin is halogen free and meets UL94 flammability standard, level V0
- · Lead-free package leads plating


Figure 13. DPAK package outline











DS14021 - Rev 1 page 6/11

-



Table 5. DPAK package mechanical data

	Dimensions						
Ref.	Millimeters			Inches ⁽¹⁾			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	2.20	2.30	2.38	0.0866	0.0906	0.0937	
A1	0.90	1.01	1.10	0.0354	0.0398	0.0433	
A2	0.00		0.10	0.0000		0.0039	
b	0.72		0.85	0.0283		0.335	
b4	5.13	5.33	5.46	0.2020	0.2098	0.2150	
С	0.47		0.60	0.0185		0.0236	
c2	0.47		0.60	0.0185		0.0236	
D	6.00	6.10	6.20	0.2362	0.2402	0.2441	
D1	5.15	5.40	5.65	0.2028	0.2126	0.2224	
E	6.50	6.60	6.70	0.2550	0.2598	0.2638	
E1	4.70	4.85	5.00	0.1850	0.1909	0.1969	
е	2.186	2.286	2.386	0.0860	0.0900	0.0940	
Н	9.80	10.10	10.40	0.3858	0.3976	0.4094	
L	1.40	1.50	1.70	0.0551	0.0591	0.0669	
L1		2.90 REF			0.1142 REF		
L2	0.90		1.25	0.0354		0.0492	
L3		0.51 BSC			0.201 BSC		
L4	0.60	0.80	1.00	0.0236	0.0315	0.0394	
L6	1.80 BSC			0.0709 BSC			
Θ1	5°	7°	9°	5°	7°	9°	
Θ2	5°	7°	9°	5°	7°	9°	
V2	0°		8°	0°		8°	

^{1.} Dimensions in inches are given for reference only

Note:

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

DS14021 - Rev 1 page 7/11






Figure 14. DPAK recommended footprint (dimensions are in mm)

DS14021 - Rev 1 page 8/11



3 Ordering information

Figure 15. Ordering information scheme




Table 6. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
Z0410MB	Z0410MB	DPAK	0.3 g	2500	Tape and reel

DS14021 - Rev 1 page 9/11



Revision history

Table 7. Document revision history

Date	Revision	Changes
02-Sep-2022	1	Initial release.

DS14021 - Rev 1 page 10/11



IMPORTANT NOTICE - READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics - All rights reserved

DS14021 - Rev 1 page 11/11