Graphic Adapters DisplayPort to HDMI





RoHS Compliant

Description

DisplayPort to HDMI cable adapter for connecting a graphics card with DP to a monitor with HDMI connection - with a resolution of up to $1920 \times 1080 / 1920 \times 1200 @60$ Hz!

Features

- · Support Display Port 1.1 input and HDMI output.
- · Support HDMI highes: video resolution 1080p.
- Support HDMI 225MHz/2.25Gbps per channel (6.75Gbps all channel) bandwidth.
- Support HDMI 12bit per channel (36bit all channel) deep colour.
- · Powered from Display Port Source.

Specifications

Product type	DisplayPort-HDMI Adapter
Colour	Black
Length	0.15m
Max. resolution	1920 × 1080 / 1920 × 1200 @60Hz (2K, Full HD)
Side 1 connection (PC)	DisplayPort Male
Side 2 connection (Peripherals)	HDMI Female
Side 1 Connector Type	DisplayPort
Side 1 Connector Gender	Male
Side 2 Connector Type	HDMI Type A
Side 2 Connector Gender	Female
Active / Passive	Passive
Conversion direction	HDMI-VGA
Area of application	External
Dimensions (HxWxD)	14mm × 44mm × 44mm
Height	14mm
Width	44mm
Depth	44mm
Weight	35.6g
Height of packaging (single piece)	10mm
Width of packaging (single piece)	40mm
Depth of packaging (single piece)	180mm
Package weight (single piece)	0.039kg


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Graphic Adapters DisplayPort to HDMI


multicomp PRO

Diagram



Dimensions: Millimetres

PIN Assignment



No	Specification Description	Q'ty	Unit
1	Display Port cable UL20276 [32AWG(7/0.08TC) \times 1P+D+AL+Mylar) \times 5+32AWG(7/0.08TC) \times 5C+AL/MY+D.W+BD+Jocket colour PMS: Black OD: 5 \pm 0.2mm	0.2	m
2	Display Port Male Pin Gold, Insulation Black, Shell Nickel Plated	1	set
3	Display Port to HDMI PCB+SMT	1	set
4	Inside Molding: PE	1	set
5	Outside Molding 45P PVC PMS: Black	20	g
6	6 Plastic Hood for HDMI Female, Material: ABS, Colour: Black		Set

Part Number Table

Description	Part Number	
Graphic Adapter, DisplayPort Male to HDMI Female, Black, 0.2m	MP010454	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

