



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Cannot be Certified**

Power Technology Type: **Manual**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	SDE Crimp Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233)



Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-AM705-T273 AMP MCP, RECEPTACLE AND TAB	 TE Part # 2063524-1 SDE MCP1.5 0.2-1.0mm2 ASSY	 TE Part # 1241375-1 AMP MCP 1.5K, CONTACT, (LP)	 TE Part # 1241381-1 AMP MCP 1.5K, CONTACT, SWS, (LP)
 TE Part # 1241381-3 AMP MCP 1.5K, CONTACT, SWS, (LP)	 TE Part # 1241381-2 AMP MCP 1.5K, CONTACT, SWS, (LP)	 TE Part # 1241375-2 AMP MCP 1.5K, CONTACT, (LP)	 TE Part # 1241375-3 AMP MCP 1.5K, CONTACT, (LP)
 TE Part # 1241377-1 AMP MCP1.5K,CONTACT,(LP)	 TE Part # 2362810-1 SDE CRIMP HAND TOOL FRAME W /O DIES	 TE Part # 6-1241374-1 MCP1.5 SOCKET CONTACT	 TE Part # 6-1241374-2 MCP1.5 BU-KONTAKT


Customers Also Bought



TE Part #480054-5
FF 250 REC HSG 1P NYLON RED



TE Part #1-644752-6
16P MTA156 HDR ASSY SQ STR F/L



TE Part #2063409-1
SDE MICROTIMER 0.2-1.0mm2 ASSY




TE Part #2063524-1
SDE MCP1.5 0.2-1.0mm2 ASSY




TE Part #AS014-35SC
RECEPT.2 HOLE MNT.TYPE 0



TE Part #AS608-35SA
PLUG BOOT TERMIN'N TYPE 6



TE Part #539950-2
ERGO DIE MCP 1,5 K



TE Part #539955-2
ERGO DIE MCP 4,8K E



TE Part #519609-1
ZANGE

Documents

Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English