

Low Pressure Sensor Amplified Analog Output

SM6295-BCM-S-040-000



FEATURES

- Pressure range from 0 to 40 cmH₂O
- 5.0V operation
- Amplified analog output (10 to 90%V_{dd})
- Compensated temperature range: 0 to 60°C
- Gage pressure configuration
- Insensitive to mounting orientation
- Pressurized from backside to protect topside electronics

DESCRIPTION

The SM6295-BCM-S-040-000 is an amplified analog, low pressure MEMS sensor offering state-of-the-art pressure transducer technology and CMOS mixed signal processing technology to produce an analog, fully conditioned, pressure and temperature compensated sensor in a JEDEC standard SOIC-16 package with dual vertical porting. It is available in a gage pressure configuration.

Combining the pressure sensor with a signal-conditioning ASIC in a single package simplifies the use of advanced silicon micro-machined pressure sensors. The pressure sensor can be mounted directly on a standard printed circuit board and a high level, calibrated pressure signal can be acquired from the analog output. This eliminates the need for additional circuitry, such as a compensation network or microcontroller containing a custom correction algorithm.

The SM6295-BCM-S-040-000 is shipped in sticks. The SM6295-BCM-T-040-000 is shipped in tape & reel.

Medical	Industrial	Consumer
CPAP	Airflow Measurement	Sports Equipment
Ventilators	Pneumatic Gauges	Appliances
Gas Flow Instrumentation	Pressure Switches	
Air Flow Monitors	Life Sciences	
	Gas Flow Instrumentation	

Absolute Maximum Ratings

All parameters are specified at V_{DD} = 5.0 V supply voltage at 25°C, unless otherwise noted.

No.	Characteristic	Symbol	Minimum	Typical	Maximum	Units
1	Supply Voltage	V _{DD}	0.0		6.0	V
2	Operating Temperature	T _{OP}	-20		+85	°C
3	Storage Temperature	T _{STG}	-40	-	+125	°C

No.	Product Number	Operating Pressure	Proof Pressure (P _{PROOF}) ^(a, b)	Burst Pressure (P _{BURST}) ^(a, c)
5	SM6295-BCM-T-040-000 ^(d) SM6295-BCM-S-040-000 ^(e)	40 cmH ₂ O	±4.8 PSI	±6.0 PSI

Notes:


- a. Tested on a sample basis.
- b. Proof pressure is defined as the maximum pressure to which the device can be taken and still perform within specifications after returning to the operating pressure range
- c. Burst pressure is the pressure at which the device suffers catastrophic failure resulting in pressure loss through the device.
- d. Shipped in Tape & Reel
- e. Shipped in sticks

No.	Characteristic	Symbol	Minimum	Typical	Maximum	Units
6	Supply Voltage	V _{DD}	4.75	5.0	5.25	V
7	Supply Current	I _{VDD}		4.5		mA
8	Zero Offset Voltage	V _{ZERO}		10		%VDD
9	Full Scale Output	FSO		90		
10	Full Scale Span	FS		80		
11	Compensated Temperature Range	T _{COMP}	0		+60	°C
12	Accuracy ^(f)	ACC	-2.5		+2.5	%FS

Notes:

- f. The accuracy specification applies over the compensated temperature range. This specification includes the combination of linearity, repeatability, and hysteresis errors over pressure and temperature .



SOIC-16 (C) Vertical Package Dimensions




Notes:

- All dimensions in units of [mm]
- Moisture Sensitivity Level (MSL): Level 3
- Wetted materials: Silicon, glass, copper, silicone, epoxy, mold compound.
- Tolerance on all dimensions ± 0.13 mm unless otherwise specified.
- [B] is tube connected to bottom side of sensor die.
- [T] is tube connected to top side of sensor die.
- An increase in bottom pressure will result in an increase in sensor output

Part & Lot Number Identification



SM6295 Applications Circuit



Pin No.	Pin Function
1	NC
2	NC
3	NC
4	NC
5	NC
6	GND
7	NC
8	NC
9	NC
10	Vout: Analog Output
11	VDD
12	NC (I ² C SCK)
13	NC (I ² C SDA)
14	NC
15	NC
16	NC


NOTES:

- Do not connect to NC pins
- Pins 12 and 13 can be used for I²C digital interface. They then need pull-up resistors to VDD (e.g. 4.7 kΩ). When using only the analog output, do not connect to these pins.

Ordering Information

Order Code	Part Marking	Minimum Pressure Range	Positive Pressure Range	Pressure Type	Port Configuration	Shipping Method
SM6295-BCM-T-040-000	95-007	0 cmH ₂ O	40 cmH ₂ O	Gage	Dual Vertical	Tape & Reel
SM6295-BCM-S-040-000	95-007	0 cmH ₂ O	40 cmH ₂ O	Gage	Dual Vertical	Sticks

Part Number Legend



Qualification Standards

REACH Compliant
 RoHS Compliant
 PFOS/PFOA Compliant
 For qualification specifications, please contact Sales at sales@si-micro.com



Silicon Microstructures Warranty and Disclaimer:

Silicon Microstructures, Inc. reserves the right to make changes without further notice to any products herein and to amend the contents of this data sheet at any time and at its sole discretion.

Information in this document is provided solely to enable software and system implementers to use Silicon Microstructures, Inc. products and/or services. No express or implied copyright licenses are granted hereunder to design or fabricate any silicon-based microstructures based on the information in this document.

Silicon Microstructures, Inc. makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does Silicon Microstructures, Inc. assume any liability arising out of the application or use of any product or silicon-based microstructure, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Silicon Microstructure's data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Silicon Microstructures, Inc. does not convey any license under its patent rights nor the rights of others. Silicon Microstructures, Inc. makes no representation that the circuits are free of patent infringement. Silicon Microstructures, Inc. products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Silicon Microstructures, Inc. product could create a situation where personal injury or death may occur. Should Buyer purchase or use Silicon Microstructures, Inc. products for any such unintended or unauthorized application, Buyer shall indemnify and hold Silicon Microstructures, Inc. and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Silicon Microstructures, Inc. was negligent regarding the design or manufacture of the part.

Silicon Microstructures, Inc. warrants goods of its manufacture as being free of defective materials and faulty workmanship. Silicon Microstructures, Inc. standard product warranty applies unless agreed to otherwise by Silicon Microstructures, Inc. in writing; please refer to your order acknowledgement or contact Silicon Microstructures, Inc. directly for specific warranty details. If warranted goods are returned to Silicon Microstructures, Inc. during the period of coverage, Silicon Microstructures, Inc. will repair or replace, at its option, without charge those items it finds defective. The foregoing is buyer's sole remedy and is in lieu of all warranties, expressed or implied, including those of merchantability and fitness for a particular purpose. In no event shall Silicon Microstructures, Inc. be liable for consequential, special, or indirect damages.

While Silicon Microstructures, Inc. provides application assistance personally, through its literature and the Silicon Microstructures, Inc. website, it is up to the customer to determine the suitability of the product for its specific application. The information supplied by Silicon Microstructures, Inc. is believed to be accurate and reliable as of this printing. However, Silicon Microstructures, Inc. assumes no responsibility for its use. Silicon Microstructures, Inc. assumes no responsibility for any inaccuracies and/or errors in this publication and reserves the right to make changes without further notice to any products or specifications herein

Silicon Microstructures, Inc.™ and the Silicon Microstructures, Inc. logo are trademarks of Silicon Microstructures, Inc. All other service or product names are the property of their respective owners.

© Silicon Microstructures, Inc. 2001-2017. All rights reserved.