1.5mm Box Header Single Row, 180 SMT Type


multicomp PRO

RoHS Compliant




Specifications


- Voltage rating Current rating Withstanding voltage Temperature range Insulation resistance Contact resistance After environmental testing
- : 100V AC / DC
- : 2A AC / DC
- : 500V AC/minute
- : -40°C to +105°C
- : ≥500MΩ : ≤20mΩ
- : ≤40mΩ




Diagram















02P Single Hole

No.	Description	Material	Remarks	QTY
1	Housing	LCP	Natural	1
2	PIN	Phorphos Bronze	Matte Tin 40u" Min.	*
3	Stator	Brass	Matte Tin 40u" Min	1


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Dimensions : Millimetres

1.5mm Box Header Single Row, 180 SMT Type

multicomp PRO



Poles	Dimensions			Delea	Dimensions		
Foles	A	В	С	Poles	А	В	С
02	1.5	7.3	4.45	09	12	17.8	14.95
03	3	8.8	5.95	10	7.5	19.3	16.45
04	4.5	10.3	7.45	11	15	20.8	17.95
05	6	11.8	8.95	12	16.5	22.3	19.45
06	7.5	13.3	10.45	13	18	23.8	20.95
07	9	14.8	11.95	14	19.5	25.3	22.45
08	10.5	16.3	13.45	15	21	26.8	23.95

Dimensions : Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



1.5mm Box Header Single Row, 180 SMT Type

multicomp PRO

Part Number Table

Description	Part Number	
Header, 1.5mm, 2Pins, Single Row, SMT	MP011285	
Header, 1.5mm, 3Pins, Single Row, SMT	MP011286	
Header, 1.5mm, 4Pins, Single Row, SMT	MP011287	
Header, 1.5mm, 5Pins, Single Row, SMT	MP011288	
Header, 1.5mm, 6Pins, Single Row, SMT	MP011289	
Header, 1.5mm, 7Pins, Single Row, SMT	MP011290	
Header, 1.5mm, 8Pins, Single Row, SMT	MP011291	
Header, 1.5mm, 9Pins, Single Row, SMT	MP011292	
Header, 1.5mm, 10Pins, Single Row, SMT	MP011293	
Header, 1.5mm, 11Pins, Single Row, SMT	MP011294	
Header, 1.5mm, 12Pins, Single Row, SMT	MP011295	
Header, 1.5mm, 13Pins, Single Row, SMT	MP011296	
Header, 1.5mm, 14Pins, Single Row, SMT	MP011297	
Header, 1.5mm, 15Pins, Single Row, SMT	MP011298	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for white any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

