

## C2220Y332JGGACAUTO

SMD COG HV AUTO FF, Ceramic, 3300 pF, 5%, 2000 VDC, COG, SMD, MLCC, Floating Electrode, Ultra-Stable, Automotive Grade, 2220



Click here for the 3D model.

Dimensions	
Chip Size	2220
L	5.9mm +/-0.75mm
W	5mm +/-0.4mm
T	2.5mm +/-0.20mm
В	0.7mm +/-0.35mm

Packaging Specifications		
Packaging	T&R, 180mm, Plastic Tape	
Packaging Quantity	500	

General Information	
Series	SMD COG HV AUTO FF
Style	SMD Chip
Description	SMD, MLCC, Ultra-Stable, Automotive Grade
Features	Floating Electrode, Automotive Grade
RoHS	Yes
Termination	Flexible Termination
Marking	No
Qualifications	AEC-Q200
AEC-Q200	Yes
Component Weight	320 mg
Shelf Life	78 Weeks
MSL	1

Specifications	
Capacitance	3300 pF
Measurement Condition	1 kHz 1.0Vrms
Capacitance Tolerance	5%
Voltage DC	2000 VDC
Dielectric Withstanding Voltage	2400 VDC
Temperature Range	-55/+125°C
Temperature Coefficient	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30 ppm/C, 1kHz 1.0Vrms
Dissipation Factor	0.1% 1 kHz 1.0Vrms
Aging Rate	0% Loss/Decade Hour
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given or results obtained.