

## Coaxial PCB Connector 82\_MCX-50-0-10/111\_N

### Description

Straight PCB jack

Interface Standards

IEC 60169-36\_CECC 22220



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	6 GHz

#### Mechanical Data

Board mounting type	through holes
Weight	0.0006 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing	DCA-00012986
Mounting hole	DOU-00012639

### Ordering Information

Bulk 100 pcs package	82_MCX-50-0-10/111_NH
Single package	82_MCX-50-0-10/111_NE

### Remarks

PCB connector without stand-offs