


Coaxial PCB Connector 81_SMP-S50-0-L1/111_N

Description

Right angle PCB plug

Interface Standards
MIL-STD-348 SMP



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 40 GHz

Mechanical Data

Board mounting type surface mount
Weight 0.00025 kg

Environmental Data

Operating temperature -55 °C to 125 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)

Related Documents

Outline drawing DOU-00316675

Ordering Information

Single package 81_SMP-S50-0-L1/111_NE