



## **BlackFin CT-2525CH Crimp Head**

CT-2525CH

Crimps Panduit #22 – 10 AWG fully insulated disconnects and insulated parallel splices.

### **Specifications**

Compatible Connector	Select Terminals, Splices and Disconnects
Maximum Wire Size (AWG)	#10
Minimum Wire Size (AWG)	#22
Sub Brand	BlackFin
For Use With	CT-2500 , CT-2500/E, CT-2500/L and CT-2500/LE crimp tools
Overall Height (In.)	2
Overall Height (mm)	70
Overall Length (In.)	5
Overall Length (mm)	129
Overall Width (In.)	1
Overall Width (mm)	37
Product Type	Crimp Head
Weight (Kg)	0.8
Weight (lb)	1.74
Crimp Profile	Circumferential or Hexagonal
Base Material	Steel
Application	Panduit CT-2500 and CT-2500/E Battery Operated Crimping Tools.

### **Packaging Detail**

UPC	07498300972
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0398
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000