

# **CLOCK OSCILLATOR**


Page 1 of 3

# COM23025-50.000-EXT-T-TR

#### ELECTRICAL SPECIFICATION


PARAMETER	SYMBO L	CONDITIONS	VALUE	UNIT
Nominal Frequency	fo	Ta=25°C	50.000	MHz
Supply Voltage Range	V <sub>cc</sub>	V <sub>CC</sub> ±10%	3.3	VDC
Supply Current, max	Is	Ta=25°C	40	mA
Operating Temperature Range	Ta		-40 ~ +85	°C
Storage Temperature Range	T <sub>(stg)</sub>	Absolute max	-55 ~ +125	°C
Frequency Stability	Δf/fo	Inclusive of 25°C Tolerance and Changes due to Operating Temperature, Supply Voltage, Load and first year Aging	±25	ppm
Output Voltage	Vol	Logic "0" Level	0.1 x Vcc	VDC
Output voltage	Voн	Logic "1" Level	0.9 x Vcc	VDC
Output Load		CMOS Output	15	pF
Enable / Disable Function	E/D	Pin 1: N.C. (Open) or High, Pin 3 - Oscillation (Enab	oled)	
Enable / Disable Function	E/D	Pin 1: Low, Pin 3 – High Impedance (Disabled)		
Symmetry (Duty Cycle)	DC	@50% Vdd	45 ~ 55	%
Rise Time and Fall Time	tr / tf	@10% to 90% Vdd	5	ns
Stand-by Current, max	I <sub>(std-by)</sub>		10	μA
Start-up Time, max	Ts		10	ms
Jitter, RMS, max.	J	1σ, 12kHz < Fj < 12MHz	1	ps

### MECHANICAL SPECIFICATION



#### NOTE: A capacitor of 0.01 $\mu F$ between Vcc and Ground is recommended

### CARRIER TAPE DIMENSIONS



NOTE: REFER TO EIA-481 FOR DIMENSIONS NOT LISTED

### PACKAGING

178 mm REEL DIAMETER 24 mm TAPE WIDTH, 8 mm PITCH QUANTITY: 1000 PIECES PER REEL

IN ACCORDANCE WITH EIA-481




# **CLOCK OSCILLATOR**

Page 2 of 3

# COM23025-50.000-EXT-T-TR

### REFLOW PROFILE



Reflow profile			
Temperature Min Preheat	T <sub>SMIN</sub>	150°C	
Temperature Max Preheat	T <sub>SMAX</sub>	200°C	
Time (T <sub>SMIN</sub> to T <sub>SMAX</sub> )	ts	60-180 sec.	
Temperature	T∟	217°C	
Peak Temperature	T <sub>P</sub>	260°C	
Ramp-up rate	R <sub>UP</sub>	3°C/sec max.	
Ramp-down rate	R <sub>DOWN</sub>	6°C/sec max.	
Time within 5°C of Peak Temperature	t <sub>P</sub>	10 sec.	
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.	
Time	t <sub>L</sub>	60-150 sec.	

### ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH-SVHC	Compliant
HALOGEN-FREE	Compliant
TERMINATION FINISH	Au





# **CLOCK OSCILLATOR**

Page 3 of 3

## COM23025-50.000-EXT-T-TR

#### MARKING

Rx50.00T •3AEyww

x - 1 or 2 digits as Internal Production ID code

y - Year code

w - Week code

YEAR CODE		
Year	Code	
2018	8	
2019	9	
2020	0	
2021	1	
2022	2	
2023	3	
2024	4	
2025	5	
2026	6	
2027	7	
2028	8	
2029	9	

ALPHA WEEK CODE TABLE					
Week	Code	Week	Code	Week	Code
1	а	19	S	37	K
2	b	20	t	38	L
3	С	21	u	39	М
4	d	22	V	40	N
5	е	23	W	41	0
6	f	24	Х	42	Р
7	g	25	у	43	Q
8	h	26	Z	44	R
9	i	27	Α	45	S
10	j	28	В	46	T
11	k	29	С	47	U
12	1	30	D	48	V
13	m	31	Е	49	W
14	n	32	F	50	Х
15	0	33	G	51	Υ
16	р	34	Н	52	Z
17	q	35			
18	r	36	J		

#### APPROVAL

RALTRON		
DRAWN BY:	KJackson, January 19, 2015	
APPROVED BY:	KJackson, January 19, 2015	
REVISION:	A, Initial Release B, Updated to current spec levels KJ 6/13/19 C, Updated marking to current spec levels by XLiu, December 10, 2020	

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech does not sasume any liability arising lability arising labi

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.