Data Sheet



Coaxial PCB Connector 92_MMBX-S50-0-12/111_N

Description

Edge mount PCB jack

Interface Standards
SUHNER-MMBX



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 12.4 \ \text{GHz} \end{array}$

Mechanical Data

Board mounting type edge mount Weight 0.0011 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -55 °C to 155 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing DOU-00013388
Catalogue drawing DCA-00013390
Mounting hole DOU-00013391

Ordering Information

 Tape and Reel package
 92_MMBX-S50-0-12/111_NM

 Single package
 92_MMBX-S50-0-12/111_NE

Remarks

PCB connector without stand-offs

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.