Data Sheet



Coaxial Cable Connector 11_SMA-50-3-45/133_N

Description

Straight cable plug

Interface standards
IEC 60169-15 MIL-STD-348A/310 CECC 22110



Technical Data

Electrical Data

Impedance 50 Ω Interface frequency max. 18 GHz

Mechanical Data

Centre contact soldered
Outer contact crimped
Weight 0.0045 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)

-65 °C to 165 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00007384
Catalogue drawing DOU-00006088
Assembly instruction DOC-0000179078

Ordering Information

 Single package
 11_SMA-50-3-45/133_NE

 Bulk 100 pcs package
 11_SMA-50-3-45/133_NH

Additional Information

Suitable cables RG_58_C/U, G_03232, GX_03272

Remarks

El. Optimized for cable RG 58 C/U

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.