EMC Components

⊗TDK

Common mode filters Ultra high-speed differential signal line (HDMI, DVI, DisplayPort, USB3.0, etc.) TCM-T series



TCM0605T type



FEATURES

- O This product is a thin-film common mode filter with a wide frequency range that can be used for high-speed differential signal interfaces such as USB3.0 and DisplayPort.
- In improved common mode attenuation of 2.4GHz or 5.0GHz, produces a sufficient anti effect to common mode noise of highfrequency. Also, to realizing remarkable band differential mode transmission(8.0GHz or more), do not have an impact almost to transmission speed difference differential line signal.
- Operating temperature range: -25 to +85°C

APPLICATION

Noise countermeasure for ultra-high-speed differential interfaces (HDMI, DVI, DisplayPort, USB3.0, etc.) for mobile devices and general consumer products such as smart phones, tablets, digital cameras, and portable music players.

O Application guides: Smart phones/tablets

PART NUMBER CONSTRUCTION

TCM	0605	T	- 080 -	2P -	- T	201
Series name	L×W×T dimensions 0.65×0.5×0.3 mm	Product internal code	Impedance (Ω) at 100MHz	Number of lines	Packaging style	Internal code

CHARACTERISTICS SPECIFICATION TABLE

Common mode attenuation	DC resistance	Cutoff frequency	Rated current	Rated voltage	Insulation resistance	Part No.
	[1 line]					
(dB)	(Ω)	(GHz)typ.	(A)max.	(V)max.	(MΩ)min.	
30min. @5.0GHz	- 2.0±30%	10.0	0.1	10	10	TCM0605T-080-2P-T201
18min. @4.0 to 6.0GHz	2.0±30 %	10.0	0.1	10	10	<u>10000001-000-21-1201</u>
35min. @2.4GHz	- 2.5±30%	8.0	0.1	10	10	TCM0605T-200-2P-T201
18min. @1.9 to 3.3GHz	2.0±30%	0.0	0.1	10	10	10100001-200-2F-1201

Measurement equipment

Measurement item	Product No.	Manufacturer
Common mode impedance	4291A	Keysight Technologies
DC resistance	4338A	Keysight Technologies
Insulation resistance	4339A	Keysight Technologies


* Equivalent measurement equipment may be used.



20181101


TCM0605T type

■ IMPEDANCE VS. FREQUENCY CHARACTERISTICS



Measurement equipment				
Product No.	Manufacturer			
4991A	Keysight Technologies			
* Equivalent measurement equipment may be used.				

■ INSERTION LOSS VS. FREQUENCY CHARACTERISTICS




* Equivalent measurement equipment may be used.


A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (2/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.

TCM0605T type

SHAPE & DIMENSIONS



PACKAGING STYLE




RECOMMENDED LAND PATTERN




Dimensions in mm


CIRCUIT DIAGRAM




RECOMMENDED REFLOW PROFILE



TAPE DIMENSIONS



Туре	А	В	К
TCM0605T	0.63	0.77	0.35



Dimensions in mm

Dimensions in mm

PACKAGE QUANTITY

Package quantity

10,000 pcs/reel

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range	Storage temperature range*	Individual weight
–25 to +85 °C	–25 to +85 °C	0.5 mg
* The storage temperature range is for after the assembly.		

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/4)

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

 The storage period is less than 6 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 20 to 70% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. 				
O Do not use or store in locations where there are conditions such as	gas corrosion (salt, acid, alkali, etc.).			
 Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature does not exceed 150°C. 	difference between the solder temperature and chip temperature			
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.				
• When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.				
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.				
 Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference. 				
\bigcirc Use a wrist band to discharge static electricity in your body through	the grounding wire.			
\bigcirc Do not expose the products to magnets or magnetic fields.				
O Do not use for a purpose outside of the contents regulated in the de	livery specifications.			
 The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property. If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us. 				
 (1) Aerospace/aviation equipment (2) Transportation equipment (cars, electric trains, ships, etc.) (3) Medical equipment (4) Power-generation control equipment (5) Atomic energy-related equipment (6) Seabed equipment (7) Transportation control equipment 	 (8) Public information-processing equipment (9) Military equipment (10) Electric heating apparatus, burning equipment (11) Disaster prevention/crime prevention equipment (12) Safety equipment (13) Other applications that are not considered general-purpose applications 			
When designing your equipment even for general-purpose applications tection circuit/device or providing backup circuits in your equipment.	s, you are kindly requested to take into consideration securing pro-			

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (4/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.