


Within Series Adaptor 33_SMA-50-0-100/111_N

Description

Adaptor plug/jack
SMA-precision plug (male) / SMA-precision jack (female)

For Test & Measurement applications
Expanded freq. range up to 26.5 GHz

Interface standard
Series SMA-precision - IEC 60169-15_MIL-STD-348A/405_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	26.5 GHz
Electrical length	31.94 mm

Mechanical Data

Number of matings	500
Weight	0.0055 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)	-65 °C to 125 °C compliant
--	-------------------------------

Material Data

Interface - SMA-precision plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating (Nickel underplated)
Gasket	VMQ (Silicone rubber)	

Interface - SMA-precision jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00013734
-------------------	--------------

Ordering Information

Single package	33_SMA-50-0-100/111_NE
----------------	------------------------