

## Features

- Universal Input 100~240VAC 50/60Hz
- IEC/EN/ANSI/AAMI ES 60601-1 (ED 3.1)
- EMC: IEC60601-1-2:2014(ED 4.0)
- Safety Approvals: cULus / UKCA / CB / PSE / FCC / CE / TUV / RoHS / REACH
- Means of Protection: 2 X MOPP
- Touch Current: < 100µA
- Single Output to 90W
- Regulated Output with Low Ripple Noise
- Safety Agency Requirements and EMI/EMS Certified
- Meets DoE Level VI, Energy Star, ErP Stage 2
- No Load Power Consumption Less Than 0.21W
- IEC C14 Connector



Ideal Power's 44ATM090T-Pxyz 90W AC/DC External Desktop Power Supply (PSU) Series are certified to cULus / UKCA / CB / PSE / FCC / CE / TUV / RoHS / REACH & IEC 60601-1-2:2014(ED 4.0) Standards and comply with (EU) 2019/1782, Level VI Efficiency Regulations. These are primarily used in Medical, ITE, Audio & Video Industries and customised solutions are available upon request.

### Models

Model Number	Output Voltage V DC	Output Current A	Output Power W
44ATM090T-P120	12	7	84
44ATM090T-P150	15	6	90
44ATM090T-P180	18	5	90
44ATM090T-P190	19	4.74	90
44ATM090T-P240	24	3.75	90

### General Specification

Type	Switched Mode Power Supply
Input Connector	IEC 320-C14
Output Connection	2.1x5.5x11.0mm +ve inner/centre
Number of Outputs	1
Energy Efficiency Level	VI
Mounting Style	Desktop
MTBF	300,000 hours calculated at 25°C, by Telcoria SR-332
Power Indicator	LED Indicator for power on
Cable Length	1500mm(±30mm)
Cable Type	16AWG/18AWG/20AWG (Depending on model)
Medical Approved	Yes

**Mechanical Specifications**

Housing Material	Fully Enclosed Plastic Case
Overall Dimensions	160mm x 64mm x 35mm
Overall Length	160mm
Overall Depth	64mm
Overall Width	35mm
Weight	460g

**Input Specifications**

Rated Input Voltage	100~240Vac ( $\pm 10\%$ )
Rated Frequency	50/60Hz
Efficiency Level VI	Level VI / Efficiency (EU) 2019/1782
Input Current	1.2A-0.5A
Inrush Current	80A Max. / 230Vac (Cold Start At 25°C, Full Load)
Touch Current	Less than 100 $\mu$ A
Input Protection	Internal Primary Current Fuse

**Output Specifications**

Output Regulation	$\pm 5\%$
Ripple & Noise (max.)	1% Vp-p Max. for Output Voltage @ Full Load
Voltage Tolerance	$\pm 5\%$
Load Regulation	$\pm 5\%$
No Load Power Consumption	<0.21W
Hold-up Time	10mS @ Full Load
Transient Response	0.5mS for 50% Load Change (Typical)
Number of Outputs	1
Insulation Class	I
Dielectric Strength	Primary to Secondary 4,000Vac for 1 Minutes
Isolation Resistance	10M $\Omega$ for 500Vdc
Over Circuit Protection	Auto-recovery
Over Voltage Protection	V out * 150% MAX., latch off
Over Current Protection	I out * 170% MAX., auto-recovery


**Protection Category**

Means of Protection	2 X MOPP
---------------------	----------


**Approvals**

Compliance/Certifications	CB / cULus/ FCC / CE / UKCA / T-mark / TUV / PSE
Safety Standard	IEC/EN/ANSI/AAMI ES 60601-1
EMC Emission:	Directive 93/42/EEC (EN 60601-1-2)


**Mechanical Drawing**




TOP-VIEW




BOTTOM-VIEW



SIDE-VIEW



FRONT-VIEW



Output cable plug pin assignment

