

# Features

- Universal Input 90~264VAC 50/60Hz
- Output Voltages: 12-48V DC
- IEC/UL/EN 60950-1
- Meets the latest Safety Standards and Approvals
- Single Output to 60W
- High Efficiency
- 100% Full load burn-in Test
- Low Ripple & Noise
- Class II
- Protection: Overload/Over voltage/Short circuit
- Dimensions: 58 x 52.5 x 90mm
- Weight: 190g



Ideal Power's 56YSD60S-xy 60W DIN Rail Mount AC/DC Power Supply Converter Series are certified to cURus, CE, RoHS & IEC/UL/EN62368 Standards and comply with (EU) 2019/1782, Level VI Efficiency Regulations. These are primarily used in ITE, Audio & Video Industries and customised solutions are available upon request.

#### Models

Model Number	Output Voltage V DC	Output Current A	Output Power W
56YSD60S-1204500	12	4.5	54
56YSD60S-1504000	15	4	60
56YSD60S-2402500	24	2.5	60
56YSD60S-4801250	48	1.25	60

#### **General Specification**

Туре	DIN Rail Power Supply
AC or DC Input Voltage	AC
AC or DC Output Voltage	DC
Number of Outputs	1
Mounting Style	Din Rail Mount
Connection Type	Screw Terminal Type
Overload Protection	>130%-200% rated output power (Protection type: Hiccup mode, recovers automatically after faultcondition is removed)
Over Current Protection	110% - 180%
Short Circuit Protection	Protection to Zero Voltage
Over Voltage Protection	110~145% (Protection Type: Clamp by zener diode)



#### **Mechanical Specifications**

Housing Material	Fully Enclosed Plastic Case
Overall Dimensions	58mm x 52.5mm x 90mm
Overall Length	90mm
Overall Depth	58mm
Overall Width	52.5mm
Weight	190g

## Input Specifications

Input Electrical Phase	Single
Line Frequency	47-63Hz
Inrush Current	30 Amps max. at 115VAC/60Hz,full load & 60Amps max. at 240VAC/50Hz,full load
AC Current	1.2A/115VAC 0.8A/230VAC
Efficiency Type	88~91% Depending on Model
Leakage Current	<0.25mA/240VAC

#### **Output Specifications**

Output Voltage Adjustment	+/- 10% Depending on Model	
Ripple and Noise	120~240 mV Depending on Model	
Line Regulation	± 1%	
Load Regulation	± 1%	
Isolation Resistance	I/P-O/P:100M Ohms / 500VDC / 25 / 70% RH	
Setup, Rise, Hold Up time	500mS/50mS/12mS(115V/60HZ MAX ROAD), 500mS/50mS/30mS(230V/50HZ MAX ROAD)	
MTBF	200000 h	

## **Operational Environment**

Operating Humidity	20% ~ 90% RH non-condensing
Operating Temperature Range	-20°C to 50°C,Full load, Normal operation.
Storage Temperature Range	-40°C to 80°C
Storage Humidity	10% ~ 95% RH
Cooling	Cooling

#### **Protection Category**

IP Rating

IP20




## Approvals


Safety Standard	UL60950-1, UL508, , BSMI CNS14336-1,TUV EN61558-2-16 IEC60950-1, EAC TPTC 004,TUV EN60950-1
EMC Emissions	EN55032(CISPR32), CNS13438 Class B ,EN61000-3-2 Class A ,EN61000-3- 3,EN61000-4- 2,3,4,5,6,8,11, EN55024, EN55035, EN61000-6-2, EN61204-3

#### **Mechanical Drawing**






Deduction curve and temperature:



Minus output and input voltage curves:



Ideal Power Limited 14 Larks Way, Tree Beech Enterprise Park, Gunn, Barnstaple, Devon, EX32 7NZ. www.idealpower.co.uk | +44 (0) 845 260 3400