

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349580341](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Vertical Hybrid Header, 3 Rows, 34 Circuits, Polarization Option B, Gray, Tray

Documents:

3D Model (PDF)	Application Specification AS-34959-001-001 (PDF)
Drawing (PDF)	Test Summary TS-34961-001-001 (PDF)
3D Model	Datasheet (PDF)
Product Specification PS-34959-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 349590001-AS-CH-000 (PDF)	

General


Product Family	PCB Headers
Series	34958
Application	Automotive, Power, Signal, Wire-to-Board
Comments	30 x 0.50mm blades = 4.0A; 4 x 1.20mm blades = 16.0A
Component Type	PCB Header
Overview	Mini50 Connection Systems
Product Name	Mini50
Taxonomy	PCB Headers and Receptacles
UPC	887191714585

Physical

Breakaway	No
Circuits (Loaded)	34
Circuits (maximum)	34
Color - Resin	Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	6.670/g
Number of Rows	3
Orientation	Vertical
PC Tail Length	3.07mm
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	16.0A, 4.0A
-------------------------------	-------------



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34958 Series](#)

Mates With

Mini50 Unsealed Receptacle [349590341](#) ,
[349590348](#)

Voltage - Maximum

500V DC

Material Info

Reference - Drawing Numbers

Application Specification

349590001-AS-CH-000, AS-34959-001-001

Product Specification

PS-34959-001-001

Test Summary

TS-34961-001-001

This document was generated on 03/10/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION