



50 Ω nominal input / conjugate match balun to QFN-4L STM32WL in low power mode, 862-928 MHz with integrated harmonic filter



Chip scale package on glass 8 bumps - 1.83 x 2.13 mm²



Product status

BALFHB-WL-05D3

Features

- QFN STM32WL sub-GHz wireless microcontrollers impedance matched balun and Tx harmonics filter
- Optimized for QFN STM32WL sub-GHz wireless microcontrollers in low power mode and dedicated to 4-layers PCB
- 50 Ω nominal input / conjugate matched balun to QFN STM32WL
- 50 Ω nominal impedance on antenna side Tx and Rx
- Deep Tx rejection harmonic filter
- Low insertion loss
- Small footprint
- Low profile ≤ 630 µm after reflow
- High RF performance
- RF BOM and area reduction
- ECOPACK2 compliant component

Applications

- STM32WL sub-GHz wireless microcontrollers
- LPWAN-compliant radio solution, enabling the following modulations: LoRa®, (G)FSK, (G)MSK, and BPSK

Description

STMicroelectronics BALFHB-WL-05D3 is an ultra-miniature balun. This device integrates a matching network, balun, and harmonics filter. Matching impedance has been customized for the STM32WL sub-GHz wireless microcontrollers.

It is using STMicroelectronics IPD technology on a nonconductive glass substrate, which optimizes RF performances.



1 Characteristics

Table 1. Absolute maximum ratings (T_{amb} = 25 °C)

Symbol	Parameter	Value	Unit
P _{IN}	Input power RF _{IN}	27	dBm
V _{ESD}	ESD ratings human body model (JESD22-A114), all I/O one at a time while others connected to GND	2000	V
	ESD ratings machine model, all I/O		
T _{OP}	Operating temperature	-40 to +105	°C

Table 2. Impedances (T_{amb} = 25 °C)

Symbol	Parameter	Value			Unit
Symbol		Min.	Тур.	Max.	Unit
Z _{RX}	Nominal differential Rx balun impedance	-	Matched to STM32WL	-	
Z _{TX}	Nominal Tx filter impedance	-	Matched to STM32WL	- Ω	
Z _{RX-ANT}	Nominal Rx balun antenna impedance	-	50		
Z _{TX-ANT}	Nominal Tx filter antenna impedance	-	50	-	

Table 3. Electrical characteristics and RF performances (T_{amb} = 25 °C)


Cymhal	Parameter	Took condition	Value		Unit	
Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
f	Frequency range	•	862	868	928	MHz
IL _{RX}	Rx balun insertion loss differential mode S _{DS} without mismatch loss Typical value given at 868 MHz			1.20	1.40	dB
IL _{TX}	LP Tx filter insertion loss S ₂₁ without mismatch loss	Typical value given at 868 MHz		0.65	0.95	dB
RL _{RX-ANT}	Rx balun input return loss differential mode S _{DD} on antenna Typical value given at 868 MHz		15	20		dB
RL _{TX-ANT}	Tx filter output return loss S ₁₁ on antenna Typical value given at 868 MHz		16	24		dB
Ф _{imb}	RX balun phase imbalance		-3.0		3.0	0
A _{imb}	RX balun amplitude imbalance		-0.6		0.6	dB
		Attenuation at 2fo	33	35		
	Tx filter harmonic rejection levels S ₂₁	Attenuation at 3fo	38	40		
		Attenuation at 4fo	39	48		
		Attenuation at 5fo	36	64		
Att _{TX}		Attenuation at 6fo	30	56		dB
		Attenuation at 7fo	20	33		
		Attenuation at 8fo	20	27		
		Attenuation at 9fo	30	39		
		Attenuation at 10fo	37	42		


DS14104 - Rev 2 page 2/13




1.1 RF measurements (Rx balun)









DS14104 - Rev 2 page 3/13



1.2 RF measurements (Tx filter)

Figure 5. Transmission wide band with harmonics attenuation (dB)




Figure 6. Insertion loss (dB)





Figure 7. Return loss on antenna (dB)



DS14104 - Rev 2 page 4/13



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 CSPG 8 bumps package information

| FE1 | E2 | E3 | FE2 | FD2 | FD2 | FD2 | FD2 | FD2 | FD3 | FD3 | FD4 | FD4 | FD5 |

Figure 8. CSPG 8 bumps package outline (bottom view - bumps up) (in µm)

Table 4. CSPG 8 bumps dimensions (in µm)

Parameter	Min.	Тур.	Max.
Α	580	630	680
A1	180	205	230
A2	380	400	420
b	230	255	280
D	2080	2130	2150
D1		340	
D2		500	
D3		210	
D4		630	
E	1780	1830	1880
E1		690	
E2		85	
E3		605	
fD1		225	
fD2		225	
fE1		225	
fE2		225	

DS14104 - Rev 2 page 5/13



2.2 CSPG 8 bumps packing information




Table 5. Pads description top view (pads down)

Pad ref.	Pad name	Description	
A1	RFO_in	Tx filter input	
A2	RFI_N_out	Differential-N Rx balun output	
A3	RFI_P_out	Differential-P Rx balun output	
B1	GND2	Ground #2	
B2	GND3	Ground #3	
C1	RFO_out	Tx filter output	
C2	GND1	Ground #1	
C3	RFI_in	Single ended Rx balun input	

DS14104 - Rev 2 page 6/13



Pin 1 located according to EIA-481

P0

Ø D0

E1

F

W

User direction of unreeling

Figure 11. Tape and reel outline

Note: Pocket dimensions are not on scale Pocket shape may vary depending on package

Table 6. Tape and reel mechanical data

	Dimensions				
Ref	Millimeters				
	Min	Тур	Max		
A0	1.89	1.94	1.99		
В0	2.19	2.24	2.29		
Ø D0	1.40	1.50	1.60		
Ø D1	0.95	1.00	1.05		
E1	1.65	1.75	1.85		
F	3.45	3.50	3.55		
K0	0.70	0.75	0.80		
P0	3.90	4.00	4.10		
P1	3.90	4.00	4.10		
P2	1.95	2.00	2.05		
W	7.90	8.00	8.30		

Note: More packing information is available in the application note:

AN2348 Flip-Chip: "Package description and recommendations for use"

DS14104 - Rev 2 page 7/13



3 PCB assembly recommendations

3.1 Land pattern

STM32WL QFN

300 μm

250 μm

200 μm

250 μm

BALFHB-WL-05D3

50 Ω line

Figure 12. QFN-4L PCB recommended land pattern

Layout example using STM32WL in QFN package / 4 layers PCB for low power mode.





Figure 13. QFN-4L PCB stack-up recommendations

DS14104 - Rev 2 page 8/13



3.2 Stencil opening design



3.3 Solder paste

- 1. Halide-free flux qualification ROL0 according to ANSI/J-STD-004.
- 2. "No clean" solder paste is recommended.
- 3. Offers a high tack force to resist component movement during high speed.
- 4. Use solder paste with fine particles: powder particle size 20-38 μm.

3.4 Placement

- Manual positioning is not recommended.
- It is recommended to use the lead recognition capabilities of the placement system, not the outline centering
- 3. Standard tolerance of ±0.05 mm is recommended.
- 4. 1.0 N placement force is recommended. Too much placement force can lead to squeezed out solder paste and cause solder joints to short. Too low placement force can lead to insufficient contact between package and solder paste that could cause open solder joints or badly centered packages.
- 5. To improve the package placement accuracy, a bottom side optical control should be performed with a high resolution tool.
- 6. For assembly, a perfect supporting of the PCB (all the more on flexible PCB) is recommended during solder paste printing, pick and place and reflow soldering by using optimized tools.

3.5 PCB design preference


- 1. To control the solder paste amount, the closed via is recommended instead of open vias.
- 2. The position of tracks and open vias in the solder area should be well balanced. A symmetrical layout is recommended, to avoid any tilt phenomena caused by asymmetrical solder paste due to solder flow away.

DS14104 - Rev 2 page 9/13



3.6 Reflow profile

Figure 16. ST ECOPACK® recommended soldering reflow profile for PCB mounting



Note: Minimize air convection currents in the reflow oven to avoid component movement.

Note: More information is available in the application note:

AN2348 Flip-Chip: "Package description and recommendations for use"

DS14104 - Rev 2 page 10/13



4 Ordering information

Table 7. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
BALFHB-WL-05D3	W5	CSPG	3.9 mg	5000	Tape and reel

DS14104 - Rev 2 page 11/13



Revision history

Table 8. Document revision history

Date	Revision	Changes
14-Oct-2022	1	Initial release.
21-Dec-2022	2	Updated Table 1. Absolute maximum ratings (T _{amb} = 25 °C).

DS14104 - Rev 2 page 12/13



IMPORTANT NOTICE - READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics - All rights reserved

DS14104 - Rev 2 page 13/13