









## **RCJ6FA**

3 pole XLR female receptacle with 1/4" stereo jack without switching contact



## **Article Variations**

Article Name	Details	Packaging
RCJ6FA-H	Horizontal PCB contacts, locking latch	BULK
RCJ6FA-H-0	Horizontal PCB contacts, retention spring	BULK
RCJ6FA-V	Vertical PCB contacts, locking latch	BULK
RCJ6FA-V-0	Vertical PCB contacts, retention spring	BULK



## **Technical Information**

Product	
Title	RCJ6FA
Connection Type	XLR/Jacks Combo

Electrical		
Contact resistance - XLR	≤ 15 mΩ	
Contact resistance - 1/4" Jack	≤ 25 mΩ	
Dielectric strength	1500 V dc	
Insulation resistance - inital	$\geq 0.5 \ \text{G}\Omega$	
Insulation resistance -after damp heat	$\geq 0.2 \ \text{G}\Omega$	
Rated current per Contact - XLR	3 A	
Rated current per Contact - 1/4" Jack	3 A	
Rated voltage	50 V ac	

Mechanical	
Lifetime	> 1'000 mating cycles
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Panel thickness	max. 3 mm (0.12")
Wiring	PCB mount
Locking device	Latch look
Mounting direction	Rear mounting
Mounting screw	Self-tapping Plastite® screw with thread 2.9 x 1.06 and tri- rondular configuration

Material		
Shell	PA 6.6 30% GR	
Contacts	CuSn6	
Contact plating - XLR	Au / Ag (G, TN, RN, SN)	
Contact plating - 1/4" Jack	Au (TRS)	
Locking latch	CK 65Mn steel	



Environmental		
Flammability	UL 94 V0	
Operating temperature	-20°C to +70°C	
Solderability	complies with IEC68-2-20	
Environmental	complies with EU RoHS 2 and REACH	