



## **NYS216**

3 pole horizontal 1/4" jack, all contacts switched, plastic housing with nut and washer  $\,$ 













## **Article Variations**

| Article<br>Name | Details   | Packaging |
|-----------------|---|-----------|
| NYS216          | Stereo 3 pole, 8.2 mm distance to PCB                     | BULK      |
| NYS216H         | Stereo 3 pole, half threaded nose, 8.2 mm distance to PCB | BULK      |
| NYS2162         | Mono 2 pole, 8.2 mm distance to PCB                       | BULK      |
| NYS2162H        | Mono 2 pole half threaded nose, 8.2 mm distance to PCB    | BULK      |
| NYS216G         | Stereo 3 pole, gold contacts, 8.2 mm distance to PCB      | BULK      |



## **Technical Information**

| Product         |        |  |
|-----------------|--------|--|
| Title           | NYS216 |  |
| Connection Type | Jack   |  |
| Gender          | female |  |

| Electrical            |                            |  |
|-----------------------|----------------------------|--|
| Dielectric strength   | 0.5 kVdc                   |  |
| Insulation resistance | ≥ 1 GΩ                     |  |
| Rated current         | depends on mated connector |  |
| Contact resistance    | depends on mated connector |  |

| Mechanical       |                    |  |
|------------------|--------------------|--|
| Insertion force  | ≤ 20 N             |  |
| Withdrawal force | ≥ 10 N             |  |
| Lifetime         | 1000 mating cycles |  |
| Wiresize         |                    |  |

| Material           |                   |  |
|--------------------|-------------------|--|
| Contact plating    | SnCe              |  |
| Contacts           | Brass (CuZn39Pb3) |  |
| Shell / Insulation | Thermoplastic     |  |

| Environmental     |                           |  |
|-------------------|---------------------------|--|
| Solderability     | Complies with IEC 68-2-20 |  |
| Temperature range | -20 °C to +70 °C          |  |