

RJI MF-PN RJ45plug Cat5, 4p IDC angl.35°



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1142
Specification	RJI MF-PN RJ45plug Cat5, 4p IDC angl.35°
HARTING eCatalogue	https://b2b.harting.com/09451511142

Identification

Category	Connectors
Series of hoods/housings	HARTING RJ Industrial®
Element	Connector
Specification	Multi Feature RJ45 35° angled

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4

Technical characteristics

Conductor cross-section	0.12 ... 0.32 mm ² Stranded 0.12 ... 0.32 mm ² Solid
Conductor cross-section	AWG 26/7 ... AWG 22/7 Stranded AWG 26/1 ... AWG 22/1 Solid
Wire outer diameter	0.8 ... 1.6 mm
Rated current	1.76 A
Rated voltage	50 V AC 60 V DC
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Insulation resistance	> 5 x 10 ⁹ Ω



Pushing Performance
 Since 1945

Technical characteristics

Contact resistance	≤20 mΩ
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Relative humidity	95 % Non-condensing (operation)
Insertion force	≤25 N
Withdrawal force	≤25 N
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm
Test voltage U _{DC}	1 kV (contact-contact) 1.5 kV (contact-ground)

Material properties

Material (insert)	Polycarbonate (PC)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side Sn over Ni Termination side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Colour (hood/housing)	Silver
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60603-7 Mating face ISO/IEC 11801 EN 50173-1
----------------	--



Pushing Performance
Since 1945

Specifications and approvals

Approvals DNV GL

PROFINET Yes

Commercial data

Packaging size 1

Net weight 39.6 g

Country of origin Germany

European customs tariff number 85366990

GTIN 5713140224322

eCl@ss 27440114 Rectangular connector (for field assembly)