




Terminals & Splices > Splices



Wire Size: .15 – .61 mm²
Sealable: **Yes**
Splice Features: **Splice Kit**
Barrel Inside Diameter: **1.2 mm [.048 in]**

Features

Product Type Features

Splice Accessory Type	Splice
Sealable	Yes
Serrated	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Serrations	0
Compatible With Wire & Cable Type	Discrete Wire

Body Features

Weight per Piece	.68 g
Splice Features	Splice Kit
Primary Product Material	Copper Alloy

Contact Features

Barrel Type	Closed
-------------	--------

Dimensions

Wire Size	304 – 1216 CMA
Barrel Inside Diameter	1.2 mm[.048 in]
Overall Product Length	29.21 mm[1.15 in]

Usage Conditions

--	--



Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	Yes
-----------------------------	-----

Packaging Features

Packaging Quantity	100
Packaging Method	Bag/Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 316079-002
55A1121-26-6/9-9



TE Part # 382254-009
44A1121-22-0/9-9



TE Part # 749589-000
55PC2111-20-9-9



TE Part # 216027-008
55A0111-26-9



TE Part # 306144-001
44AM1121-22-0/9-9



TE Part # 849201-000
FLTWC0311-22-0



TE Part # 042113-000
FLTWC0311-22-2



TE Part # 803651-000
55PC0111-22-9



TE Part # 216001-005
55A0111-22-9



TE Part # 282030-013
44A0111-22-0



TE Part # 282039-017
44A0111-22-9



TE Part # 285752-009
44A0111-26-2-US



TE Part # 382286-000
44A1121-22-2/6-9



TE Part # 382243-015
44A1121-24-0/9-9



TE Part # 113755-000
55A1121-26-0/9-9



TE Part # 392611-000
55A1841-24-0/2/5/9-3



TE Part # 217675-000
55PC0811-22-5LL-CS2502



TE Part # 804527-000
55PC1121-22-2/6-9CS2502



TE Part # 285750-010
44A0111-26-0-US



TE Part # 383814-000
44A1121-24-2/3-9

Customers Also Bought



TE Part #3-2176306-8
RP 1E 0.1W 2K8 0.1% 25PPM 5K RL

TE Part #58573-1
SPARE WIRE CAPPER ASSEMBLY

TE Part #1901000-1
NEST #6

TE Part #1960-203-0831
CONT PIN ASSY

TE Part #C95162-000
AD-1377CRMPTOL3CVT-CS2065

TE Part #66169-2
AMP-TAB L.P. TERMINAL

TE Part #708213-000
CMC-0553-1-9CS2903

TE Part #ZPF000000000097199
086-0607-08

Documents

Product Drawings

D-436-36

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_650074-000_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_650074-000_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_650074-000_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654025_Sec8_D-436

English

Harness Repair Products Quick Reference Guide

English

Product Specifications

Application Specification

English

650074-000

Splices, 26 – 20 AWG Wire Size, .15 – .61 mm² Wire Size, Sealable, Splice Kit, .048 in [1.2 mm] Barrel Inside Diameter, 304 – 1216 CMA Wire Size

