


ENERGIZER NO. A91

AA



Industry Standard Dimensions in mm (inches)



Chemical System:	Alkaline Zinc-Manganese Dioxide (Zn/MnO ₂) (No Added Mercury or Cadmium)
Designation:	ANSI-15A, IEC-LR6
Battery Voltage:	1.5 Volts
Internal Resistance:	146 Milliohms (Fresh)
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Average Capacity:	2,707 mAh (to 0.8 volts) (Rated capacity at 25 mA continuous drain)
Average Weight:	23.0 grams (0.8 oz.)
Volume:	8.1 cubic centimeters (0.5 cubic inch)
Cell:	One No. 3-315 (size 'AA')
Jacket:	Plastic Label
Shelf Life:	5 years (80% of rated capacity)


TEMPERATURE EFFECTS

Typical Service to 0.8 Volts




CONSTANT RESISTANCE PERFORMANCE

Typical Service



CONSTANT CURRENT DISCHARGE

Typical Service



Important Notice


This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.


Copyright © Eveready Battery Co. - All rights reserved

ENERGIZER NO. A91

CONSTANT POWER DISCHARGE
Typical Service




CONSTANT POWER DISCHARGE
Typical Service




ANSI - IEC Industry Standard Tests @ 20° C


RADIO
43 ohm - 4 hours/day




TOY
3.9 ohm - 1 hr/day



REMOTE
24 ohm - 15 spm - 8 hr/day



TAPE PLAYER
10 ohm - 1 hr/day



CD / MD / ELEC GAME
250 mA - 1 hr/day



DIGITAL CAMERA
1000 mA-Cont

PHOTOFLASH
1000 m10sec/min
1 hr/day



Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved