

# SEK mezz Fe 34P THR 2.9mm PL2



| Part number        | 09 19 534 6824 741                     |
|--------------------|--|
| Specification      | SEK mezz Fe 34P THR 2.9mm PL2          |
| HARTING eCatalogue | https://b2b.harting.com/09195346824741 |

Image is for illustration purposes only. Please refer to product description.

## Identification

| Category                   | Connectors       |
|----------------------------|------------------|
| Series                     | SEK Mezzanine    |
| Element                    | Female connector |
| Description of the contact | Straight         |

#### Version

| Termination method | Reflow soldering termination (THR)        |
|--------------------|---|
| Connection type    | PCB to PCB<br>Motherboard to daughtercard |
| Number of contacts | 34  |
| Termination length | 2.9 mm                                    |
| Pack contents      | Tape & reel                               |

# Technical characteristics

| Contact rows                       | 2   |
|------------------------------------|---|
| Contact spacing (termination side) | 2.54 mm   |
| Rated current                      | 1 A   |
| Insulation resistance              | >10 <sup>9</sup> Ω  |
| Contact resistance                 | ≤20 mΩ  |
| Limiting temperature               | -55 +125 °C (during reflow soldering max. +240 °C for 60 s) |
| Insertion and withdrawal force     | ≤68 N   |
| Performance level                  | 2   |
| Mating cycles                      | ≥250  |



## Technical characteristics

Test voltage U<sub>r.m.s.</sub> 1 kV

Isolation group IIIa (175 ≤ CTI < 400)

# Material properties

| Material (insert)                         | Liquid crystal polymer (LCP)                             |
|---|--|
| Colour (insert)                           | Black  |
| Material (contacts)                       | Copper alloy   |
| Surface (contacts)                        | Sn over Ni Termination side<br>Au over Pd/Ni Mating side |
| Material flammability class acc. to UL 94 | V-0  |
| RoHS                                      | compliant  |
| ELV status                                | compliant  |
| China RoHS                                | е  |
| REACH Annex XVII substances               | Not contained  |
| REACH ANNEX XIV substances                | Not contained  |
| REACH SVHC substances                     | Not contained  |
| California Proposition 65 substances      | Not contained  |

## Specifications and approvals

| Specifications | IEC 60603-13                      |
|----------------|-----------------------------------|
| UL / CSA       | UL 1977 ECBT2.E102079             |
|                | CSA-C22.2 No. 182.3 ECBT8.E102079 |

#### Commercial data

| Packaging size                 | 160                                      |
|--------------------------------|--|
| Net weight                     | 8.82 g                                   |
| Country of origin              | China                                    |
| European customs tariff number | 85366990                                 |
| GTIN                           | 5713140212381                            |
| eCl@ss                         | 27460201 PCB connector (board connector) |