


Han Domino DD cube, crimp (M.1)



Part number	09 14 906 1001
Specification	Han Domino DD cube, crimp (M.1)
HARTING eCatalogue	https://b2b.harting.com/09149061001

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] Domino DD Cube
Size of the module	Domino module
Description of the module	Small tab
Version	
Termination method	Crimp termination
Gender	Male
Number of contacts	6
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 2.5 mm²
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500
Mating cycles with other HMC components	≥10,000

Page 1 / 2 | Creation date 2022-10-13 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

GTIN

eCl@ss

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Specifications and approvals	
Specifications	IEC 60664-1 IEC 61984
Commercial data	
Packaging size	2
Net weight	4.6 g
Country of origin	Romania
European customs tariff number	85389099

5713140185135

27440217 Module for industrial connectors (power/signals)