

Han Domino DD cube, crimp (F.2)



Part number	09 14 906 2101
Specification	Han Domino DD cube, crimp (F.2)
HARTING eCatalogue	https://b2b.harting.com/09149062101

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] Domino DD Cube
Size of the module	Domino module
Description of the module	Large Tab

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	6
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 2.5 mm ²
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500
Mating cycles with other HMC components	≥10,000



Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	
	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	2
Net weight	5.48 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140185166
eCl@ss	27440217 Module for industrial connectors (power/signals)