HellermannTyton

		Material Datasheet	03.04.2023
TAG26TD6-896-WHCL Article Number 596-26896			H2
Material: Colour:		Type 896, Vinyl (896) White (WH), Transparent (CL)	
Operating Temperature : Curing Temperature:		-40 °C to +80 °C from +10 °C	
Bundle Ø min.:		1.50 mm	
Bundle Diameter max (Metric):		3.00 mm	
Self adhesiv	ve (Yes/No):	Yes	
Width (W):		12.70 mm	
Height (H):		9.52 mm	
Height (H2):		19.05 mm	
Width of Lin		85.00 mm	
Labels per F	Row:	6 pcs.	
Thickness o	f Foil:	80 µm	Test Method ASTM D3652-83
Adhesive:		Acrylic	
Initial tack:		110 g/cm ²	ASTM D2979-71
Peel strengt	h:	550 N/m	PSTC 7
Shear streng	gth:	120 h	FINAT FTM 8

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved

HellermannTyton

	Material Datasheet	03.04.202
Print Method: Application Tool: Recommended Ribbon Type:	Thermal transfer print TT431, TT4030 TT932DOUT	
Shelf Life: Storage Temperature: Storage conditions:	Minimum 1 year upon receipt / maximal 2 years after production date. +21 °C 50% relative humidity., The storage in the original packaging is recommended., Please avoid warehousing under impacts such as high humidity, heat and coldness.	
Application Method:	The functionality and durability of the labels can be negatively affected if improperly processed or applied. All surfaces to be bonded must be clean, dry as well as free from dust and grease. Avoid touching the adhesive surface of the label as this could impair the application performance.	
RoHS		

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved