NEUTRIK



NC10FDX-TOP

8+2 pole female chassis connector, TRUE OUTDOOR PROTECTION (TOP)

The X-TOP series is a "heavy-duty" XLR cable connector for outdoor use. Outdoor protected by mating with related cable connector of the XLR TOP range (IP65).

Gold contacts are standard.

Features & Benefits

- Heavy-duty sealed XLR connector range for harsh and demanding environment.
- High impact UV-resistant materials.
- Receptacle with duplex ground contact for excellent signal integrity.
- Superior ruggedness compared to RJ45 type connectors.

- Outdoor protection according to IP65.
 Maintains sealing when in use and when disconnected.
- D-size housing provides installation compatibility with industry standard D mounting dimensions.
- Suitable for data offering CAT 5e performance and power up to 16 A and 50 V - exceeds PoE+ capabilities.
- IEC 61984 certified

NEUTRIK

Technical Information

Product	
Title	NC10FDX-TOP
Connection type	XLR
Gender	Female

Electrical	
Contact resistance	≤ 3 mΩ
Dielectric strength	1 kVdc
Insulation resistance	> 10 GΩ (initial)
Number of electronical contacts	8 + 2
Rated current per contact	16 A (power pins), 3 A (data pins)
Rated voltage	50 V
Cable shield - shell connection	choosable
Transmission performance	CAT 5e

NEUTRIK

Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiring	Solder contacts
Wiring Size	<2.5 mm²/<1 mm² (8 x 24 AWG + 2 x 16AWG)
Locking device	Latch lock
Mounting direction	Front mounting
Chassis shape	D

Material	
Contact plating	Au over Ni
Contacts	Brass
Insert	Polyamide
Locking element	Stainless steel
Gasket	TPE
Shell	Polyamide



Environmental

Linvironmentat	
Flammability acc. to UL94	V-0
Standard compliance	IEC 61076-2-103
Protection class according to IEC 60529	IP 65
Solderability acc. to	IEC 60068-2-20
Temperature range	-30 °C to +80 °C
Pollution degree acc. to IEC 60664-1	II