



# Time-of-Flight 8x8 multizone ranging sensor with 90° FoV expansion board based on the VL53L7CX for STM32 Nucleo







#### **Product summary** Time-of-Flight 8x8 multizone ranging sensor with 90° FoV expansion X-NUCLEO-53L7A1 board based on the VL53L7CX for STM32 Nucleo Time-of-Flight sensor software X-CUBE-TOF1 expansion for STM32Cube STM32 Nucleo-64 development NUCLEO-F401RE board with STM32F401RE MCU Personal Electronics - Audio and Video/Gaming and **Applications** Drones/Virtual -Augmented Reality/

#### **Features**

- VL53L7CX Time-of-Flight 8x8 multizone ranging sensor with 90° FoV
- Accurate absolute ranging distance, independent of the reflectance of the target
- Up to 350 cm ranging
- Histogram-based technology
- Multiobject detection capability
- 0.25, 0.5, and 1 mm spacers to simulate air gaps
- · One cover glass to protect the sensor from dust
- · Compatible with STM32 Nucleo development boards
- Equipped with Arduino® UNO R3 connectors
- Full system software supplied, including code examples and graphical user interface
- RoHS, CE, UKCA, and China RoHS compliant

#### **Description**

The X-NUCLEO-53L7A1 is an expansion board for any STM32 Nucleo board equipped with the Arduino® R3 connectors. It provides a complete evaluation kit that allows you to learn, evaluate, and develop applications using the VL53L7CX Time-of-Flight 8x8 multizone ranging sensor with 90° FoV.

The expansion board is delivered with a cover glass holder in which you can fit three different spacers of 0.25, 0.5, and 1 mm height below the cover glass to simulate various air gaps.

Several ST expansion boards can be stacked through the Arduino® connectors, which allow, for example, the development of VL53L7CX applications with Bluetooth® Low Energy or Wi-Fi interfaces.

Wearable



## 1 Ordering information

Table 1. Ordering information

Order code	Core product
X-NUCLEO-53L7A1	VL53L7CX

DB4808 - Rev 1 page 2/15



### 2 Laser safety considerations

The VL53L7CX contains a laser emitter and the corresponding drive circuitry.

The laser output is designed to remain within Class 1 laser safety limits under all reasonable foreseeable conditions, including single faults, in compliance with the IEC 60825-1:2014 (third edition).

The laser output remains within Class 1 limits as long as you use the STMicroelectronics recommended device settings and respect the operating conditions specified in the data sheet.

The laser output power must not be increased and no optics should be used with the intention of focusing the laser beam.

Figure 1. Class 1 laser product label



DB4808 - Rev 1 page 3/15



### 3 Optional VL53L7CX breakout boards

The SATEL-VL53L7CX is designed to connect remotely the VL53L7CX sensor to any type of electronic controller.

**Attention:** 

The VL53L7CX is delivered with a liner to prevent potential foreign material from piercing the module holes during the assembly process. Remove this liner before use.

The VL53L7CX breakout boards can be directly plugged onto the X-NUCLEO-53L7A1 expansion board through two six-pin connectors (Figure 2) or through flying wires (Figure 3).

You can buy the breakout boards separately as SATEL-VL53L7CX. This order code package includes two breakout boards.

Figure 2. SATEL-VL53L7CX breakout boards connected to the X-NUCLEO-53L7A1 expansion board



DB4808 - Rev 1 page 4/15



Figure 3. VL53L7CX mini PCB flying wires connection to X-NUCLEO-53L7A1 expansion board



DB4808 - Rev 1 page 5/15



### 4 Simplified schematics

ARDUINO HEARDERS **NUCLEO-F401RE** ARDUINO / F401RE CN5 D15 / PB8 10 D14 / PB9 9 AVDD 8 GND\_7 D13 / PA5 6 D12 / PA6\_5 I2C\_RST\_R D7 / PA8 8 I2C\_RST\_L D6 / PB10 7 SDA INT\_C LPn\_C SCL U2 I2C\_RST\_C D4 / PB5 \_5 LPn\_R +3V3 VL53L7CX D3 / PB3 4 I2C\_RST\_C LPn\_C D2 / PA10 3 INT\_R GŇD D1 / PA2 2 D0 / PA3 1 J5\_Right Satellite Right header IOREF 2 GND J5\_Left Satellite GND 6 Left header GND 7 VIN 8 GND A0 / PA0 1 U1 A1 / PA1 2 +3V3 Voltage INT\_C A2 / PA4 3 Regulator PWR\_EN\_C A3 / PBO 4 A4 / PC1 5 PWR\_EN\_R A5 / PCO 6

Figure 4. X-NUCLEO-VL53L7CX simplified schematic

DB4808 - Rev 1 page 6/15




Figure 5. SATEL-VL53L7CX simplified schematic

DB4808 - Rev 1 page 7/15









Figure 7. X-NUCLEO-53L7A1 circuit schematic (2 of 5)



AVDD and IOVDD power supply for main sensor
Max Current = 60 mA + 90 mA = 150 mA

Power = 1.7 V x 150 mA = 255 mW

Satellite boards supplied directly from host power supplies







Figure 8. X-NUCLEO-53L7A1 circuit schematic (3 of 5)


Nucleo Arduino Connectors



























### 6 Board versions

Table 2. X-NUCLEO-53L7A1 versions

PCB version	Schematic diagrams	Bill of materials	
X\$NUCLEO-53L7A1- (1)	X\$NUCLEO-53L7A1- schematic diagrams	X\$NUCLEO-53L7A1-bill of materials	

<sup>1.</sup> This code identifies the X-NUCLEO-53L7A1 expansion board first version. It is printed on the board PCB.

DB4808 - Rev 1 page 13/15



### **Revision history**

Table 3. Document revision history

Date	Revision	Changes
26-Sep-2022	1	Initial release.

DB4808 - Rev 1 page 14/15



#### **IMPORTANT NOTICE - READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics - All rights reserved

DB4808 - Rev 1 page 15/15