Electronic circuit breaker; 1-channel; 24 VDC input voltage; 0.5 A; Signal contact




https://www.wago.com/787-2861/050-000















https://www.wago.com/787-2861/050-000





Dimensions in mm

Features:

- · Space-saving ECB with one channel
- Reliably and safely trips in the event of an overload and short circuit on the secondary side
- Switch-on capacity > 50,000 μF
- Minimizes wiring via two voltage outputs and maximizes commoning options on both input and output sides (e.g., commoning of the output voltage on 857 and 2857 Series devices)
- Status signal as single or group message
- · Reset, switch on/off via remote input or local switch
- · Prevents power supply overload due to total inrush current thanks to time-delayed switching on during interconnected operation

echnical data			
nput		Output	
Nominal input voltage U _{i nom}	DC 24 V	Total number of channels (module)	1
Input voltage range DC 18 30 V	Nominal output voltage $U_{o nom}$	1 x DC 24 V	
	Output voltage range	DC 18 30 V (U _e - voltage drop)	
	Voltage drop	≤ 50 mV	
	Nominal output current I _{o nom}	1 x 0.5 A (fixed setting)	
	Switch-on capacity		
	Switch-on behavior	Time-delayed channel switching (load dependent, min. 170 ms/max. 500 ms/	
	Active current limitation	No	

Signaling and communication	
Signaling	1 x Status LED (green/yellow/red/blue) 1 x Control input 1 x Active signal output (U _i , max. 4 mA)
Operation status indicator	Green LED (channel OK) Red LED (tripped channel)
Remote input	18 30 VDC signal, switches on/off and resets the channel

Circuit protection	
Internal fuse	T 15 A

Efficiency/power losses	
Power loss P _I	≤ 0.36 W
Efficiency (typ.)	99 %

Data Sheet | Item Number: 787-2861/050-000 https://www.wago.com/787-2861/050-000



Safety and protection	
Isolation voltage (connectors – housing)	DC 0.5 kV
Protection class	III
Protection type	IP20; per EN 60529
Reverse voltage protection	No
Pollution degree	2
Transient suppression (primary)	Suppressor diode (33 V)
Parallel operation of single channels	Not permitted
Series operation	No
MTBF	1,263,074 h (per MIL-HDBK-217F2)

Connection data	
Number of jumper slots	8
Connection technology	Push-in CAGE CLAMP®
WAGO connector	WAGO 857 Series
Solid conductor	0.08 2.5 mm ² / 28 14 AWG
Fine-stranded conductor	0.34 2.5 mm ² / 22 14 AWG
Strip length	9 10 mm / 0.35 0.39 inches

Physical data	
Width	6 mm / 0.236 inches
Height from upper-edge of DIN-rail	97.8 mm / 3.85 inches
Depth	94 mm / 3.701 inches

Mechanical data	
Mounting type	DIN-35 rail

Material data	
Fire load	0 MJ
Weight	34 g

Environmental requirements	
Ambient temperature (operation)	-25 +70 °C (Device starts at -40 °C (type-tested))
Ambient temperature (storage)	-40 +85 °C
Relative humidity	10 95 % (no condensation permissible)
Derating	No derating

Standards and specifications	
Conformity marking	CE
Standards/specifications	EN 61000-6-2 EN 61000-6-3 UL 61010-2-201 DNV

https://www.wago.com/787-2861/050-000



Commercial data	
ETIM 8.0	EC001440
ETIM 7.0	EC001440
PU (SPU)	1 pcs
Packaging type	Bag
Country of origin	CN
GTIN	4066966241686
Customs tariff number	85363010900

Approvals / Certificates

General approvals



Approvai	Standard	Certificate Name
EAC Brjansker Zertifizierungs- stelle	TP TC 020/2011	EAC_Certificate_RU_C- DE.AM02.B.00115_19
UL Underwriters Laboratories Inc. (ORDINARY LOCATI-	UL 2367,UL 61010-2-201	E175199 Vol.3 Sec.2 Series 0787 ECB

Approvals for marine applications



Approval	Standard	Certificate Name
DNV DNV Germany GmbH	DNV-CG-0339,Aug.2021	TAA00001D1

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 787-2861/050-000



Documentation

Manual

Product Manual Electronic Circuit Breaker

V 1.3.1

16.12.2019

pdf 2933.00 KB

Instruction Leaflet

Electronic Circuit Brea-V 2.0.0

27.02.2023

pdf 3477.29 KB



CAD/CAE-Data

CAD data

2D/3D Models 787-2861/050-000



1 Compatible Products

1.1 Optional Accessories

1.1.1 Ferrule

https://www.wago.com/787-2861/050-000



1.1.1.1 Ferrule

Item No.: 216-241

Ferrule; Sleeve for 0.5 mm2 / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white

Item No.: 216-242

Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

Item No.: 216-243

Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red

Item No.: 216-244

Ferrule; Sleeve for 1.5 mm2 / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

1.1.2 Jumper

1.1.2.1 Jumper



Item No.: 859-410/000-006

Jumper; for jumper slot; 10-way; insulated; blue

distribite

Item No.: 859-410

Jumper; for jumper slot; 10-way; insulated; light gray

Item No.: 859-410/000-005

Jumper; for jumper slot; 10-way; insulated; red



Item No.: 859-410/000-029

Jumper; for jumper slot; 10-way; insulated; yellow



Item No.: 859-402/000-006

Jumper; for jumper slot; 2-way; insulated; blue

Item No.: 859-402

Jumper; for jumper slot; 2-way; insulated; light gray

Item No.: 859-402/000-029

Jumper; for jumper slot; 2-way; insulated; yellow

Item No.: 859-403/000-006

Jumper; for jumper slot; 3-way; insulated; blue



Item No.: 859-403

Jumper; for jumper slot; 3-way; insulated; light gray

Item No.: 859-403/000-005

Jumper; for jumper slot; 3-way; insulated;

Item No.: 859-403/000-029

Jumper; for jumper slot; 3-way; insulated; yellow

Item No.: 859-404/000-006

Jumper; for jumper slot; 4-way; insulated; blue



Item No.: 859-404

Jumper; for jumper slot; 4-way; insulated; light gray

Item No.: 859-404/000-005

Jumper; for jumper slot; 4-way; insulated; red

Item No.: 859-404/000-029

Jumper; for jumper slot; 4-way; insulated; yellow

Item No.: 859-405/000-006

Jumper; for jumper slot; 5-way; insulated; blue



Item No.: 859-405

Jumper; for jumper slot; 5-way; insulated; light gray

Item No.: 859-405/000-005 Jumper; for jumper slot; 5-way; insulated;

Item No.: 859-405/000-029 Jumper; for jumper slot; 5-way; insulated;

Item No.: 859-406/000-006

Jumper; for jumper slot; 6-way; insulated; blue



vellow

Item No.: 859-406

Jumper; for jumper slot; 6-way; insulated; light gray

Item No.: 859-406/000-005

Jumper; for jumper slot; 6-way; insulated; red

Item No.: 859-406/000-029

Jumper; for jumper slot; 6-way; insulated; signal yellow

Item No.: 859-407/000-006

Jumper; for jumper slot; 7-way; insulated;



Item No.: 859-407 Jumper; for jumper slot; 7-way; insulated; light gray

blue



Jumper; for jumper slot; 7-way; insulated;

Item No.: 859-407/000-005

Jumper; for jumper slot; 7-way; insulated; red

Item No.: 859-407/000-029

yellow

Item No.: 859-408/000-006

Jumper; for jumper slot; 8-way; insulated; blue



Item No.: 859-408

Jumper; for jumper slot; 8-way; insulated; light gray

Item No.: 859-408/000-005

Item No.: 859-408/000-029

Jumper; for jumper slot; 8-way; insulated; yellow

Item No.: 859-409 Jumper; for jumper slot; 9-way; insulated; light gray

Jumper; for jumper slot; 8-way; insulated; red

Item No.: 859-409/000-006

Jumper; for jumper slot; 9-way; insulated; blue



Item No.: 859-409/000-005

Jumper; for jumper slot; 9-way; insulated;

Item No.: 859-409/000-029

Jumper; for jumper slot; 9-way; insulated;

1.1.3 Marking

https://www.wago.com/787-2861/050-000



1.1.3.1 Marker







Item No.: 793-5501

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; white

Item No.: 793-502


WMB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type; white

Item No.: 793-566

WMB marking card; as card; MARKED; 1 ... 50 (2x); not stretchable; Horizontal marking; snap-on type; white

Item No.: 793-503

WMB marking card; as card; MARKED; 11 ... 20 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-504 WMB marking card; as card; MARKED; 21 ... 30 (10x); not stretchable; Horizontal marking; snap-on type; white

Item No.: 793-505 Item No.: 793-506

WMB marking card; as card; MARKED; 31 ... 40 (10x); not stretchable; Horizontal marking; snap-on type; white

WMB marking card; as card; MARKED; 41 ... 50 (10x); not stretchable; Horizontal marking; snap-on type; white

Item No.: 793-501

WMB marking card; as card; not stretchable; plain; snap-on type; white

Item No.: 2009-115 WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snapon type; white

1.1.3.2 Marking strip



Item No.: 2009-110

Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

1.1.4 Tool

1.1.4.1 Operating tool



Item No.: 210-720

Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at:: www.wago.com

Page 6/6 Version 03.04.2023