


#### Key Features Type

**Type RLC73 Series** 

Resistance values from 10mΩ

Low TCR version available for many values

High purity alumina substrate for high power dissipation



RoHS Compliance

**MSL Level 1** 

TE Connectivity (TE) introduces a new range of current sense resistors to be offered as a low-cost alternative to legacy solutions characterised by noble metal construction (Ag /Pd / RU) and terminations. RLC73 series has the additional benefit of being fully RoHS compliant, and features power ratings up to 2W and TCRs down to 50ppm/°C in the high-power version. Furthermore, these resistors satisfy the demand for low ohmic shunt resistors to act as current sensors towards ICs for battery charge management and low voltage power supplies produced by global semiconductor manufacturers.

#### **Applications**

Power management applications

### Characteristics - Electrical - Standard

Switching				,		1			1
	Type	Size	Power	Operating	Max	Resistance Ra	nge (mΩ)		TCR
power supply			Rating	Temp.	Operating	±1%	±2%	150/	(PPM/C°)
			(W)	Range	Current (A)			±5%	
Over current						E24 & E96*	E24	E24	
protection in						20 – 50		0 – 50	±600
audio	RLC73	0805	0.125		2.5	51 – 100	_	- 100	±400
auulo	ILEC/ 5	0003	0.123		2.3	102 – 196	110	0 – 180	±300
applications						200 – 1000	200	- 1000	±200
• •	RLC73	1206	0.25		5.0	10 – 20	10 – 20	1	±600
Voltage						22 – 50	22 – 50	)	±400
•						51 – 91	51 – 91		±300
regulation						100 – 1000	100 – 1	.000	±200
module (VRM)	RLC73	1210	0.5		7.07	10 – 20	10 – 20	1	±600
medale (Timi)				-55 ~ 155°C		22 – 50	22 – 50	1	±400
DC DC						51 – 91	51 – 91		±300
DC-DC						100 – 1000	100 – 1	.000	±200
converter,	RLC73	2010	0.75		8.66	10 – 20	10 – 20	)	±600
battery pack,						22 – 50	22 – 50		±400
battery pack,						51 – 91	51 – 91		±300
charger,						100 – 1000	100 – 1	.000	±200
adaptor	RLC73	2512	1		10.0	10 – 20	10 – 20	1	±600
auaptoi						22 – 50	22 – 50	1	±400
						51 – 91	51 – 91		±300
Disk driver						100 – 1000	100 – 1	.000	±200

<sup>\*</sup>The nominal resistance value range for less than  $100m\Omega$  is in E24 series

te.com 1773269-3 Rev. C 04/2023




# **Characteristics – Electrical – High Power**

Туре	Size	Power	Operating Max Temp. Operating Range Current (A)		Resistance Ra	nge (mΩ	2)	TCR
		Rating (W)			±1% E24 & E96*	±2% E24	±5% E24	(PPM/C°)
RLC73P	0805	0.25		2.21	20 – 50 51 – 91	20 – 50 51 – 91		±600 ±400
RLC/3P	0803	0.23		1.58	100 – 196 200 – 499 500 - 1000	100 - 1 200 - 2 500 - 1	170	±100 ±75 ±50
RLC73P	1206	0.5	-55 ~ 155°C	7.07	10 – 20 22 – 50 51 – 68	10 - 20 22 - 50 51 - 68	)	±600 ±400 ±300
RLC73P	1206	1		-55 ~ 155°C	3.65	75 – 100 102 – 147 150 - 1000	75 – 10 110 – 1 150 - 1	L40
RLC73P	1210	0.75		8.66	10 – 20 22 - 47	10 – 20 22 - 47	-	±600 ±400
KLC/3P	1210	0.75		3.87	50 – 147 150 -1000	50 – 14 150 - 1		±75 ±50
RL73CP	2010	1		10.0	10 – 20 22 - 47	10 – 20 22 - 47		±600 ±400
NL/3CP	KL/3CP 2010 1	1		4.47	50 – 147 150 - 1000	50 – 14 150 - 1		±75 ±50
				14.1	10 – 18	10 - 18		±600
RL73CP	2512	2		10.0	20 – 47	20 - 47		±100
AL/3CP	2312			6.32	50 – 147 150 - 1000	50 – 14 150 - 1		±75 ±50

<sup>\*</sup>The nominal resistance value range for less than  $100 m\Omega$  is in E24 series

# **Construction and Dimensions**




- Alumina Substrate
- ② Bottom Electrode
  ③ Top Electrode
- (4) Edge Electrode
- S Barrier Layer
- 6 External Electrode
  7 Resistor Layer
- 8 Overcoat

Туре	Size	L (mm) ±0.10	W (mm)	T (mm)	D1 (mm)	D2 (mm)	Weight (g) / K pcs
RLC73 / RLC73P	0805	2.00	1.25 ±0.10	0.55 ±0.10	0.30 ±0.20	0.40 ±0.25	4.6
RLC73 / RLC73P	1206	3.10	1.55 ±0.10	0.55 ±0.10	0.50 ±0.30	0.40 ±0.25	8.7
RLC73 / RLC73P	1210	3.10	2.60 ±0.15	0.55 ±0.10	0.50 ±0.30	0.50 ±0.25	16.0
RLC73 / RLC73P	2010	5.00	2.50 ±0.15	0.60 ±0.15	0.60 ±0.30	0.50 ±0.25	23.7
RLC73	2512		3.10	0.60 ±0.10		0.55 ±0.25	40.0
	2512 10-18mΩ	6.35	±0.15	0.74 ±0.10		2.10 ±0.10	53.6
RLC73P	20 – 43mΩ	6.45	3.25 ±0.15	0.85 ±0.10	0.60 ±0.30	0.60 ±0.30	65.3
	47mΩ 51 – 1000mΩ	6.35	3.10 ±0.15	0.74 ±0.10		210 ±0.10	53.6

te.com 1773269-3 Rev. C 04/2023




# **Derating Curve**



# **Soldering Profile**

#### Soldering Condition (Ref. IPC/JEDEC J-STD-020 & J-STD-002)



Profile Feature	Pb-Free Assembly
Preheat	
Min. Temperature (Tsmin)	150 °C
Max Temperature (Tsmax)	200 °C
Preheating time (ts) from (Tsmin to Tsmax)	60-120 seconds
Ramp-up rate (TL to Tp)	3°C/second max.
Liquidous temperature (TL)	217 °C
Time (tL) maintained above TL	60-150 seconds
Min. Peak temperature (Tp min)	235°C
Max. Peak temperature (Tp max)	260°C
Time (tp) within 5 °C of the specified classification temperature (Tc)	30 seconds max.
Ramp-down rate (Tp to TL)	6°C/second max.
Time 25 °C to peak temperature	8 minutes max.



### **Environmental Characteristics**

Item	Requirement	Test Method
Temperature Coefficient	As Spec.	JIS-C-5201-1 4.8
of resistance (T.C.R.)	·	IEC-60115-1 4.8
(**************************************		At 25°C/-55°C and 25°C/+125°C,
		25°C is the reference temperature
		Low TCR: At 25°C/+125°C, 25°C is
		the reference temperature
	±(0.5%+0.05Ω)	JIS C 5201-1 4.13
	•	IEC 60115-1 4.13
Short Time Overload	±(1.0%+0.05Ω) For ≦50mR & all High	RCWV*2.5 or Max. Overload
Short Time Overload	· ·	Voltage whichever is lower for 5
	power	
Landation Books and	2100	seconds
Insulation Resistance	≧10G	JIS-C-5201-1 4.6
		IEC-60115-1 4.6
		Max. Overload Voltage for 1
		minute
	±(1.0%+0.05Ω)	JIS-C-5201-1 4.25
Endurance	±(2.0%+0.05Ω)	IEC-60115-1 4.25.1
Endurance	For ≦50mΩ & all High	70±2°C, RCWV for 1000 hrs with
	power	1.5 hrs "ON" and 0.5 hr "OFF"
	±(0.5%+0.05Ω)	JIS-C-5201-1 4.24
	±(1.0%+0.05Ω)	IEC-60115-1 4.24
Damp Heat with Load	For ≦50mΩ & all High	40±2°C, 90~95% R.H., RCWV for
	power	1000 hrs with 1.5 hrs "ON" and
	•	0.5 hr "OFF"
	±(1.0%+0.05Ω)	JIS-C-5201-1 4.23
Doublest	±(2.0%+0.05Ω)	IEC-60115-1 4.23.2
Dry Heat	For ≦50mΩ & all High	at +155°C for 1000 hrs
	power	
Bending Strength	±(1.0%+0.05Ω)	JIS-C-5201-1 4.33
	,	IEC-60115-1 4.33
		Bending once for 60 seconds with
		3mm 2010, 2512 sizes: 2mm
Solderability	95% min. coverage	JIS-C-5201-1 4.17
Solderdomey	33% mm. coverage	IEC-60115-1 4.17
		245±5°C for 3 seconds
Posistance to Soldering	±(0.5%+0.05Ω)	JIS-C-5201-1 4.18
Resistance to Soldering Heat	±(0.3/0±0.0322)	IEC-60115-1 4.18
Heat		260±5°C for 10 seconds
Į Į		I ZOUIS CIUI IU SECUIUS
Voltage Droof	No brookdours as	
Voltage Proof	No breakdown or	JIS-C-5201-1 4.7
Voltage Proof	No breakdown or flashover	JIS-C-5201-1 4.7 IEC-60115-1 4.7
Voltage Proof		JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating
Voltage Proof		JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V
	flashover	JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V CSN06/13/10:400V; CSN12:500V
Voltage Proof  Leaching	flashover  Individual leaching area	JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V CSN06/13/10:400V; CSN12:500V JIS-C-5201-1 4.18
	flashover  Individual leaching area ≤5%	JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V CSN06/13/10:400V; CSN12:500V JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1
Leaching	flashover  Individual leaching area ≤5%  Total leaching area ≤10%	JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V CSN06/13/10:400V; CSN12:500V JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1 260±5°C for 30 seconds
	flashover  Individual leaching area ≤5%	JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V CSN06/13/10:400V; CSN12:500V JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1 260±5°C for 30 seconds JIS-C-5201-1 4.19
Leaching	flashover  Individual leaching area ≤5%  Total leaching area ≤10%	JIS-C-5201-1 4.7 IEC-60115-1 4.7 1.42 times Max. Operating Voltage for 1 minute CSN05:300V CSN06/13/10:400V; CSN12:500V JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1 260±5°C for 30 seconds

RCWV(Rated Continuous Working Voltage)=V(P\*R) or Max. Operating Voltage whichever is lower.


Storage Temperature: 15~28°C; Humidity < 80%RH

Shelf Life: 2 years from production date




# **Packaging**

# Reel Dimensions (mm)



Size	Туре	Qty	Tape	Reel	øΑ	øΒ	øС	W	Т
			Width	Diameter	(mm)	(mm)	(mm)	(mm)	(mm)
0805	Paper	5K /	8mm	7 inch	178.5	60	13.0	9.0	12.5
1206		1K			±1.5	+0/-1	±0.2	±0.5	±0.5
1210									
2010	Embossed	4K /	12mm	7 inch	178.5	60	13.0	13.0	15.5
2512		1K			±1.5	+0/-1	±0.5	±0.5	±0.5
2512	Embossed	2K/	12mm	7 inch	178.5	60	13.0	13.0	15.5
2W		1K			±1.5	+0/-1	±0.5	±0.5	±0.5

# **Paper Tape Specifications**




Size	Α	В	W	E	F	Po	P <sub>1</sub>	P <sub>2</sub>	$\phi D_o$	T
	(mm)	(mm)	(mm)	(mm)						
	±0.10	±0.20	±0.20	±0.10	±0.05	±0.10	±0.05	±0.05	+0.1	±0.1
									-0	
0805	1.60	2.40	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85
1206	1.90	3.50	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85
1210	2.90	3.50	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85

te.com 1773269-3 Rev. C 04/2023




### **Embossed plastic tape specifications**



Size	Α	В	W	E	F	Po	P <sub>1</sub>	P <sub>2</sub>	øDο	T
	(mm)	(mm)	(mm)	(mm)						
2010	2.80	5.40	12.0	1.75	5.5	4.00	4.00	2.00	1.50	1.00
2010	±0.10	±0.20	±0.30	±0.10	±0.05	±0.05	±0.10	±0.05	±0.10	±0.20
2512	3.50	6.70	12.0	1.75	5.5	4.00	4.00	2.00	1.50	1.00
2512	±0.10	±0.10	±0.30	±0.10	±0.05	±0.05	±0.10	±0.05	±0.10	±0.20
2512										
2W	3.50	6.70	12.0	1.75	5.5	4.00	4.00	2.00	1.50	1.45
20 -	±0.10	±0.10	±0.30	±0.10	±0.05	±0.10	±0.10	±0.05	±0.10	±0.20
49mΩ										
2512										
2W	3.38	6.68	12.0	1.75	5.5	4.00	4.00	2.00	1.55	1.45
10 –	±0.10	±0.10	±0.30	±0.10	±0.10	±0.10	±0.10	±0.05	±0.05	±0.20
18mΩ	10.10	±0.10	±0.30	10.10	±0.10	10.10	10.10	10.03	±0.03	±0.20
>49mΩ										

### **Recommended Land Pattern**



Size	Α	В	С
	(mm)	(mm)	(mm)
			±0.2
0805	1.00	1.00	1.35
1206	2.00	1.15	1.70
1210	2.00	1.15	2.50
2010	3.60	1.40	2.50
2512	4.90	1.60	3.20
2512 2W	4.00	1.00	2.20
20 - 43mΩ	4.90	1.60	3.20
2512 2W			
$10-18m\Omega$	1.00	3.55	3.20
≥47mΩ			



# **Marking**

4 digit marking for all models

Example	Resistance	10mΩ	51mΩ	100mΩ	549mΩ
	Marking	R010	R051	R100	R549

#### **How To Order**

RLC73	K	2H	R357	F	TE
Common Part	T.C.R	Size	Resistance Value	Tolerance	Packaging
RLC73 – Standard Power	D - 50ppm W - 75ppm H - 100ppm	2A - 0805 2B - 1206 2E - 1210	R010 - 10mΩ R051 - 51mΩ R100 -	F – 1% G – 2% J – 5%	TDF - 1K RL (all models)
RLC73P – High Power	K - 200ppm N - 300ppm M - 400ppm V - 600ppm	2H - 2010 3A - 2512	100mΩ		TD - 5K RL (0805, 1206, 1210) TE - 4K RL
					(2010, 2512) TDG - 2K RL (2512 2W)

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this data sheet are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.