


IEC Appliance Plug J, 70°C

NEW

Snap-in mounting



Screw-on mounting

**Description**

- Panel Mount:
Snap-in or screw-on mounting, from front side
- 1 Function:
Outlet, Pin temperature 70 °C Protection class I
- Solder terminals or quick connect terminals Substitute for type 0723

Characteristics

- Qualified for use in equipment according IEC/EN 60950

Other versions on request

- Other panel thickness
- For protection class II


WeblinksApprovals: <http://www.schurter.com/approvals>RoHS: <http://www.schurter.com/rohs>**Technical Data**

Ratings IEC	16 A / 250 VAC; 50 Hz
Ratings UL/CSA	20 A / 250 VAC; 60 Hz
Dielectric Strength	> 2.5 kVAC between L-N > 3 kVAC between L/N-PE (1 min/50 Hz)
Allowable Operation Temp.	-25 °C to 70 °C
Protection Class	Suitable for appliances with protection class I or II acc. to IEC 61140
Terminal	Solder terminals or quick connect terminals
Panel Thickness s	Screw-on: max 8 mm Mounting screw torque max 0.5 Nm Snap-in: 0.8 mm to 3 mm
Material: Housing	Thermoplastic, black, UL 94V-0


Appliance-Inlet /-Outlet	J acc. to IEC/EN 60320-2-2 UL 498, CSA C22.2 no. 42 (for cold condition) pin-temperature 70 °C, 16 A, Protection class I
--------------------------	---

Dimensions

Snap-in mounting



Screw-on mounting



Variants

Panel mounting	Panel Thickness s [mm]	Terminal	Protection Class	Order Number
Snap-in	1.5	Quick connect terminals 6.3 x 0.8	I	4797.0015
Snap-in	2	Quick connect terminals 6.3 x 0.8	I	4797.0020
Snap-in	2.5	Quick connect terminals 6.3 x 0.8	I	4797.0025
Snap-in	2	Solder terminals	I	4797.3020
Snap-in	2.5	Solder terminals	I	4797.3025
Screw-on	-	Quick connect terminals 6.3 x 0.8	I	4797.0000
Screw-on	-	Solder terminals	I	4797.3000

Packaging unit 50 Pcs

Accessory

Description



Assorted Covers



Cord retaining kits