

Agilent U3606A Multimeter | DC Power Supply

Data Sheet

The real two instruments in one box



Features

- Two independent instruments in one box
- 9 basic measurements as well as
 4-wire milliohm measurement and
 8 math functions
- Measurement speed: up to 37 readings/s
- Low error rate: up to 0.025% DCV accuracy
- 30-W dual-range power supply with remote sensing
- Excellent load regulation: up to 0.01%+3 mV
- OVP and OCP load protection
- Auto scan and ramp, and built-in 4.8 kHz square-wave generator
- USB-TMC488.2 and GPIB connectivity
- Kensington lock slot security

Pick both

Digital multimeter (DMM) and power supply? Simultaneous and independent? Small and cost-effective? Get all this and more in the Agilent U3606A multimeter | DC power supply. This convenient new hybrid combines a 5½-digit DMM and 30-W dual-range supply in a single unit. Operating simultaneously and independently, the instruments provide efficient, affordable testing while saving space on the bench or in a rack.

The 5.5-digit DMM

The 5.5-digit DMM includes nine essential multimeter capabilities as well as 4-wire milliohm measurement and eight built-in math functions. The DMM also provides a fast measurement speed of up to 37 readings/s, and a low error rate of up to 0.025% DCV accuracy.

Physical security and seamless system integration

Instruments may be at risk of theft or misplacement when left unattended on the bench. With the hybrid multimeter's rear Kensington lock slot, you can secure your instrument and be assured that it is where you expect it to be for your continued testing the next day. The rackmountable U3606A also enables seamless integration into your system via popular GPIB and USB-TMC488.2 interfaces, programmable with standard SCPI commands.



The 30-W DC power supply

The 30-W DC power supply provides a dual-range output of 30 V/1 A and 8V/3 A, with an excellent load regulation of up to 0.01%+3 mV. The power supply adds overvoltage and overcurrent load protection (OVP and OCP), a built-in square-wave generator, and auto scan and ramp for multi-level DC bias testing. Remote sensing capability further ensures accurate supply of power at load end.


Square-wave generator

Square-wave output is a unique function for many applications, such as pulse-width modulation (PWM) output, adjustable voltage control, and synchronous clock (baud rate generator). You can also use this function to check and calibrate flow-meter displays, counters, tachometers, oscilloscopes, frequency converters, frequency transmitters, and other frequency input devices. The U3606A's square-wave output provides selectable frequencies up to 4.8 kHz with variable duty cycles and amplitudes.


Sweep functions

Sweep functions in the U3606A are auto ramp and scan outputs for low-speed multilevel DC bias tests, such as margin tests, power cycling tests and relay control. Both functions are conveniently configurable from the front panel to sweep up to 100 steps for scan and 10,000 steps for ramp, programmable to 105% of full scale.

Auto scan output



Auto ramp output



Take a closer look



Figure 1 Front panel of the U3606A.




Figure 2 Rear panel of the U3606A.

Digital multimeter specifications

Specification assumptions:

- Specifications stated are after 60-minutes of warm-up and for 5½-digit resolution
- One-year calibration cycle, with calibration temperature of 18 °C 20 °C
- Operating temperature: 18 °C 28 °C (64.4 °F 82.4 °F)
- Accuracy is expressed as ±(% of reading + % of range)
- Temperature coefficient: Add [0.1 x (the specified accuracy) / °C] for 0 °C 18 °C and 28 °C 55 °C
- Relative humidity (RH) up to 80% at 30 °C, proportional to 50% for 30 °C 55 °C

DC specifications

Function	Range [1] Test current or		Accuracy	Temperature		
		burden voltage	24 hours ^[2] 23 °C ± 1 °C	90 days 23 °C ± 5 °C	1 year 23 °C ± 5 °C	coefficient 0 °C – 18 °C 28 °C – 55 °C
DC voltage	100.000 mV	-	0.012 + 0.008	0.015 + 0.008	0.025 + 0.008	0.0015 + 0.0005
	1.00000 V	-	0.012 + 0.005	0.015 + 0.005	0.025 + 0.005	0.0010 + 0.0005
	10.0000 V	-	0.012 + 0.005	0.015 + 0.005	0.025 + 0.005	0.0020 + 0.0005
	100.000 V	-	0.012 + 0.005	0.015 + 0.005	0.025 + 0.005	0.0015 + 0.0005
	1000.00 V	-	0.012 + 0.005	0.015 + 0.005	0.025 + 0.005	0.0015 + 0.0005
DC current [3]	10.0000 mA	< 0.2 V	0.05 + 0.015	0.05 + 0.015	0.05 + 0.015	0.0060 + 0.0005
	100.000 mA	< 0.2 V	0.05 + 0.005	0.05 + 0.005	0.05 + 0.005	0.0060 + 0.0005
	1.00000 A	< 0.3 V	0.05 + 0.007	0.05 + 0.007	0.15 + 0.007	0.0100 + 0.0005
	3.0000 A	< 0.7 V	0.05 + 0.007	0.05 + 0.007	0.15 + 0.007	0.0150 + 0.0010
Resistance [4]	100.000 Ω	0.83 mA	0.04 + 0.008	0.04 + 0.008	0.05 + 0.008	0.0050 + 0.0005
	1000.00 Ω	0.83 mA	0.04 + 0.005	0.04 + 0.005	0.05 + 0.005	0.0050 + 0.0005
	10.0000 kΩ	100 μΑ	0.04 + 0.005	0.04 + 0.005	0.05 + 0.005	0.0050 + 0.0005
	100.000 kΩ	10 μΑ	0.04 + 0.005	0.04 + 0.005	0.05 + 0.005	0.0050 + 0.0005
	1.00000 MΩ	900 nA	0.05 + 0.005	0.05 + 0.005	0.06 + 0.005	0.0050 + 0.0005
	10.0000 MΩ	205 nA	0.20 + 0.005	0.20 + 0.005	0.25 + 0.005	0.0150 + 0.0005
	100.000 MΩ	205 nA 10 MΩ	1.60 + 0.005	1.60 + 0.005	2.00 + 0.005	0.1500 + 0.0005
Continuity	1.0000 kΩ	0.83 mA	0.04 + 0.005	0.04 + 0.005	0.05 + 0.005	0.0050 + 0.0005
Diode [5]	1.0000 V	0.83 mA	0.04 + 0.005	0.04 + 0.005	0.05 + 0.005	0.0050 + 0.0005
Capacitance [6]	1.000 nF	0.75 μΑ	-	-	2.0 + 0.8	0.02 + 0.001
	10.00 nF	0.75 μΑ	-	-	1.0 + 0.5	0.02 + 0.001
	100.00 nF	8.3 μΑ	-	-	1.0 + 0.5	0.02 + 0.001
	1.000 μF	83 μΑ	-	-	1.0 + 0.5	0.02 + 0.001
	10.00 μF	83 μΑ	-	-	1.0 + 0.5	0.02 + 0.001
	100.0 μF	83 μΑ	-	-	1.0 + 0.5	0.02 + 0.001
	1000 μF	0.83 mA	-	-	1.0 + 0.5	0.02 + 0.001
	10000 μF	0.83 mA	-	-	2.0 + 0.5	0.02 + 0.001

^{[1] 20%} over-range on all ranges, except for 1000 V_{dc} range.

^[2] Relative to calibration standards.

^[3] Any current measurement greater than 500 mA will have a temporary thermo-effect. If you wish to measure a lower current or offset current immediately after a high-current measurement, ensure that the U3606A has cooled down.

^[4] Specifications stated are for 2-wire resistance measurements using Null math operation. Without Null, add a 0.2 Ω error. To eliminate noise interference which may be induced by the test leads, a shielded test cable is recommended for resistances above 100 k Ω .

^[5] Specifications stated are for the voltage measured at the input terminals only. The test current (1 mA) is typical. Variation in the current source will create some variation in the voltage dropped across a diode junction.

^[6] Specifications stated are for open test lead measurements with film capacitor or better, using Null math operation.

Low-resistance specifications

Range	Test current	Accuracy \pm (% of reading + % of range) ^[1] 1 year (23 °C \pm 5 °C)
100 m Ω	1.0000 A	0.25 + 0.05
1000 m Ω	0.1000 A	0.25 + 0.03
10 Ω	0.1000 A	0.25 + 0.03

^[1] Four-wire measurement method is used. Test current is sent from the FORCE terminals and resistance is measured at the SENSE terminals.

AC specifications

Function	Range [1]	Test current or	Accuracy \pm (% of reading + % of range)			Temperature
		burden voltage	24 hours ^[2] 23 °C ± 1 °C	90 days 23 °C ± 5 °C	1 year 23 °C ± 5 °C	coefficient 0 °C – 18 °C 28 °C – 55 °C
		20 Hz – 45 Hz	0.60 + 0.1	0.60 + 0.1	1.00 + 0.1 [4]	0.02 + 0.02
True rms AC	100.000 mV to 750.00 V	45 Hz – 10 kHz	0.16 + 0.1	0.16 + 0.1	0.20 + 0.1	0.02 + 0.02
voltage ^[3]		10 kHz – 30 kHz	0.80 + 0.1	0.80 + 0.1	1.00 + 0.1 ^[5]	0.02 + 0.02
		30 kHz – 100 kHz ^[6]	3.00 + 0.2	3.00 + 0.2	3.00 + 0.2 ^{[7][8]}	0.05 + 0.02
T 40	10,0000 4	20 Hz – 45 Hz	0.80 + 0.1	0.80 + 0.1	1.50 + 0.1	0.02 + 0.02
True rms AC current ^[10]	10.0000 mA to 3.0000 A	45 Hz – 1 kHz	0.40 + 0.1	0.40 + 0.1	0.50 + 0.1	0.02 + 0.02
		1 kHz – 10 kHz ^[9]	2.00 + 0.2	2.00 + 0.2	2.00 + 0.2	0.02 + 0.02

^{[1] 20%} over-range on all ranges, except for 750 $\ensuremath{V_{\text{ac}}}$ range.

^[2] Relative to calibration standards.

^[3] Specifications stated are for input signals greater than 5% of range.

^[4] For 750 V range, accuracy is specified for input less than 200 V_{rms}.

^[5] For 100 mV range, accuracy is specified at 1.5 + 0.3.

^[6] Add an error of 0.003% of full scale per kHz when input signal changes less than 10% of range.

^[7] For 100 mV range, accuracy is specified at 5 + 0.3.

^[8] For 750 V range, accuracy is specified for input less than 300 V_{rms} .

^[9] For 1 A and 3 A ranges, the accuracy is specified for frequencies less than 5 kHz.

^[10] Any current measurement greater than 500 mA will have a temporary thermo-effect. If you wish to measure a lower current or offset current immediately after a high-current measurement, ensure that the U3606A has cooled down.

^[11] Specifications for AC+DC measurement is the sum of the AC and DC accuracy. The frequency range is from 50 Hz for 5½-digit resolution and 225 Hz for 4½-digit resolution.

Frequency specifications

Function	Input range	Frequency range Min. input frequency = 1 Hz	Accuracy \pm (% of reading + % of range) 1 year (23 °C \pm 5 °C)	Temperature coefficient 0 °C – 18 °C 28 °C – 55 °C
	Voltage:	< 2 Hz	0.18 + 0.003	0.005
	100 mV to 750 V ^[1]	< 20 Hz	0.04 + 0.003	0.005
Frequency		20 Hz – 100 kHz	0.02 + 0.003	0.005
rrequency	quency	100 kHz – 300 kHz	0.02 + 0.003	0.005
	Current:	< 2 Hz	0.18 + 0.003	0.005
	10 mA to 3 A	< 20 Hz	0.04 + 0.003	0.005
		20 Hz – 10 kHz	0.02 + 0.003	0.005

Input range ^[2]	Minimum frequency sensitivity for voltage measurement (RMS sine wave)		
	20 Hz – 100 kHz	100 kHz – 300 kHz	300 kHz – 1 MHz
100 mV	50 mV	50 mV	0.5 V
1.0 V	100 mV	120 mV	0.5 V
10 V	1 V	1.2 V	-
100 V	10 V	12 V	-
750 V	100 V	-	-

Input range	Minimum frequency sensitivity for current measurement (RMS sine wave)	
	20 Hz – 100 kHz	
10 mA	1 mA	
100 mA	10 mA	
1 A	100 mA	
3 A	300 mA	

^[1] For 100 mV and 1 V ranges, the measurable frequency is up to 1 MHz at 0.5 V input signal.

Duty cycle and pulse width specifications

Function	Range	Resolution	Accuracy at full scale
Duty cycle	100.000% [1]	0.001%	0.3% + 0.2% per kHz
Pulse width	199.999 ms ^[2]	0.001 ms	Duty cycle/Frequency
r dioo widdi	1999.99 ms ^[2]	0.01 ms	Duty cycle/Frequency

^[1] The range is from {10 μ s × frequency × 100%} ~ {[1 – (10 μ s × frequency)] × 100%}. For example, a 1 kHz signal can be measured from 1% ~ 99%.

^[2] Maximum input for the specified accuracy = 10 x range or 1000 V_{dc} .

^[3] All frequency counters are susceptible to errors when measuring low-voltage, low-frequency signals. Shielding inputs from external noise pickup is critical for minimizing measurement errors.

^[2] The positive or negative pulse width must be greater than 10 μ s. The range of the pulse width is determined by the frequency of the signal.

Measurement speeds (typical)

Function	Rate	Reading speed ^[1] (readings/second)	Reading speed over USB ^[2] (readings/second)	Reading speed over GPIB ^[3] (readings/second)
DCltomo (10.\/)	Slow (5½ digits)	15	17	17
DC voltage (10 V)	Fast (4½ digits)	70	31	32
DC assument (1 A)	Slow (5½ digits)	15	17	17
DC current (1 A)	Fast (4½ digits)	70	37	36
A.C. volto no (10.)/ ot 1 l.l.l=\	Slow (5½ digits)	15	17	17
AC voltage (10 V at 1 kHz)	Fast (4½ digits)	70	31	32
AC ourrent (1 A at 1 kHz)	Slow (5½ digits)	15	16	17
AC current (1A at 1 kHz)	Fast (4½ digits)	70	37	37
Pagistance (100 kO)	Slow (5½ digits)	15	17	17
Resistance (100 k Ω)	Fast (4½ digits)	70	27	31
Capacitance (10 μF)	Slow/Fast (3½ digits)	5	4.4	4.6
Frequency	Slow (5½ digits)	9	2.7	2.7
(voltage path at 10 V, 1 kHz)	Fast (4½ digits)	9	2.7	2.7
Frequency	Slow (5½ digit)	9	2.7	2.7
(current path at 10 V, 1 kHz)	Fast (4½ digit)	9	2.7	2.7

^[1] Reading rate of the A/D converter.

Supplementary specifications

DC voltage	
Measurement method	Sigma Delta A-to-D converter
Maximum input voltage	1000 V _{dc} on all ranges
Input impedance	10 M Ω ± 2% range (typical) in parallel with capacitance < 120 pF
Input protection	1000 V_{rms} on all ranges, < 0.3 A short circuit
Response time	Approximately 0.15 s when the displayed reading reaches 99.9% DC value of the tested input signal at the same range.
DC current	
Measurement method	Sigma Delta A-to-D converter
Maximum input current	10 mA – 3.0 A DC
Burden voltage and shunt resistance	• <0.2 V, 10 Ω for 10 mA range • <0.2 V, 1 Ω for 100 mA range • < 0.3 V, 0.1 Ω for 1 A range • < 0.7 V, 0.01 Ω for 3 A range
Input protection	Protected with 3.15 A/500 V, FF fuse
Response time	Approximately 0.15 s when the displayed reading reaches 99.9% DC value of the tested input signal at the same range.

 $[\]label{eq:command} \ensuremath{\text{[2]}} \ \mbox{Number of measurements per second that can be read through USB using SCPI "READ?" command. }$

^[3] Number of measurements per second that can be read through GPIB using SCPI "READ?" command.

Input protection

Supplementary specifications	
AC voltage	
Measurement method	AC coupled true rms
Maximum input voltage	$750 V_{rms}/1200 V_{peak}/3 \times 10^7 V$ -Hz of product
Input impedance	1 M Ω ± 2% range (typical) in parallel with capacitance < 120 pF
Input protection	750 V _{rms} on all ranges
Crest factor	For < 5:1 errors included. Limited by the peak input and 100 kHz bandwidth. Maximum 3.0 at full scale.
Peak input	300% of range. Limited by maximum input.
Response time	Approximately $2.5\mathrm{s}$ when the displayed reading reaches $99.9\%\mathrm{AC}$ rms value of the tested input signal at the same range.
Overload ranging	Will select higher range if peak input overload is detected during auto range. Overload is reported in manual ranging.
AC current	
Measurement method	AC coupled true rms
Maximum input current	10 mA – 3.0 A DC or AC rms
Burden voltage and shunt resistance	• < 0.2 V, 10 Ω for 10 mA range • < 0.2 V, 1 Ω for 100 mA range • < 0.3 V, 0.1 Ω for 1 A range • < 0.7 V, 0.01 Ω for 3 A range
Input protection	Protected with 3.15 A/500 V, FF fuse
Crest factor	For $<$ 5:1 errors included. Limited by the peak input and 100 kHz bandwidth. Maximum 3.0 at full scale.
Peak input	300% of range. Limited by maximum input.
Response time	Approximately 2.5 s when the displayed reading reaches 99.9% AC rms value of the tested input signal at the same range.
Resistance	
Measurement method	Two-wire, open-circuit voltage limited to $< 5 \text{ V}$
Open circuit voltage	$<+5.0~V_{dc}$
Input protection	1000 Vrms on all ranges, < 0.3 A short circuit
Response time	Approximately 0.15 seconds for 1 $M\Omega$ and ranges below 1 $M\Omega$
Low-resistance	
Measurement method	Four-wire; test current is sent from the FORCE terminals and resistance measured at the SENSE terminals.
Input protection	 FORCE terminals: 3.15 A/250 V SENSE terminals: 1000 V_{rms} on all ranges, < 0.3 A short circuit
Continuity	
Measurement method	$0.83~\text{mA} \pm 0.2\%$ constant current source
Open circuit voltage	$<+5.0~V_{dc}$
Audible tone	Continuous beeping when reading is less than the threshold resistance of 10 Ω at 1.0 $k\Omega$ range
Input protection	1000 V _{rms} on all ranges, < 0.3 A short circuit
Diode	
Measurement method	0.83 mA ± 0.2% constant current source
Open circuit voltage	< +5.0 V _{dc}
Audible tone	 Continuous beeping when level is below +50 mV DC Single tone for normal forward-biased diode or semiconductor junction where 0.3 V ≤ reading ≤ 0.8 V
	5

1000 V_{rms} on all ranges, < 0.3 A short circuit

Supplementary specifications

Capacitance	
Measurement method	Computed from constant current source charge time, typical 0.2 V to 1.4 Vac signal level
Maximum voltage at full scale	• For 1 nF $-$ 10 μ F range: $<$ 1.5 V • For 100 μ F $-$ 10000 μ F: 0.33 V
Input protection	1000 V _{rms} on all ranges, < 0.3 A short circuit
Response time	Approximately 1 s for 100 μF and ranges below 100 μF
Charge and discharge voltage	5 V_{pp} (approximately from +3 V to -2 V)
Frequency	
Measurement method	Reciprocal counting technique
Signal level	0.2 V – 1.4 V
Input protection	 Voltage path: 1000 Vrms on all ranges, < 0.3 A short circuit Current path: Protected with 3.15 A/500 V, FF fuse
Maximum display counts (excluding frequency)	
5½ digits	120,000
4½ digits	12,000
Noise rejection	
Common mode rejection ratio (CMRR) for 1 $k\Omega$ unbalanced in LO lead	DC: 140 dB, AC: 70 dB
Normal mode rejection ratio (NMRR)	60 Hz ± 0.1%: 5½ digits: 65 dB, 4½ digits: 0 dB
	50 Hz ± 0.1%: 5½ digits: 55 dB, 4½ digits: 0 dB

Power supply specifications

Specification assumptions:

- Specifications stated are after 60-minutes of warm-up and with no load
- Operating temperature: $18 \,^{\circ}\text{C} 28 \,^{\circ}\text{C} \, (64.4 \,^{\circ}\text{F} 82.4 \,^{\circ}\text{F})$
- Accuracy is expressed as \pm (% of output + offset) at 23 °C \pm 5 °C
- Temperature coefficient: Add [0.1 x (the specified accuracy) / °C] for 0 °C 18 °C and 28 °C 55 °C
- Relative humidity (RH) up to 80% at 30 °C, proportional to 50% for 30 °C 55 °C

DC power supply specifications

Output ratings	Range S1: 0 V to 30 V, 0 A to 1 A
	Range S2: 0 V to 8 V, 0 A to 3 A
Programming accuracy	• 0.05% + 5 mV
1 year (@ 23 °C \pm 5 °C), \pm (% of output + offset)	• 0.15% + 3mA
Readback accuracy	• 0.05% + 5 mV
1 year over GPIB and USB or front panel with respect to actual output (@ 23 °C ± 5 °C), ±(% of output + offset)	• 0.15% + 3mA
Ripple and noise	• < 2 mV _{rms} ; < 30 mV _{pp}
With outputs ungrounded, or with either output terminal grounded, 20 Hz to 1 MHz	<1 mA _{rms}
Front terminal load regulation	• < 3 mV ^[1]
\pm (% of output + offset)	< 0.03% + 0.3 mA
Rear terminal load regulation	• < 0.01% + 3 mV
±(% of output + offset)	• < 0.03% + 0.3 mA
Line regulation	3 mV, 1.5 mA
±(% of output + offset)	
Programming resolution	1 mV, 0.1 mA
Readback resolution	1 mV, 0.1 mA
Front panel resolution	1 mV, 0.1 mA
Transient response time	Less than 300 ms for output to recover to within 15 mV following a change in output current from full load to half load or vice versa.
Command processing time	Average time for output voltage to begin to change after receipt of digital data when instrument is connected directly to the USB or GPIB is less than 100 ms.
Overvoltage protection (for CC mode):	Accuracy: 0.5% + 0.5 V
	Activation time ^[2] : < 2ms
Overcurrent protection (for CV mode):	Accuracy: 0.5% + 0.05 A
	Activation time ^[2] : < 2 ms

^[1] Contacts and leads resistance may contribute an additional error of 6mV/A (typical).

^[2] Average time for the detection of OVP or OCP condition.

Power supply specifications (continued)

Sweep specifications

Function		Range	Amplitude	Step	Dwelling time
Scan	Constant voltage	S1 (30 V/1 A)	0 – 31.500 V	1 step – 100 steps	1 s – 99 s
		S2 (8 V/3 A)	0 - 8.4000 V		
	Constant current	S1 (30 V/1 A)	0 – 1.0500 A	1 step – 100 steps	1 s – 99 s
		S2 (8 V/3 A)	0 – 3.1500 A		
Ramp	Constant voltage	S1 (30 V/1 A)	0 – 31.500 V	1 step — 10,000 steps	300 ms/step (typical)
		S2 (8 V/3 A)	0 - 8.4000 V		
	Constant current	S1 (30 V/1 A)	0 – 1.0500 A	1 step — 10,000 steps	300 ms/step (typical)
		S2 (8 V/3 A)	0 – 3.1500 A		

^[1] Ramp and scan outputs start at 0 volt by default.

Square-wave output specifications

Parameter	Range	Resolution	Accuracy
Frequency	0.5, 2, 5, 6, 10, 15, 25, 30, 40, 50, 60, 75, 80, 100, 120, 150, 200, 240, 300, 400, 480, 600, 800, 1200, 1600, 2400, 4800 Hz	0.01 Hz	0.005% + 1 count
Duty cycle	0.39% - 99.60%	0.39% [1]	0.4% [1][2]
Pulse width	1/Frequency	Range/256	Duty cycle/Frequency [1][3]
Amplitude	S1 (30 V/1 A) S2 (8 V/3 A)	1 mV 1 mV	0.2 V 0.2 V

^[1] Specification applies when the positive or negative pulse width is greater than 50 $\mu s.\,$

$$Accuracy = 0.4\% + \left(\frac{frequency}{100} - 1\right) \times 0.1\%$$

Supplementary specifications

Output programming range

Range	Output programming	0V/0C	OVP/OCP
S1	0 V to 31.500 V/0 A to 1.05 A	31.500 V/1.05 A	33.000 V/1.1 A
S2	0 V to 8.4 V/0 A to 3.15 A	8.4 V/3.15 A	8.8 V/3.3 A

Remote sensing capability

• Range S1 (30 V/1 A): up to a 0.75-volt drop per load lead

• Range S2 (8V/3 A): up to a 0.5-volt drop per load lead

Temperature coefficient

 \pm (% of output + offset)/ °C for 0 °C - 18 °C and 28 °C - 55 °C

Voltage: 0.005% + 0.5 mV/°C
 Current: 0.02% + 1 mA/°C

Voltage programming speed (excludes command processing time)

• Up: 300 ms (full load and no load)

• Down: 400 ms (full load and no load)

^[2] For frequency signals greater than 100 Hz, an additional 0.1% per 100 Hz is to be added.

^[3] The accuracy of pulse width could also be calculated as $[0.4\% + (frequency/100 - 1) \times 0.1\%]/frequency$.

^[4] Rise/fall time is less than 25 $\mu s.$

^[5] Specifications are based on a resistive load.

General characteristics

Power supply

- Universal 100 Vac to 240 Vac ±10%
- AC line frequency 45 Hz to 66 Hz and (360 Hz to 440 Hz, for 100/120 V operation)

Power consumption

150 VA maximum

Fuse

Front panel 3.15 A, 500 V FF fuse

Display

Highly visible vacuum-fluorescent display (VFD)

Operating environment

- Operating temperature from 0 °C to +55 °C
- Relative humidity up to 80% at 30 °C RH (non-condensing)
- Altitude up to 2000 meters
- Pollution degree 2
- · For indoor use only

Storage compliance

-40 °C to 70 °C

Safety compliance

Certified with:

- IEC 61010-1:2001/EN61010-1:2001 (2nd Edition)
- Canada: CAN/CSA-C22.2 No. 61010-1-04
- USA: ANSI/UL 61010-1:2004

EMC compliance

Certified with:

- IEC61326-1:2005 / EN61326-1:2006
- CISPR 11:2003 / EN55011:2007 (Group 1 Class A)
- Canada: ICES/NMB-001:2004
- Australia/New Zealand: AS/NZS CISPR11:2004

Shock and vibration

Tested to IEC/EN 60068-2

Remote interface

- GPIB IEEE-488
- Full Speed USB 2.0 (Type B)
- USBTMC 488.2 Class device
- USB-CDC

Programming language

Standard Commands for Programmable Instruments (SCPI)

Measurement category

- CAT II, 300 V
- CAT I, 1000 V_{dc}, 750 V_{ac} rms
- 2500 V_{pk} transient over voltages

Dimensions $(H \times W \times D)$

 $105 \times 255 \times 329$ mm (with rubber bumpers) 87 x 215 x 312 mm (without rubber bumpers)

Weight

3.775 kg (with rubber bumpers)
3.535 kg (without rubber bumpers)

Warranty

One year

Calibration cycle

One year

Warm-up time

60 minutes

Ordering information

Standard shipped items

- · Quick Start Guide
- · Product Reference CD
- Agilent IO Library Suite
- · Certificate of Calibration
- U8201A Combo Test Lead Kit
- USB 2.0 High-Speed Type-A to Type-B cable
- · AC power cord

Warranty options

R-51B-001-3C Extended warranty from one year to three years

R-51B-001-5C Extended warranty from one year to five years

Optional accessories



U8201A Combo Test Lead Kit



U3606A-1CM Rack Mount Kit



U8202A Electronic Test Lead Kit (for DMM function)



34133A Precision Electronic Test Leads (for DMM function)



34330A Current Shunt (30 A) (for DMM function)



34136A 40 kV high-voltage probe (for DMM function)



11059A Kelvin Probe Set and 11062A Kelvin Clip Set (for DMM function)



E3600A-100 Test Lead Kit (for DC power supply function)

I/O connectivity options

For control via GPIB interface

- 82350B/82351A PCI/PCIe high-performance GPIB interface card
- 82357B USB/GPIB converter
- E5810A LAN/GPIB gateway
- 10833D/A/B/C/F/G GPIB cables
- 10834A GPIB-to-GPIB adapter

For control via USB interface

• E5813A networked 5-port USB hub

Agilent Email Updates

www.agilent.com/find/emailupdates Get the latest information on the products and applications you select.



www.agilent.com/find/agilentdirect Quickly choose and use your test equipment solutions with confidence.

Remove all doubt

Our repair and calibration services will get your equipment back to you, performing like new, when promised. You will get full value out of your Agilent equipment throughout its lifetime. Your equipment will be serviced by Agilent-trained technicians using the latest factory calibration procedures, automated repair diagnostics and genuine parts. You will always have the utmost confidence in your measurements.

Agilent offers a wide range of additional expert test and measurement services for your equipment, including initial start-up assistance onsite education and training, as well as design, system integration, and project management.

For more information on repair and calibration services, go to

www.agilent.com/find/removealldoubt

Product specifications and descriptions in this document subject to change without notice.

www.agilent.com www.agilent.com/find/hybridmultimeter

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Phone or Fax Americas

, miloriouo	
Canada	(877) 894-4414
Latin America	305 269 7500
United States	(800) 829-4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Thailand	1 800 226 008

Europe & Middle East

Austria	01 36027 71571	
Belgium	32 (0) 2 404 93 40	
Denmark	45 70 13 15 15	
Finland	358 (0) 10 855 2100	
France	0825 010 700*	
	*0.125€/minute	
Germany	07031 464 6333	
Ireland	1890 924 204	
Israel	972-3-9288-504/544	
Italy	39 02 92 60 8484	
Netherlands	31 (0) 20 547 2111	
Spain	34 (91) 631 3300	
Sweden	0200-88 22 55	
Switzerland	0800 80 53 53	
United Kingdom	44 (0) 118 9276201	
Other Furonean Countries:		

Other European Countries: www.agilent.com/find/contactus Revised: October 6, 2008

© Agilent Technologies, Inc. 2009 Printed in USA, May 13, 2009 5990-3971EN

