

### RoHS Compliant

#### **Features**

- · Compact 17.5 mm Wide
- · Multi Function: (8 or 18) Non Signal & Signal based functions
- Multi-Voltage: 24 240V AC/DCWide Timing Range: 0.1s to 999 Hr
- 3 Digit LCD for Preset time and Run time
- · Option to select Up/Down counting
- · Tamper proof with key lock feature

### **Specification**

Part Number		MP008382	MP008383	MP008384	MP008385	
Parameters						
Timer Description		Multi Function Digital Timer				
Functions		1) ON Delay 2) Cyclic OFF/ON 3) Cyclic ON/OFF 4) Signal ON/OFF 5) Signal OFF Delay 6) Interval 7) Signal OFF/ON 8) One Shot Output		1) ON Delay 2) Cyclic OFF/ON 3) Cyclic ON/OFF 4) Impulse on Energizing 5) Accumulative Delay on Signal 6) Accumulative Delay on Inverted Signal 7) Accumulative Impulse on Signal 8) Signal ON Delay 9) Inverted Signal ON Delay 10) Signal OFF Delay 11) Impulse ON/OFF 12) Signal OFF/ON 13) Leading Edge Impulse 1 14) Leading Edge Impulse 2 15) Trailing Edge Impulse 2 16) Trailing Edge Impulse 2 17) Delayed Impulse 18) Inverted Signal ON Delay		
Supply Voltage		24 - 240V AC/DC				
Supply Variation		-15% to +10%				
Frequency		50-60 Hz				
Power Consumption (Max.)		0.5 VA (@ 24/48V AC), 4 VA (@ 110 to 265V AC/DC)				
Timing Range		0.1s to 999h				
Reset Time		200 ms (Max.)				
Repeat Accuracy		± 0.5%				
Output	Relay Output	1 C/O	2 NO	1 C/O	2 NO	
	Contact Rating	8A @ 240V AC / 24V DC (Resistive)				
	Electrical Life	1 × 10 <sup>5</sup>				
	Mechanical Life	$2 \times 10^7$				





Utilization Category	AC - 15	Rated Voltage (Ue): 125/240 V, Rated Current (Ie): 3/1.5 A		
	DC - 13	Rated Voltage (Ue): 125/250 V, Rated Current (Ie): 2/0.22/0.1 A		
Operating Temperature Storage Temperature		-10°C to +55°C -20°C to +65°C		
Humidity (Non Condensing)		95% (Rh)		
LED Indication		Red LED—Relay ON		
Enclosure		Flame Retardant UL94-VO		
Dimension (W x H x D)		18mm × 85mm × 76mm		
Weight (unpacked) Approx.		85 g		
Mounting		DIN rail		
Degree of Protection		IP 20 for Terminals, IP 30 for Enclosure		

### Functional Diagrams For MP008382, MP008383




#### ON DELAY (A)

On application of supply voltage, the preset time duration (T) starts. On completion of the preset time, the output is switched ON and remains ON till the supply voltage is present



#### CYCLIC OFF/ON {OFF Start, (Sym, Asym)} (b)

On application of supply voltage, the output is initially switched OFF for the preset 'OFF' time duration (TOFF) after which it is switched ON for the preset 'ON' time duration (TON). This cycle repeats and continues till the supply is present.




### CYCLIC ON/OFF {ON Start, (Sym, Asym)} (C)

On application of supply voltage, the output is initially switched ON for the preset 'ON' time duration (TON) after which it is switched OFF for the preset 'OFF' time duration (TOFF). This cycle repeats and continues till the supply is present.









#### SIGNAL ON/OFF (d)

The output relay is turned ON for Preset Time (T) whenever the Signal(S) is applied or removed




#### SIGNAL OFF DELAY (E)

On application of supply voltage and input signal, the output is switched ON. When the signal is removed the preset time duration commences & the output is switched OFF at the end of the time duration.




#### INTERVAL (F)

When supply power is applied to the timer and on application of input signal the output is immediately switched ON. The output remains ON for the preset time duration (T) after which it is switched OFF.



#### SIGNAL OFF / ON (G)

When Signal (S) is applied or removed, the relay changes its state after Timer Duration (T)



#### ONE SHOT OUTPUT (H)

When Signal (S) is applied, the Timer Duration (T) starts. At the end of Timer duration (T), the relay gets energized for approximately 1 sec.(Refer Note : 2)






### Functional Diagrams for MP008384 & MP008385

#### ON DELAY [0]

On application of supply voltage, the preset time duration (T) starts. On completion of the preset time, the output is switched ON and remains ON till the supply voltage is present.



#### CYCLIC OFF/ON

#### {OFF Start, (Sym, Asym)} [1]

On application of supply voltage, the output is initially switched OFF for the preset 'OFF' time duration (TOFF) after which it is switched ON for the preset 'ON' time duration (TON). This cycle repeats and continues till the supply is present.



#### CYCLIC ON/OFF


#### {ON start, (Sym, Asym)} [2]

On application of supply voltage, the output is initially switched ON for the preset 'ON' time duration (TON) after which it is switched OFF for the preset 'OFF' time duration (TOFF). This cycle repeats and continues till the supply is present.




#### **IMPULSE ON ENERGIZING [3]**

On application of supply voltage, the output is instantly switched ON for the preset time duration (T) after which it is switched OFF.




#### **ACCUMULATIVE DELAY ON SIGNAL [4]**

On application of supply voltage, the preset timing duration commences. When input signal is applied, the timing pauses and resumes only when the input signal is removed. The output is switched ON at the end of the preset time duration (T).




#### ACCUMULATIVE DELAY ON INVERTED SIGNAL [5]

On application of supply voltage and input signal, the preset timing duration commences. When the signal is removed the timing pauses and resumes when the signal is applied. The output is switched ON at the end of the preset time duration (T).



#### ACCUMULATIVE IMPULSE ON SIGNAL [6]

On application of supply voltage the output is switched ON & the preset timing duration commences. When the signal is applied the timing pauses and resumes when the signal is removed. The output is switched OFF at the end of the preset time duration (T).









#### **SIGNAL ON DELAY [7]**

On application of input signal, the preset time duration (T) starts. On completion of the preset time, the output is switched ON and remains ON till the input signal is present




#### **INVERTED SIGNAL ON DELAY [8]**

On application of supply voltage, the preset time duration (T) starts. When input signal is applied, the timing pauses & resumes only when the signal is removed. On completion of the preset time, the output is switched ON.




#### **SIGNAL OFF DELAY [9]**

On application of supply voltage and input signal, the output is switched ON. When the signal is removed the preset time duration commences & the output is switched OFF at the end of the time duration.




#### IMPULSE ON/OFF [A]

On application or removal of input signal, the output is switched ON & the preset time duration (T) starts. On completion of the time duration the output is switched OFF. When timing commences, changing the state of the input signal resets the time.




#### SIGNAL OFF/ON [b]

On application of input signal, the preset delay time period (T) starts. On completion of the preset time, the output is switched ON. On removal of input signal, the preset time period starts again and the output is switched ON when the preset time duration is complete.




#### **LEADING EDGE IMPULSE1 [C]**

On application of input signal the output is immediately switched ON. The output remains ON for the preset time duration (T) after which it is switched OFF. If the input signal is removed during the preset time, the output remains unaffected.



#### LEADING EDGE IMPULSE2 [d]

On application of input signal the output is immediately switched ON. The output remains ON for the preset time duration (T) after which it is switched OFF. If the input signal is removed during the preset time, the output is immediately switched OFF.






# multicomp PRO


#### TRAILING EDGE IMPULSE1 [E]

When the input signal to the timer is removed, the output is immediately switched ON for the preset time duration (T) after which it is switched OFF. If the input signal is applied during the preset time, the output is immediately switched OFF.




#### TRAILING EDGE IMPULSE2 [F]

When the input signal to the timer is removed, the output is immediately switched ON for the preset time duration (T) after which it is switched OFF. If the input signal is applied during the preset time, the output remains unaffected.




#### **DELAYED IMPULSE [G]**

On application of input signal, the preset 'OFF' time duration (TOFF) starts. the output is switched ON at the end of the preset 'OFF' time duration & the preset 'ON' time duration commences irrespective of signal level and remains ON till the completion of 'TON'.



#### **INVERTED SIGNAL ON DELAY-TYPE 2 [H]**

Timing starts only upon signal 'S' transition high to low. During timing or after completion of Time (i.e. relay on), any signal transition is ignored. To reset the timer supply has to be interrupted.



### **Part Number Table**

Description	Part Number
Multi Function Digital Timer, 8 Functions, 1CO	MP008382
Multi Function Digital Timer, 8 Functions, 2NO	MP008383
Multi Function Digital Timer, 18 Functions, 1CO	MP008384
Multi Function Digital Timer, 18 Functions, 2NO	MP008385

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

