Anti-Vandal Switches Push Button

multicomp PRO








RoHS Compliant

Specifications

Material		
Case	: Dially Phthalate, Rated UL 94V-0	
Сар	: Polyamide66	
Bushing	: Polyamide66	
Terminal	: Gold Over Silver Plated	
Electrical		
Rating	: 400mA 32V AC	
	100mA 50V DC	
	125mA 125V DC	
	500mA 48V DC	
	200mA 50V DC	
Contact Resistance	: 50mΩ max.	
Insulation Resistance	: 1G–Ω min. @ 500V DC	
Dielectric withstanding voltage	: 1000V AC, for 1 Minute	
Electrical Life	: 500,000 cycles	
Temperature Rating		
Operating temperature	: -30°C to +85°C	
Environmental		
Front Panel Protection	: IP67	

Diagram



Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Part Number Table

Description	Button Colour	Part Number
Anti Vandal Switch, SPST, Off-MOM, Solder Type	Green	MP-PB11-1CSG-10
	Red	MP-PB11-1CSR-10
	Black	MP-PB11-1CSK-10

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

