

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0464379302

Status:


Active

Overview:

EXTreme Ten60 High-Power Connectors

Description:

EXTreme Ten60Power Right-Angle Plug with Side Guides, 2 DC Power Circuit, Press Fit Tail



Documents:	
3D Model	Packaging Specification 464371001-PK-000 (PDF)
3D Model (PDF)	Test Summary 464361000-TS-000 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification PS-46436-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	46437
Application	Board-to-Board, Power
Comments	See Product Specification for details
Component Type	PCB Header
Overview	EXTreme Ten60 High-Power Connectors
Product Name	EXTreme Ten60Power
Taxonomy	Board-to-Board Connectors
UPC	195842663237
Physical	
(p)ower-(s)ignal Configuration	2p - 0s
Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	No
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	8.118/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.28mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	5.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

46437 Series

Mates With

EXTreme Ten60Power Right-Angle Receptacle [464369302](#) . EXTreme Ten60Power Vertical Receptacle [465629302](#)

Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	60.0A
Voltage - Maximum	600V AC / 250V DC
Material Info	
Engineering Number	46437-9301
Reference - Drawing Numbers	
Packaging Specification	464371001-PK-000
Product Specification	PS-46436-100-001
Sales Drawing	464379310-000
Test Summary	464361000-TS-000

This document was generated on 01/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION