


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0464379304](#)
Status: **Active**
Overview: [EXTreme Ten60 High-Power Connectors](#)
Description: EXTreme Ten60Power Right-Angle Plug with Side Guides, 4 DC Power Circuits, Press Fit Tail

Documents:

3D Model	Packaging Specification 464371001-PK-000 (PDF)
Drawing (PDF)	Test Summary 464361000-TS-000 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-46436-100-001 (PDF)	RoHS Certificate of Compliance (PDF)



Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	46437
Application	Board-to-Board, Power
Comments	See Product Specification for details
Component Type	PCB Header
Overview	EXTreme Ten60 High-Power Connectors
Product Name	EXTreme Ten60Power
Taxonomy	Board-to-Board Connectors
UPC	195842664814

Physical

(p)ower-(s)ignal Configuration	4p - 0s
Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	No
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	13.543/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.28mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	5.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46437 Series](#)

Mates With

EXTreme Ten60Power Right-Angle Receptacle [464369304](#) . EXTreme Ten60Power Vertical Receptacle [465629304](#)

Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	60.0A
Voltage - Maximum	600V AC / 250V DC

Material Info**Reference - Drawing Numbers**

Packaging Specification	464371001-PK-000
Product Specification	PS-46436-100-001
Sales Drawing	464379310-000
Test Summary	464361000-TS-000

This document was generated on 01/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION