

2-conductor fuse terminal block; for automotive blade-style fuses; with test option; with blown fuse indication by LED; 24 V; for DIN-rail 35 x 15 and 35 x 7.5; 6 mm<sup>2</sup>; Push-in CAGE CLAMP®; 6,00 mm²; gray




Blade-style fuses: Observe touch-proof protection for 42 V and higher voltages!

https://www.wago.com/2006-1681/1000-434







2006-1681/1000-434

Rated current UL (Use Group C)

Electrical data	
Ratings per IEC/EN	
Ratings per	IEC/EN 60947-7-3
Ratings (note)	Electrical ratings are given by the fuse and blown fuse indication.
Nominal voltage (III/3)	500 V
Rated impulse voltage (III/3)	8 kV
Rated current	25 A
Current at conductor cross-section (max.) mm²	30 A
Operation status indicator	24 V
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

2.000.100.100.100.100.100.100.100.100.10	
Ratings per IEC/EN	
Ratings per	IEC/EN 60947-7-3
Ratings (note)	Electrical ratings are given by the fuse and blown fuse indication.
Nominal voltage (III/3)	500 V
Rated impulse voltage (III/3)	8 kV
Rated current	25 A
Current at conductor cross-section (max.) mm <sup>2</sup>	30 A
Operation status indicator	24 V
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Polluti-

30 A

Ratings per CSA	
Approvals per	CSA 22.2 No 158
Rated voltage CSA (Use Group B)	24 V
Rated current CSA (Use Group B)	30 A
Rated voltage CSA (Use Group C)	24 V
Rated current CSA (Use Group C)	30 A

Ratings per UL 1059 Ratings per CSA	
Approvals per UL 1059 Approvals per CSA 22.2 No 158	
Rated voltage UL (Use Group B) 24 V Rated voltage CSA (Use Group B) 24 V	
Rated current UL (Use Group B) 30 A Rated current CSA (Use Group B) 30 A  Rated voltage UL (Use Group C) 24 V Rated voltage CSA (Use Group C) 24 V	

Ratings per IEC/EN 2

Ratings (note) 2

# Data Sheet | Item Number: 2006-1681/1000-434 https://www.wago.com/2006-1681/1000-434



pluggable Fuse receptacle

Standard flat plug-in fuse; 19.1 x 5.1 x 18.5 mm Fuse type



Connection data			
Connection points	2	Connection 1	
Total number of potentials	2	Connection technology	Push-in CAGE CLAMP®
Number of levels	1	Actuation type	Operating tool
Number of jumper slots	2	Connectable conductor materials	Copper
		Nominal cross-section	6 mm²
		Solid conductor	0.5 10 mm² / 20 8 AWG
		Solid conductor; push-in termination	2.5 10 mm² / 14 8 AWG
		Fine-stranded conductor	0.5 10 mm² / 20 8 AWG
		Fine-stranded conductor; with insulated ferrule	0.5 6 mm² / 20 10 AWG
		Fine-stranded conductor; with ferrule; push-in termination	2.5 6 mm² / 16 10 AWG
	Note (conductor cross-section)	Depending on the conductor characteristic, a conductor with a smaller cross-section can also be inserted via push-in termination.	
		Strip length	13 15 mm / 0.51 0.59 inches
		Wiring direction	Front-entry wiring

Physical data	
Width	7.5 mm / 0.295 inches
Height	96.3 mm / 3.791 inches
Depth from upper-edge of DIN-rail	32.9 mm / 1.295 inches

Mechanical data	
Mounting type	DIN-35 rail
Marking level	Center/side marking

Material data	
Note (material data)	
	<u>Information on material specifications can be found here</u>
Color	gray
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.322 MJ
Weight	17.7 g

https://www.wago.com/2006-1681/1000-434



## **Environmental requirements**

Processing temperature -35 ... +85 °C Continuous operating temperature -60 ... +105 °C

Commercial data	
Product Group	22 (TOPJOB S)
eCl@ss 10.0	27-14-11-16
eCl@ss 9.0	27-14-11-16
ETIM 8.0	EC000899
ETIM 7.0	EC000899
PU (SPU)	25 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454789800
Customs tariff number	85369095000

## Approvals / Certificates

#### General approvals







Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	IEC 60947	71-122840 REV.1
CCA DEKRA Certification B.V.	EN 60947	NTR NL 7925/1
CSA DEKRA Certification B.V.	C22.2 No. 158	1543858
UL UL International Germany GmbH	UL 1059	E45172

## Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
Railway WAGO GmbH & Co. KG	-	Railway Ready
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

## Approvals for marine applications








Approval	Standard	Certificate Name
ABS American Bureau of Ship- ping	EN 60947	20-HG1941090-PDA
DNV GL Det Norske Veritas, Ger- manischer Lloyd	-	TAE00001V2
LR Lloyds Register	EN 60947	91/20112 (E9)


### Downloads


## **Environmental Product Compliance**

https://www.wago.com/2006-1681/1000-434











## 1.2 Optional Accessories

#### 1.2.1 Cover

#### 1.2.1.1 Cover



Item No.: 2006-191

Lockout cap; for wire insertion and actuating opening; gray

## 1.2.2 DIN-rail

https://www.wago.com/2006-1681/1000-434

#### 1.2.2.1 Mounting accessories



#### Item No.: 210-196

Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored



#### Item No.: 210-198

Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; copper-colored



Item No.: 210-508 Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; galvanized; similar to EN 60715; silver-colored

## Item No.: 210-197

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715; silver-colored



#### Item No.: 210-506

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; galvanized; similar to EN 60715; silver-colored

## Item No.: 210-114

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715: silver-colored

#### Item No.: 210-118

Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to FN 60715; silver-colored

#### Item No.: 210-115

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm; silver-colored



Item No.: 210-112

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm; silver-colored

#### Item No.: 210-504

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; galvanized; according to EN 60715; silver-colored

#### Item No.: 210-113

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored

## Item No.: 210-505

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; galvanized; according to EN 60715; silver-colored

#### 1.2.3 Ferrule

#### 1.2.3.1 Ferrule





lated; electro-tin plated; electrolytic cop-

per; gastight crimped; acc. to DIN 46228,

## Item No.: 216-264

Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN



#### Item No.: 216-262

Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray



#### Ferrule; Sleeve for 1 mm2 / AWG 18; insu-

46228, Part 4/09.90; black

#### Item No.: 216-266

Ferrule; Sleeve for 2.5 mm<sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue



Ferrule; Sleeve for 4 mm<sup>2</sup> / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

#### Item No.: 216-208

Item No.: 216-263

Part 4/09.90; red

Ferrule; Sleeve for 6 mm<sup>2</sup> / AWG 10; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; yellow

### 1.2.4 Installation

#### 1.2.4.1 Cover



#### Item No.: 709-156

Cover; Type 3; suitable for cover carrier, type 3; 1 m long; transparent

#### 1.2.4.2 Cover carrier



#### Item No.: 709-169

Cover carrier; Type 3; gray

#### 1.2.5 Jumper

https://www.wago.com/2006-1681/1000-434



#### 1.2.5.1 Jumper

Item No.: 2006-403 Jumper; 3-way; insulated; light gray

Item No.: 2006-405

Jumper; 5-way; insulated; light gray



Jumper; 2-way; insulated; light gray

Item No.: 2006-433

Item No.: 2006-402

Jumper; from 1 to 3; insulated; light gray

Item No.: 2006-434

Jumper; from 1 to 4; insulated; light gray

Jumper; 4-way; insulated; light gray

Item No.: 2006-404

Item No.: 2006-435 Jumper; from 1 to 5; insulated; light gray Item No.: 2006-405/011-000

Star point jumper; 3-way; insulated; light

#### 1.2.6 Marking

#### 1.2.6.1 Group marker carrier



Item No.: 2009-192 Group marker carrier; gray



Item No.: 2009-193

Group marker carrier; gray

#### 1.2.6.2 Marker

Item No.: 2009-191

Group marker carrier; gray

#### Item No.: 2009-145/000-006

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue

#### Item No.: 2009-145/000-007

Item No.: 2009-145/000-024

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray

Mini-WSB Inline: for Smart Printer: 1700

pieces on roll; stretchable 5 - 5.2 mm;

#### Item No.: 2009-145/000-023

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green

#### Item No.: 2009-145/000-012

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange

#### Item No.: 2009-145/000-005

Mini-WSB Inline: for Smart Printer: 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red



plain; snap-on type; violet

Item No.: 248-501/000-007 Mini-WSB marking card; as card; not stretchable; plain; snap-on type; gray

### Item No.: 2009-145

Mini-WSB Inline: for Smart Printer: 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

Mini-WSB marking card; as card; not

## Item No.: 2009-145/000-002

Mini-WSB Inline: for Smart Printer: 1700 pieces on roll: stretchable 5 - 5.2 mm: plain; snap-on type; yellow



#### Item No.: 248-501/000-006

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; blue



#### Item No.: 248-501/000-023

stretchable; plain; snap-on type; green

## Item No.: 248-501/000-017

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; light green



#### Item No.: 248-501/000-012

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; orange



## Item No.: 248-501/000-005

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; red



## Item No.: 248-501/000-024

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; violet



## Item No.: 248-501

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white



#### Item No.: 248-501/000-002

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; yellow

## Item No.: 793-5501/000-006

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; blue

WMB marking card; as card; for terminal

block width 5 - 17.5 mm; stretchable 5 -

5.2 mm; plain; snap-on type; orange



## Item No.: 793-5501/000-007

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; gray




## Item No.: 793-5501/000-023

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; green



## Item No.: 793-5501/000-017

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; light green



## Item No.: 793-5501/000-005

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; red



## Item No.: 793-5501/000-024

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; violet



## Item No.: 793-5501

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; white



#### Item No.: 793-5501/000-002

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; yellow



#### Item No.: 793-501/000-006

WMB marking card; as card; not stretchable; plain; snap-on type; blue



#### Item No.: 793-501/000-007

WMB marking card; as card; not stretchable; plain; snap-on type; gray



#### Item No.: 793-501/000-023

WMB marking card; as card; not stretchable; plain; snap-on type; green

#### Item No.: 793-501/000-017

WMB marking card; as card; not stretchable; plain; snap-on type; light green

#### Item No.: 793-501/000-012

WMB marking card; as card; not stretchable; plain; snap-on type; orange



#### Item No.: 793-501/000-005

WMB marking card; as card; not stretchable; plain; snap-on type; red

https://www.wago.com/2006-1681/1000-434



#### 1.2.6.2 Marker



Item No.: 793-501/000-024 WMB marking card; as card; not stretchable; plain; snap-on type; violet



WMB marking card; as card; not stretchable; plain; snap-on type; white

## Item No.: 793-501/000-002

WMB marking card; as card; not stretchable; plain; snap-on type; yellow

A

## Item No.: 2009-115/000-006

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue

4



Item No.: 2009-115/000-023 WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green

#### Item No.: 2009-115/000-017

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; light green

#### Item No.: 2009-115/000-012

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange



Item No.: 2009-115/000-024

Item No.: 2009-115/000-007

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray

WMB-Inline; for Smart Printer; 1500 pie-

ces on roll; stretchable 5 - 5.2 mm; plain;

Item No.: 2009-115

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

#### Item No.: 2009-115/000-002

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow

# 1.2.6.3 Marker carrier

snap-on type; violet



Item No.: 2002-121 Adaptor; gray

Item No.: 2009-198

Adaptor; gray

## 1.2.6.4 Marking strip



Item No.: 2009-110

Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

#### 1.2.7 Protective warning marker

#### 1.2.7.1 Cover



### Item No.: 2006-115

Protective warning marker; for 5 terminal blocks; with high-voltage symbol, black; yellow

#### 1.2.8 Test and measurement

### 1.2.8.1 Testing accessories



Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks; gray

Item No.: 210-136

Test plug; 2 mm Ø; with 500 mm cable; red

Item No.: 2009-182

Testing tap; for max. 2.5 mm<sup>2</sup>; tool-free connection for individual test wires 0.08 -2.5 mm; gray

### 1.2.9 Tool

https://www.wago.com/2006-1681/1000-434



#### 1.2.9.1 Operating tool



Item No.: 210-721

Operating tool; Blade: 5.5 x 0.8 mm; with a partially insulated shaft; multicoloured

#### **Installation Notes**

#### **Conductor termination**



All conductor types at a glance



Push-in termination of solid and ferruled conductors



Inserting a conductor via push-in termination:

Solid conductors with cross-sections from either one size above, or up to two sizes below, the rated cross-section can be simply pushed in – no tools needed.



Inserting a conductor via operating tool: Connecting fine-stranded conductors without ferrules, or small cross-sectional conductors that cannot be pushed in, is performed similarly to the original CAGE CLAMP® – just use an operating tool. Advantage:

To open the clamp, the operating tool is inserted vertically. The conductor entry is less than 15 degrees for easier wiring.

#### Commoning



Insert push-in type jumper bar and push down until it hits backstop.



Removing a push-in type jumper bar: Insert the operating tool between the jumper and partition wall of the dual jumper slots, then lift up the jumper. Place the operating tool in the center of jumpers for up to five contacts (see above), or alternately on both sides for jumpers with more than five contacts.



https://www.wago.com/2006-1681/1000-434










Application Notes on Terminal Blocks for Glass Cartridge Fuses Diagram: "Block Arrangement"



Application Notes on Terminal Blocks for Glass Cartridge Fuses

Nominal current ratings for fuse cartridges are defined differently in international standards. This is why the recommended continuous current-carrying capacity of the fuses is a max. 80% of their nominal current according to DIN 72581/ Part 3 (for a surrounding air temperature of 23°C).


Selecting the correct fuse cartridge is important for product safety within applications, as well as for fuse cartridge service life and reliability. Fuse cartridges will only operate perfectly as protection components (break-off point) if they are properly selected and used as intended (i.e., according to the state of the technology and valid specifications, as well as data sheet characteristics), according to basic safety requirements (i.e., persons, animals and property must be protected against hazards).



Concerning product safety, fuse cartridges must generally be tested under both normal and faulty operating conditions within your application.

#### Marking







Subject to changes. Please also observe the further product documentation!