

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0464369314](#)
Status: **Active**
Overview: [EXTreme Ten60 High-Power Connectors](#)
Description: EXTreme Ten60Power Right-Angle Receptacle with Side Guides, 4 DC Power Circuits, 15 Signal Circuits, Press Fit Tail

Documents:

3D Model	Packaging Specification 464361001-PK-000 (PDF)
Drawing (PDF)	Test Summary 464361000-TS-000 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-46436-100-001 (PDF)	RoHS Certificate of Compliance (PDF)



Agency Certification

UL E29179

General

Product Family	PCB Receptacles
Series	46436
Application	Board-to-Board, Power, Signal
Comments	See Product Specification for details
Component Type	PCB Receptacle
Overview	EXTreme Ten60 High-Power Connectors
Product Name	EXTreme Ten60Power
Taxonomy	Board-to-Board Connectors
UPC	195842670815

Physical

(p)ower-(s)ignal Configuration	4p - 15s
Circuits (Loaded)	19
Circuits (maximum)	19
Color - Resin	Black
Durability (mating cycles max)	200
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	No
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	17.565/g
Number of Rows	1, 5
Orientation	Right Angle
PC Tail Length	2.50mm, 3.28mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm, 5.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46436 Series](#)

Mates With

[EXTreme Ten60Power Right-Angle Plug
464379314](#)

Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 60.0A
Grounding to PCB No
Voltage - Maximum 600V AC / 250V DC

Material Info

Reference - Drawing Numbers

Packaging Specification 464361001-PK-000
Product Specification PS-46436-100-001
Sales Drawing 464369320-000
Test Summary 464361000-TS-000

This document was generated on 01/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION