|                                  |              | BI-METAL HOLE SAWS |              |   | TUNGSTEN CARBIDE HOLE SAWS            |                                |                               | DIAMOND GRIT/<br>TIPPED HOLE SAWS             |                                    |
|----------------------------------|--------------|--------------------|--------------|---|---------------------------------------|--------------------------------|-------------------------------|---|------------------------------------|
| MATERIAL THICKNESS & APPLICATION |              | Fast Cut           | Deep Cut     | Cordless<br>Smooth<br>Cutting<br>Hole Saw | Fast Cut Multi<br>Purpose Hole<br>Saw | Stainless<br>Steel<br>Hole Saw | Carbide<br>Tipped<br>Hole Saw | Ceramic &<br>Abrasive<br>Material Hole<br>Saw | Brick &<br>Masonry<br>Dri-Core Dri |
| Hole Saw Depth                   |              | 41mm<br>1.5/8"     | 51mm<br>2"   | 13mm<br>1/2"                              | 54mm<br>2.1/8"                        | 13mm<br>1/2"                   | 41mm<br>1.5/8"                | Diameter<br>Dependant                         | Diameter<br>Dependant              |
| Recommended<br>Cutting<br>Depths | Hole Saw Ref | FCH                | DCH          | CSC                                       | FCH                                   |                                | MPH                           | D   |                                    |
|                                  | <3MM         | ✓                  |              | ✓   | $\checkmark$                          | <b>√</b>                       | ✓                             | <b>✓</b>                                      |                                    |
|                                  | 3-13MM       |                    | $\checkmark$ |   | ✓                                     |                                | ✓                             | ✓   |                                    |
|                                  | >13MM        |                    | ✓            |   | ✓                                     |                                | ✓                             | <b>√</b>                                      | ✓                                  |
| Metal/Inox (Stainless)           |              | **                 | **           | **  |                                       | **                             |                               |   |                                    |
| Non Ferrous<br>Material          |              | **                 | **           | **  |                                       | **                             |                               |   |                                    |
| Cast                             | Iron         | **                 | *            |   |                                       |                                | *                             |   |                                    |
| Wood                             |              | *                  | *            | *   | **                                    |                                | *                             |   |                                    |
| Nail Embedded Wood               |              |                    |              |   |                                       |                                | **                            |   |                                    |
| Veneer                           |              | *                  | *            | *   | **                                    |                                | **                            |   |                                    |
| MDF                              |              |                    |              |   | **                                    |                                |                               |   |                                    |
| Plastic                          |              | *                  | *            | *   | **                                    |                                | *                             |   |                                    |
| Acrylic                          |              | *                  | *            | *   | **                                    |                                | *                             |   |                                    |
| Ceramic                          |              |                    |              |   | *                                     |                                | *                             | **  |                                    |
| Porcelain/Glass/Stone            |              |                    |              |   |                                       |                                |                               | **  |                                    |
| Fibreglass                       |              | *                  | *            |   | *                                     |                                | **                            | **  |                                    |
| Formica                          |              | *                  | *            | *   | **                                    |                                | **                            |   |                                    |
| Plaster                          |              | *                  | *            | *   | **                                    |                                | **                            |   |                                    |
| Suspended Floors                 |              | *                  | *            |   |                                       |                                | **                            |   |                                    |
| Brick & Masonry                  |              |                    |              |   |                                       |                                | *                             | **  | **                                 |
| Cutting Po                       | erformance   |                    |              |   |                                       |                                |                               |   |                                    |
| Excellent                        | **           |                    |              |   |                                       |                                |                               |   |                                    |
| Satisfactory                     | *            |                    |              |   |                                       |                                |                               |   |                                    |

### **Starrett Hole Saws**

### The Fast Cut Bi-Metal Hole Saw

The Fast Cut saw combines a new tooth material, and a new tooth design, providing a smoother, faster cut on a wide range of materials, when compared against the previous Constant Pitch Saws.

#### **Features and Benefits**

- Ideal for stainless and mild steel sheet and tubes with a wall thickness of up to 3mm (1/8")
- New 5.5 TPI/25mm tooth form provides a smoother, faster cut in all materials
- New tooth material for enhanced heat and wear resistance and greater product life
- Cutting depth of 41mm (1.5/8")



Fast Cut Hole Saw.





Fast Cut Hole Saw application.

| ТҮРЕ    | Saw<br>Dia. | Pack<br>Cont. |
|---------|-------------|---------------|
| FCH0096 | 14mm        | 1             |
| FCH0058 | 16mm        | 1             |
| FCH1016 | 17mm        | 1             |
| FCH0034 | 19mm        | 1             |
| FCH2532 | 20mm        | 1             |
| FCH1036 | 21mm        | 1             |
| FCH0078 | 22mm        | 1             |
| FCH1056 | 24mm        | 1             |
| FCH0100 | 25mm        | 1             |
| FCH0116 | 27mm        | 1             |
| FCH0118 | 29mm        | 1             |
| FCH0136 | 30mm        | 1             |
| FCH0114 | 32mm        | 1             |
| FCH0156 | 33mm        | 1             |
| FCH0138 | 35mm        | 1             |
| FCH0176 | 37mm        | 1             |
| FCH0112 | 38mm        | 1             |
| FCH0196 | 40mm        | 1             |
| FCH0158 | 41mm        | 1             |
| FCH1116 | 43mm        | 1             |
| FCH0134 | 44mm        | 1             |
| FCH1136 | 46mm        | 1             |
| FCH0178 | 48mm        | 1             |
| FCH0200 | 51mm        | 1             |
| FCH0216 | 52mm        | 1             |
| FCH0218 | 54mm        | 1             |


# **Electrical Installation** Hole Saws



# **Starrett Hole Saws**

## The Fast Cut Hole Saw







Fast Cut Hole Saw Kits also available. See pg 52

|          | Saw   | Pack  |  |  |
|----------|-------|-------|--|--|
| TYPE     | Dia   | Cont. |  |  |
| FCH56MM  | 56mm  | 1     |  |  |
| FCH0214  | 57mm  | 1     |  |  |
| FCH0256  | 59mm  | 1     |  |  |
| FCH0238  | 60mm  | 1     |  |  |
| FCH0212  | 64mm  | 1     |  |  |
| FCH0296  | 65mm  | 1     |  |  |
| FCH0258  | 67mm  | 1     |  |  |
| FCH68MM  | 68mm  | 1     |  |  |
| FCH0234  | 70mm  | 1     |  |  |
| FCH0278  | 73mm  | 1     |  |  |
| FCH0300  | 76mm  | 1     |  |  |
| FCH0318  | 79mm  | 1     |  |  |
| FCH0314  | 83mm  | 1     |  |  |
| FCH0338  | 86mm  | 1     |  |  |
| FCH0312  | 89mm  | 1     |  |  |
| FCH0358  | 92mm  | 1     |  |  |
| FCH0334  | 95mm  | 1     |  |  |
| FCH0378  | 98mm  | 1     |  |  |
| FCH0400  | 102mm | 1     |  |  |
| FCH0418  | 105mm | 1     |  |  |
| FCH0414  | 108mm | 1     |  |  |
| FCH0438  | 111mm | 1     |  |  |
| FCH0412  | 114mm | 1     |  |  |
| FCH0434  | 121mm | 1     |  |  |
| FCH0500  | 127mm | 1     |  |  |
| FCH0514  | 133mm | 1     |  |  |
| FCH0512  | 140mm | 1     |  |  |
| FCH0600  | 152mm | 1     |  |  |
| FCH160MM | 160mm | 1     |  |  |
| FCH168MM | 168mm | 1     |  |  |
| FCH177MM | 177mm | 1     |  |  |
| FCH210MM | 210mm | 1     |  |  |