≣FCi Basics

Amphenol


BergStak® 0.635mm Connector

MICRO PITCH LOW PROFILE HIGH SPEED BOARD-TO-BOARD CONNECTOR

BergStak® 0.635mm pitch is a compact board-to-board connector with low stack height of 3.00mm. Available in 80 and 140 positions it support applications which require high pin counts and low profile connection.

BergStak® 0.635mm supports signal speeds up to 8Gb/s with an open-pin-field, providing design flexibility.

- Micro pitch of 0.635mm
- Low profile design to support 3mm stack height
- Polarization feature to prevent mis-mating
- Side walls to protect the contacts during mating
- High-speed performance



FEATURES

- Micro pitch of 0.635mm with a low profile design
- High pin counts of 80 and 140
- Polarization and mis-alignment features to support correct and easier mating
- Side walls to protect contacts
- High-speed performance of 8Gb/s with open-pin-field

BENEFITS

- High performance, space saving solution
- Ideal for applications that require high pin counts
- Prevents mis-mating and ensures proper mating
- Minimizes contact deforming risk during mating
- Offers design flexibility for high speed applications

TECHNICAL INFORMATION

MATERIAL

- Housing: High temperature thermoplastic LCP, Black (UL94V-0)
- Terminal: Copper Alloy, High spring
- Plating: Gold flash

ELECTRICAL PERFORMANCE

- Current Rating: 0.5A per contact (all contacts powered)
- Insulation Resistance: 1000MΩ min.
- Voltage Rating: 100VAC/DC
- LLCR: 20mΩ max.
- Data rate: 8Gb/s

MECHANICAL PERFORMANCE

- Mating and un-mating Force: 0.7N max. & 0.12N min./ contact
- Durability: 50 cycles
- Mechanical Shock: EIA 364-27
- Vibration: MIL-STD-202, Method 201

ENVIRONMENTAL

- Operating Temperature Range: -55°C to +85°C
- Salt Spray: 5% Salt Concentration, 48H
- SO2 Gas: 50 ± 5ppm SO2 gas, 24H

PART NUMBER SELECTOR

BASE NUMBER LF AA C D Ε R Description Part Number Pick/Place Lead-free D Option Vertical Receptacle 10169698 0 Vacuum tape Vertical Header 10169697 **Plating Option** Packaging AA Position 0 Gold flash R Tape and Reel 40 80 70 140 **Height Option** В 0 3mm stack height

APPROVALS AND CERTIFICATIONS

• UL E66906

SPECIFICATIONS

Product Specification: GS-12-1709

PACKAGING

• Tape and Reel

TARGET MARKETS/APPLICATIONS



Advanced Driver Assistance Systems (ADAS)



Server/Storage

Automation Machines



Medical Devices

www.amphenol-cs.com Please note that the above information is subject to change without notice.

Disclaimer

PART NUMBERS

Description	Part Numbers
BergStak® 0.635mm, 80position, Receptacle, 3mm stack height	10169698-40000RLF
BergStak® 0.635mm, 140position, Receptacle, 3mm stack height	10169698-70000RLF
BergStak® 0.635mm, 80position, Header, 3mm stack height	10169697-40000RLF
BergStak® 0.635mm, 140position, Header, 3mm stack height	10169697-70000RLF

www.amphenol-cs.com