THICK FILM (WIDE TERMINAL TYPE LOW RESISTANCE)

WK73S Wide Terminal Type Flat Chip Resistors (High Power)



Coating color : Black

Features

- \bullet Higher power than conventional type.
- Flat chip resistors of wide terminal type.
- High reliability and performance with T.C.R. $\pm 100 \times 10^{-6}$ /K, resistance tolerance ± 1 %.
- Suitable for both reflow and flow solderings.
- Products meet EU-RoHS requirements. EU-RoHS regulation is not intended for Pb-glass contained in
- electrode, resistor element and glass.
- AEC-Q200 Tested.

Applications

• Power supply, ECU etc.

Reference Standards

IEC 60115-8 JIS C 5201-8 EIAJ RC-2134C

Construction



EU RoHS

Dimensions

Туре		Weight(g)				
(Inch Size Code)	L±0.15	W	c±0.2	d±0.15	t±0.1	(1000pcs)
2B15(0612)	1.6	3.2±0.2	0.3	0.45		12.0
2H2(1020)	2.5	5.0±0.15	0.4	0.75	0.6	30.2
3A3(1225)	3.1	6.3±0.15	0.45	0.75		45.6

Type Designation

Example



Resistance Value (Ω)	3 digits		Resistance Value (Ω)	4 digits	
10m~91m	10L~91L	[22m~97.6m	22L0~97L6	
0.1~9.1	R10~9R1		0.1~9.76	R100~9R76	

Contact us when you have control request for environmental hazardous material other than the substance specified by $\operatorname{EU-RoHS}$.

For further information on taping, please refer to APPENDIX C on the back pages.

Ratings

	Power Bating	Rated Ambient	Rated Terminal Part	T.C.R. (x 10 ⁻⁶ /K)	F	Taping & Q'ty/Reel			
Туре					D:±0.5%	F:±1%	J:±5%	(pcs)	
		. emp.	. op.		E24 · E96	E24 · E96	E24	TD	TE
				±100	430m~9.76	430m~9.76	430m~9.1		
WK73S2B15	1.5W ^{≋1}	70°C	95℃	±200	—	30m~422m	30m~390m	5,000	-
				±800	—	—	10m~27m		
WK73S2H2	2W*1	70°C	95°C	±100	_	220m~9.76	220m~9.1		4,000
				±200	—	27m~215m	27m~200m		
				±800	—	-	10m~24m		
				±100	_	360m~9.76	360m~9.1		
WK73S3A3	3W*1	70℃	95°C	±200	—	33m~357m	33m~330m		4,000
				±300	-	22m~32.4m	22m~30m	—	
				±800	_	_	10m~20m		

Operating Temperature Range : $-55^{\circ}C \sim +155^{\circ}C$

Rated voltage= $\sqrt{Power Rating \times Resistance value}$

#1 If you use at the rated power, please keep the condition that the terminal of the resistor is below the rated terminal part temperature. Please refer to the derating curves based on the terminal temperature of right side on the next page.

If any questions arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature" in your usage conditions, please give priority to the "Rated Terminal Part Temperature". For more details, please refer to "Introduction of the derating curves based on the terminal part temperature" on the beginning of our catalog.

Derating Curve



For resistors operated at an ambient temperature of 70 $^{\circ}\mathrm{C}$ or higher, the current shall be derated in accordance with the above derating curve.

Terminal part temperature



When the terminal part temperature of the resistor exceeds the rated terminal part temperature shown above, the power shall be derated according to the derating curve.

Please refer to "Introduction of the derating curves based on the terminal part temperature" on the beginning of our catalog before use.

One-Pulse Limiting Electric Power



Please ask us about the resistance characteristic of continuous applied pulse. The pulse endurance values are not assured values, so be sure to check the products on actual equipment when you use them.

Temperature Rise



Regarding the temperature rise, the value of the temperature varies per conditions and board for use since the temperature is measured under our measuring conditions.



Performance

Toot Homo	Performance Requirements	$\Delta R \pm (\% + 0.005 \Omega)$	Taat Mathada	
restitems	Limit	Typical	Test Methods	
Resistance	Within specified tolerance	—	25°C	
T.C.R.	Within specified T.C.R	—	+25°C/-55°C and +25°C/+125°C	
Overload (Short time)	2	0.2	Rated voltage × 2.0 for 5s	
Resistance to soldering heat	1	0.2	260°C±5°C, 10s±1s	
Bending test	1	0.1	Holding point 90mm, Bending 1 time. Bending 5mm	
Rapid change of temperature	2	1	-55°C (30min.) / +125°C (30min.) 1000 cycles	
Moisture resistance	2	0.2	40°C±2°C, 90%~95%RH, 1000h 1.5h ON/0.5h OFF cycle	
Endurance at 70°C or rated terminal part temperature	2	0.2	$70^{\circ}C \pm 2^{\circ}C$ or rated terminal part temperature $\pm 2^{\circ}C$ 1000h 1.5h ON/0.5h OFF cycle	
High temperature exposure	2 : J (±5%) 1 : others	0.5 : J (±5%) 0.2 : others	+155°C, 1000h	

Precautions for Use

- The substrate of chip resistors is alumina. Cracks may occur at the connection of solder (solder fillet portion) due to the difference of the coefficient of thermal expansion from a mounting board when heat stress like heat cycle, etc. are repeatedly given to them. Care should be taken to the occurrence of the cracks when the change in ambient temperature or ON/OFF of load is repeated, especially when WK73 series which have self-heating. The occurrence of the crack by heat stress may be influenced by the size of a pad, solder volume, heat radiation of mounting board etc., so please pay careful attention to designing when a big change in ambient temperature and conditions for use like ON/OFF of load can be assumed.
- In the resistance values of $50m\Omega$ or under, the resistance value after soldering may change depending on the size of pad pattern or solder amount. Make sure the effect of decline/increase of resistance value before designing.