

Package For/Supply By



## **Wakefield**Thermal

# SAFETY DATA SHEET

OSHA HCS (29 CFR 1910.1200)

### SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

Product identifier Chemical Name CAS No. Trade Name Product Code

Not applicable. Mixture Grey Ice 518 None

Relevant identified uses of the substance or mixture and uses advised against

Identified Use(s) Uses Advised Against

**Company Identification** 

Telephone E-Mail (competent person)

Emergency telephone number Emergency Phone No. None vised against

Heat conducting paste for electronics None

Timtronics 35 Old Dock Road. Yaphank, NY 11980

(631) 345-6509 info@timtronics.com

Medical Emergency: PROSAR 24 hr: 1-800-217-5157 / 1-651-523-0304

Transportation Emergency: CHEMTREC 24 hr. 1-800-424-9300 / 1 (703) 527-3887 (Collect calls accepted)

### **SECTION 2: HAZARDS IDENTIFICATION**

 Classification of the substance or mixture
 OSHA HCS (29 CFR 1910.1200)
 Not classified as dangerous for supply/use.

 Label elements
 Hazard Symbol
 None

 Hazard Statement(s)
 None

 Precautionary Statement(s)
 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.

 IF ON SKIN: Wash with plenty of soap and water.
 Keep out of reach of children.

 Other hazards
 None

#### Other nazards

### SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients	% wt.	CAS No.
Zinc Oxide	4.0	1314-13-2

Additional Information - None



Package For/Supply By

# WAKEFIELDTHERMAL

122 Series Grey Ice 518

### **SECTION 4: FIRST AID MEASURES**



#### Description of first aid measures Inhalation Unlikely to be required but if necessary treat symptomatically. Skin Contact Unlikely to be required but if necessary treat symptomatically. Eye Contact IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.If symptoms occur obtain medical attention. Ingestion Do not induce vomiting wash out mouth with water.Do not give anything by mouth to an unconscious person. Seek medical treatment. Most important symptoms and effects, both acute and None delayed Indication of any immediate medical attention and None special treatment needed

### SECTION 5: FIRE-FIGHTING MEASURES

#### **Extinguishing Media**

- J	
-Suitable Extinguishing Media -Unsuitable Extinguishing Media	As appropriate for surrounding fire. None known.
Special hazards arising from the substance or mixture	None known.
Advice for fire-fighters	A self contained breathing apparatus and suitable protective clot should be worn in fire conditions. Keep containers cool by spravi

A self contained breathing apparatus and suitable protective clothing should be worn in fire conditions. Keep containers cool by spraying with water if exposed to fire.

SECTION 6: ACCIDENTAL RELEASE MEASURES		
Personal precautions, protective equipment and emergency procedures	Not normally required. Wear protective gloves/eye protection.	
Environmental precautions	Not normally required. Contain effluent and prevent effluent from	

 Methods and material for containment and cleaning up
 Transfer to a container for disposal or recovery.

 Reference to other sections
 None

 Additional Information
 None

## SECTION 7: HANDLING AND STORAGE

Precautions for safe handling

Avoid contact with skin and eyes.

Conditions for safe storage, including any incompatibilities

-Storage temperature Store at room temperature. -Incompatible materials None known



### Package For/Supply By

122 Series Grey Ice 518

## WAKEFIELDTHERMAL

Specific end use(s)

Heat conducting putty for electronics

Deete

### SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

#### **Occupational Exposure Limits**

	(8hr TWA)			ST	STEL	
SUBSTANCE.	CAS No.	PEL (OSHA)	TLV (ACGIH)	PEL (OSHA)	TLV (ACGIH)	Note:
Unlikely to be hazardous by inhalation.						
Recommended monitoring method		Unlikely to b	e hazardous by	inhalation.		
Exposure controls Appropriate engineering controls		No special r	measures are re	equired.		
Personal protection equipment						
Eye/face protection		Not normall	y required.			
Skin protection (Hand protection/ Other)     Not normally required.						
Respiratory protection		Normally no	personal respi	ratory protecti	on is necessar	у.
Thermal hazards			y required.Use when needed.	gloves with in	sulation for the	ermal
Environmental Exposure Controls Avoid release to the environment.				nment.		

### SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### Information on basic physical and chemical properties

Appearance	Paste
Color.	Grey
Odor	Not available
Odor Threshold (ppm)	Not available
pH (Value)	Not available
Melting Point (°C) / Freezing Point (°C)	Not available
Boiling point/boiling range (°C):	> 200
Flash Point (°C)	> 200
Evaporation Rate	< 1
Flammability (solid, gas)	Not available
Explosive Limit Ranges	Not available
Vapour pressure (Pascal)	Not available
Vapour Density (Air=1)	Not available
Density (g/ml)	2.2
Solubility (Water)	Insoluble
Solubility (Other)	Not available
Partition Coefficient (n-Octanol/water)	Not available



Auto Ignition Point (°C) Decomposition Temperature (°C) Kinematic Viscosity Explosive properties Oxidizing properties

Other information

### Package For/Supply By

# WAKEFIELDTHERMAL

122 Series Grey Ice 518

Not available Not available Not available Not explosive. Not oxidizing.

Not available

### SECTION 10: STABILITY AND REACTIVITY

Reactivity Chemical stability Possibility of hazardous reactions Conditions to avoid Incompatible materials Hazardous decomposition product(s) Stable under normal conditions. Stable. None anticipated. None known None known None known

### SECTION 11: TOXICOLOGICAL INFORMATION

Exposure routes: Skin Contact, Eye Contact

This material is unlikely to present a significant health hazard under normal conditions of handling and use.

### SECTION 12: ECOLOGICAL INFORMATION

#### Toxicity

<u>Zinc oxide (CAS # 1314-13-2)</u>	
Short term	LC50 (96 hour): 1.793 mg/L (Danio rerio) EC50 (48 hour): 2.6-9 mg/l ( <i>Daphnia magna,</i> mobility <i>)</i> IC50 (96 hour): 0.136 mg/l ( <i>Pseudokirchnerella subcapitata</i> )
Long Term (By analogy with similar materials)	NOEC (30 days) 0.0 75 mg/l (Jordanella floridae) NOEC (21 days): 0.156 mg/l ( <i>Daphnia magna</i> ) NOEL (72 hour) 0.06 mg/l ( <i>Cladophora glomerata)</i>
Persistence and degradability	This substance is predicted not to degrade in soil and water.
Bioaccumulative potential	The substance has low potential for bioaccumulation.
Mobility in soil	The substance has low mobility in soil.
Results of PBT and vPvB assessment	Not classified as PBT or vPvB.
Other adverse effects	None known.

#### **SECTION 13: DISPOSAL CONSIDERATIONS**

Waste treatment methods

Disposal should be in accordance with local, state or national legislation. Consult an accredited waste disposal contractor or the local authority for advice.

### **SECTION 14: TRANSPORT INFORMATION**

The information shown below is for packages exceeding 30 kg (66 lbs), gross weight, and/or when any inner packagages exceed 5 kg (11 pounds). For limited quantities, packaging materials must nonetheless comply with applicable specifications and may nonetheless require certain labeling information (e.g. the UN number in a black diamond). Refer to applicable hazardous materials transportation regulations.

	Land transport	Sea transport	Air transport
	<u>(U.S. DOT)</u>	<u>(IMDG)</u>	(ICAO/IATA)
UN number	UN3077	UN3077	UN3077



### Package For/Supply By

# WAKEFIELDTHFRMAL

### **122 Series Grey Ice** 518

Proper Shipping Name	Environmentally Hazardous Substance, solid, n.o.s. (zinc oxide)	Environmentally Hazardous Substance, solid, n.o.s. (zinc oxide)	Environmentally Hazardous Substance, solid, n.o.s. (zinc oxide)
Transport hazard class(es)	9	9	9
Packing group	None	None	None
Environmental hazards	Yes	Yes	Yes
Special precautions for user	None assigned	None assigned	None assigned

Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code: Not applicable

### **SECTION 15: REGULATORY INFORMATION**

Safety, health and environmental regulations/legislation specific for the substance or mixture:

TSCA (Toxic Substance Control Act) - Inventory Status: All components listed or polymer exempt.

Designated Hazardous Substances and Reportable Quantities (40 CFR 302.4):

			RQ
Chemical Name	CAS No.	Typical %wt.	(Pounds)
None			

#### SARA 311/312 - Hazard Categories: None

Fire Sudden Release Reactivity Immediate (acute) Chronic (delayed)

#### SARA 313 - Toxic Chemicals (40 CFR 372):

Chemical Name	CAS No.	Typical %wt.
Zinc compounds	1314-13-2	4.0

#### SARA 302 - Extremely Hazardous Substances(40 CFR 355):

Chemical Name	CAS No.	Typical %wt.	TPQ (pounds)
None			

#### California Proposition 65 List:

Chemical Name	CAS No.	Type of Toxicity
None		

### **SECTION 16: OTHER INFORMATION**

The following sections contain revisions or new statements: 1-16. Date of preparation: September 01, 2017. Date of Revision: January 01,2021

Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.