

TSC 10

Torque wrench TSC SLIPPER

1-10 N·m / with Scale

Code	ETIM
1196510	EC002132 Drehmomentschlüssel
EAN	UNSPSC
4002805918302	27-11-17-15 Drehmomentschlüssel
Country of origin	eCl@ss
England	21-04-02-22 Drehmomentschlüssel
Customs tariff number	
82041100	



Article description

- Use:
- Controlled screw tightening in the range of 2 - 10 Nm
- Ideal for assembly work where controlled tightening with low torque values is required (e.g. electronic hardware sector, precision mechanics etc.)
- Features:
- Adjustable torque wrench - with scale
- 1/4" square drive with ball locking device
- With integrated ratchet-function for controlled clockwise tightening
- Working accuracy: +/- 6 % tolerance of set torque
- Acc. to DIN EN ISO 6789, traceable to national standards
- Precision mechanism slips very noticeably and audibly ("click") when the pre-set value is achieved - over-tightening is not possible
- Micrometer graduation: 0.1 Nm
- 2 models in the range 1 - 10 Nm
- Lightweight, but robust and corrosion-resistant construction design
- Very convenient non-slip rubber handgrip
- EPA-conformant (Electrostatic Protected Area), for use in sensitive electrostatic applications
- Scope of delivery: • Torque wrench Typ TSC SLIPPER
- Test certificate acc. to DIN EN ISO 6789
- Delivery in sturdy cardboard packaging

Article information

Drive connector square (male)	1/4"	vernier Nm	0,1 Nm
Contents (Qty of pieces)	1	REACH registration available	no
Total length [mm]	195 mm	Net weight [kg]	0,235 kg
Torque (min.) [N·m]	2 Nm	Trigger mechanism	Friction clutch
Torque (max.) [N·m]	10 Nm	Precision +/-	+/- 6 %
Torque range (min./max.) [N·m]	2 Nm - 10 Nm	Direction of tightening	Right
Drive connector square (male)	6,3 mm	Fixed setting	no
Epa-/Esd-Model	no	Test certificate	DIN EN ISO 6789-2:2017
Drive type/drive	Single square ratchet		