AMP | AMP CPC

TE Internal #: 206039-1

Circular Power Connectors, Housing, 250 VDC, Wire-to-Wire, 28 Position, Wire & Cable, Plug, Reverse Gender, Pin, Signal, Black, All

Plastic, AMP CPC

View on TE.com >



Connectors > Power Connectors > Circular Power > Circular Power Connectors > CPC Connectors, Series 2











Connector Product Type: Housing

Operating Voltage: **250 VDC**Connector System: **Wire-to-Wire**

Number of Positions: 28

Sealable: No

All CPC Connectors, Series 2 (24)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	28
Number of Power Positions	0
Number of Signal Positions	28

Electrical Characteristics



Operating Voltage	250 VAC
Contact Features	
Reverse Gender	Yes
Contact Type	Pin
Contact Current Rating (Max)	7.5 A
Contact Protection	With
Mechanical Attachment	
Mating Alignment Type	Keyed
Mating Alignment	With
Panel Mount Feature Type	Flange
Mating Retention Type	Threaded Coupling
Screw & Hole Thread Size	15/16-20 UNEF – 2A
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Panel Mount Feature	Without
Housing Features	
Body Orientation	Straight
Housing Color	Black
Housing Material	Polyester, Thermoplastic
Circular Connector Shell Size	17
Circular Connector Shell Size Dimensions	17
	1.73 mm[.068 in]
Dimensions	
Dimensions Accepts Insulation Diameter Range	
Dimensions Accepts Insulation Diameter Range Usage Conditions	1.73 mm[.068 in]
Dimensions Accepts Insulation Diameter Range Usage Conditions Operating Temperature Range	1.73 mm[.068 in] -55 – 105 °C[-67 – 221 °F]
Dimensions Accepts Insulation Diameter Range Usage Conditions Operating Temperature Range Fluid Resistance	1.73 mm[.068 in] -55 – 105 °C[-67 – 221 °F]
Dimensions Accepts Insulation Diameter Range Usage Conditions Operating Temperature Range Fluid Resistance Operation/Application	1.73 mm[.068 in] -55 – 105 °C[-67 – 221 °F] None
Dimensions Accepts Insulation Diameter Range Usage Conditions Operating Temperature Range Fluid Resistance Operation/Application Circuit Application	1.73 mm[.068 in] -55 – 105 °C[-67 – 221 °F] None Signal
Dimensions Accepts Insulation Diameter Range Usage Conditions Operating Temperature Range Fluid Resistance Operation/Application Circuit Application Shielded	1.73 mm[.068 in] -55 – 105 °C[-67 – 221 °F] None Signal
Dimensions Accepts Insulation Diameter Range Usage Conditions Operating Temperature Range Fluid Resistance Operation/Application Circuit Application Shielded Industry Standards	1.73 mm[.068 in] -55 – 105 °C[-67 – 221 °F] None Signal No



Packaging Method	Bag	
3 3	\mathcal{J}	

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts













TE Part # CAT-035-DCCSC20
D-Sub Conn Contacts: Socket,
Phosphor Bronze, Signal, Size 20



TE Part # CAT-035-DCCPB20
D-Sub Connector Contacts: Pin, Brass,
Signal, Size 20



TE Part # 213810-1 CPC COUPLING RING SIZE 17



TE Part # CAT-AM71-C83998DD

Connectors, CPC Series 2, with Posted
Contacts



TE Part # 91503-1 CCII AMPLIMITE 20 DF PIN SKT 28-20 ASSY



TE Part # 207241-1 CABLE BOOT,SZ 17,CPC



TE Part # 207387-1 CABLE GRIP,SZ 17,CPC



TE Part # 207387-2 CABLE GRIP,SZ 17,CPC



TE Part # 208652-1 SEALING CAP ASSY,SZ 17,CPC



TE Part # 205089-1 HD 20 PIN CONTACT



TE Part # 205090-1 HD 20 SOCKET CONTACT




TE Part # 601966-5 K13-1 POSITIONER



TE Part # 207445-3

TE Part # 207445-3
SEALING CAP ASSY, 17,CPC ROHS
Compliant

=TE



TE Part # 205089-2
PIN CONTACT,SZ 20,AMPLIMITE



Also in the Series | AMP CPC




Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)





Circular Connector Keying Plugs(2)



Circular Connector Seals(36)



Circular Power Connectors(460)



Insertion & Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #213870-1 23-19 RCPT HSG,STD SEX,CPC



TE Part #206437-1 CPC Connectors, Series 2



TE Part #6609021-1 1VB1=F7120 S0



TE Part #52464-1 TERMINAL,PG SPR SPD 16-14 8







Documents

Product Drawings

CPC PLUG ASSEMBLY SIZE 17-28

English

CAD Files

3D PDF

English

Customer View Model ENG_CVM_206039-1_F.2d_dxf.zip



English

Customer View Model

ENG_CVM_206039-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_206039-1_F.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_206039-1_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_206039-1_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_206039-1_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications

Connector, Circular Plastic

English

Product Specification

English

Product Environmental Compliance

MD_206039-1_08232017021_dmtec

English

MD_206039-1_08232017021_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English

Circular Power Connectors, Housing, 250 VDC, Wire-to-Wire, 28 Position, Wire & Cable, Plug, Reverse Gender, Pin, Signal, Black, All Plastic, AMP CPC

