1-480703-0 ACTIVE

MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 1-480703-0

Rectangular Power Connectors, Housing, Receptacle, Wire-to-Wire / Wire-to-Panel, 4 Position, 6.35 mm [.25 in] Centerline, Universal

MATE-N-LOK

View on TE.com >



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors











Rectangular Power Connector Type: Housing

Connector & Housing Type: Receptacle

Connector System: Wire-to-Panel, Wire-to-Wire

Number of Positions: 4

Centerline (Pitch): 6.35 mm [.25 in]

Features

Product Type Features

Product Type Features	
Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Configuration Features	
Number of Positions	4
Number of Rows	1
Electrical Characteristics	
Operating Voltage	600 VDC
Contact Features	
Multiple Contact Types	Without
Contact Layout	Inline

Without

Contact Retention Within Housing



Contact Type	Pin
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
Panel Mount Feature	With
Panel Mount Feature Type	Patch & Tabs
Connector Mounting Type	Panel Mount
Housing Features	
Centerline (Pitch)	6.35 mm[.25 in]
Housing Color	Natural
Housing Material	Nylon
Dimensions	
Panel Thickness (Recommended)	.76 – 2.29 mm[.03 – .09 in]
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Industry Standards	
CSA Rating	Certified, LR 7189
UL Rating	Recognized
Agency/Standard	CSA, UL, VDE
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire
Packaging Features	
Packaging Quantity	1
Packaging Method	Package

Compliant

EU RoHS Directive 2011/65/EU



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-onreach

Compatible Parts



UMNL PIN 12-10 AU/PHBZ



TE Part # 350551-6 UMNL SOK 20-14 AU/PHBZ L/P



TE Part # 350690-2 UMNL PIN 24-18 AUBR L/P















TE Part # 350689-2 UMNL SOK 24-18 AUBR L/P



TE Part # 640310-3 UMNL SOK 12-10 PTPPHBZ



TE Part # 350689-3 UMNL SOK 24-18 PTPPHBZ L/P



TE Part # 350690-7 UMNL PIN 24-18 AUBR L/P



TE Part # 350689-1 UMNL SOK 24-18 PTPBR L/P



TE Part # 926893-3 UNIV.M-N-L.SOCKET



TE Part # 350550-6

UMNL SOK 20-14 AU/PHBZ L/P



TE Part # 350705-7
UMNL SPLIT PIN 20-14 AUBR L/P



TE Part # 350547-3
UMNL PIN 20-14 PTPPHBZ L/P



TE Part # 350551-7 UMNL SOK 20-14 AU/BR L/P



TE Part # 350547-2 UMNL PIN 20-14 AUBR L/P



TE Part # 350550-2 UMNL SOK 20-14 AU/BR L/P

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Contacts(7)



Insertion & Extraction Tools(4)



Power Contacts(201)



Rectangular Boots & Strain Relief(34)



Rectangular Connector Adapters(7)



Rectangular Connector Hardware(1)



Rectangular Connector Housings(1)





Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(662)

Customers Also Bought



TE Part #1-480711-0 15P UMNL CAP HSG NATL



TE Part #1-480706-0 09P UMNL PLUG HSG NATL



TE Part #1-480707-0 09P UMNL CAP HSG NATL



TE Part #1-480708-0 12P UMNL PLUG HSG NATL



TE Part #1-480698-0 02P UMNL PLUG HSG NATL



TE Part #1-480705-0 06P UMNL CAP HSG NATL



TE Part #1-480704-0 06P UMNL PLUG HSG NATL



TE Part #1-480709-0 12P UMNL CAP HSG NATL



TE Part #1-480700-0 03P UMNL PLUG HSG NATL



TE Part #1-2176368-9
RQ 0603 76K8 0.1% 10PPM 1K RL

Documents

Product Drawings
04P UMNL CAP HSG NATL

English

CAD Files

3D PDF

3D

Customer View Model ENG_CVM_CVM_1-480703-0_BM.2d_dxf.zip

05/01/2023 02:38PM | Page 5



English

Customer View Model

ENG_CVM_CVM_1-480703-0_BM.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-480703-0_BM.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_1-480703-0_06072018856_dmtec

English

MD_1-480703-0_06072018856_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English