

Section 1 - Chemical Product and Company Identification

Chemical Product Identification

Name : Sealed Lead Acid Battery
Details of the Supplier : Premier Farnell plc
150 Armley Road
Leeds
LS12 2QQ
+44 (0) 8701 202530
Emergency Telephone : +44 1865 407333

Section 2 - Hazards Identification

Emergency overview : This product is a battery. Intended use of the product should not result in exposure to the chemical substance. In case of rupture the below hazards exist.

Classification according to GHS

Skin corrosion/irritation (1A, 1B, 1C)
Serious eye damage/eye irritation (1)
Specific target organ toxicity, repeated exposure (2)
Hazardous to the aquatic environment, long-term hazard (1)

Label elements

Hazard pictogram(s):



Signal word : Warning

Hazard statement(s):

H314 Causes severe skin burns and eye damage
H318 Causes serious eye damage
H373 May cause damage to organs through prolonged or repeated exposure
H410 Very toxic to aquatic life with long lasting effects

Precautionary statement(s):

Prevention:

P260 Do not breathe dusts or mists.
P264 + P265 Wash skin and clothing thoroughly after handling. Do not touch eyes.
P280 Wear protective gloves, protective clothing, eye protection, face protection.
P273 Avoid release to the environment.

Response:

P310 Immediately call a POISON CENTER.
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water.
P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P363 Wash contaminated clothing before reuse.
P391 Collect spillage.

Storage

P405 Store locked up.

Disposal:

P501 Send contents to approved waste treatment plants.

Other hazards

Physical and chemical hazards: See Section 10

Human health hazards: See Section 11

Environmental hazards: See Section 12

Section 3 - Composition/Information on Ingredients

Chemical characterization : Mixture

Chemical Composition	CAS No.	EC#	Weight(%)
Dicalcium lead tetraoxide	12013-69-3	234-591-3	60-70
Acrylonitrile-butadiene-styrene terpolymer	9003-56-9	618-371 -8	5
Glass, oxide, chemicals	65997-17-3	266-046-0	5
Sulfuric acid	7664-93-9	231-639-5	10-20

Section 4 - First Aid Measures

Description of first aid measures

General information No special measures required.

After eye contact

Flush eyes with plenty of water for several minutes while holding eyelids open. Get medical attention if irritation persists.

After skin contact

Remove contaminated clothing and shoes. Immediately wash with water and soap and rinse thoroughly. Wash clothing and shoes before reuse. If irritation occurs, get medical attention.

After inhalation

Remove victim to fresh area. Administer artificial respiration if breathing is difficult. Seek medical attention.

After swallowing

Do not induce vomiting. Get medical attention.

Personal protective equipment for first-aid responders: No data available.

Most important symptoms/effects, acute and delayed: No data available.

Indication of immediate medical attention and special treatment needed: Treat symptomatically.

Section 5 - Fire Fighting Measures

Suitable extinguishing media:

Small Fire: Dry chemical, CO₂ or water spray. Large Fire: Dry chemical, CO₂, alcohol-resistant foam or water spray. Move containers from fire area if you can do it without risk. Dike fire-control water for later disposal; do not scatter the material.

Unsuitable extinguishing media:

No data available.

Specific Hazards arising from the chemical:

Special hazards arising from the substance or mixture

Battery may burst and release hazardous decomposition products when exposed to a fire situation. TOXIC; inhalation, ingestion or skin contact with material may cause severe injury or death. Contact with molten substance may cause severe burns to skin and eyes. Avoid any skin contact. Effects of contact or inhalation may be delayed. Fire may produce irritating, corrosive and/or toxic gases. Runoff from fire control or dilution water may be corrosive and/or toxic and cause pollution.

Specific protective actions for fire-fighters:

Wear positive pressure self-contained breathing apparatus (SCBA). Structural firefighters' protective clothing will only provide limited protection.

Section 6 - Accidental Release Measures**Personal precautions:**

As an immediate precautionary measure, isolate spill or leak area in all directions for at least 50 meters (150 feet) for liquids and at least 25 meters (75 feet) for solids. Keep unauthorized personnel away. Stay upwind, uphill and/or upstream. Ventilate the area before entry.

Protective equipment:

No data available.

Emergency procedures:

ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Stop leak if you can do it without risk. Prevent entry into waterways, sewers, basements or confined areas.

Absorb or cover with dry earth, sand or other non-combustible material and transfer to containers.

DO NOT GET WATER INSIDE CONTAINERS.

Environmental precautions:

Do not allow material to be released to the environment without proper governmental permits.

Methods and materials for containment and cleaning up:

All waste must refer to the United Nations, the national and local regulations for disposal.

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

Section 7 - Handling and Storage**Precautions for safe handling:**

Do not short or install with incorrect polarity. Avoid all personal contact, including inhalation. Wear protective clothing when risk of exposure occurs. Use in a well-ventilated area. Prevent concentration in hollows and sumps.

Conditions for safe storage, including any incompatibilities:

Store in a cool, dry, well-ventilated place. Keep away from heat, avoiding the long time of sunlight.

Keep container tightly sealed.

Section 8 - Exposure Controls/Personal Protection**Control parameters**

CAS No.	ACGIH	NIOSH	OSHA
12013-69-3	N/A	N/A	N/A
9003-56-9	N/A	N/A	N/A
65997-17-3	N/A	N/A	N/A
7664-93-9	TLV-1WA 0.2mg/m ³	REL-1WA 1 mg/m ³	PEL-1WA 1mg/m ³

Appropriate engineering controls:

The usual precautionary measures for handling chemicals should be followed.

Keep away from foodstuffs, beverages and feed.

Remove all soiled and contaminated clothing immediately.

Wash hands before breaks and at the end of work.

Personal Protective Equipment:

Respiratory protection : Wear suitable protective mask. For a large large number of battery leakages, wear chemical protective clothing, including self-contained breathing apparatus.

Hand Protection : Wear appropriate protective gloves to reduce skin contact.

Eye Protection : Wear safety goggles or eye protection combined with respiratory protection.

Skin and Body Protection : Working environment required, wear suitable protective clothing to minimize contact with skin. The type of protective equipment must be according to the concentration and the content of certain hazardous substances in the workplace.

Section 9 - Physical and Chemical Properties

Information on basic physical and chemical properties

General information

Appearance : Black

Form : Prismatic

Odour : Not available.

Odour threshold : Not available.

pH : Not available.

Melting point/freezing point : Not available.

Boiling point or
Initial boiling point and boiling range : Not available.

Flash Point : Not available.

Flammability : Not available.

Solubility : Not available.

Lower and upper explosion
limit/flammability limit : Not available.

Auto-ignition temperature : Not available.

Decomposition temperature : Not available.

Kinematic viscosity : Not available.

Partition coefficient: n-octanol/water
(log value) : Not available.

Vapour pressure : Not available.

Density and/or relative density : Not available.

Relative vapour density : Not available.

Particle characteristics : Not available.

Other information : -

Voltage : 12V

Electric capacity : 1.2Ah 2.3Ah 3.2Ah 7Ah 12Ah 18Ah

Section 10 - Stability and Reactivity

Reactivity : No data available.

Chemical stability : Stable.

Possibility of hazardous reactions : No data available.

Conditions to Avoid : Flames, sparks, and other sources of ignition, incompatible materials.

Incompatible materials : Oxidizing agents, acid base.

Hazardous decomposition products: Carbon monoxide, carbon dioxide.

Section 11 - Toxicological Information

Acute Toxicity:

CAS No.	LC50/LD50
12013-69-3	No data available.
9003-56-9	No data available.
65997-17-3	No data available.
7664-93-9	LD50 Rat (oral): 2140mg/kg

Skin irritation/corrosion : No data available.
Serious eye damage/irritation : No data available.
Respiratory or Skin sensitisation : No data available.
Germ Cell mutagenicity : No data available.
Carcinogenicity : No data available.
Reproductive Toxicity : No data available.
Specific target organ toxicity-Single exposure : No data available.
Specific target organ toxicity-Repeated exposure : No data available.
Aspiration hazard : No data available.
Information on the likely routes of exposure : No data available.
Eye : No data available.
Skin : No data available.
Ingestion : No data available.
Inhalation : No data available.

Section 12 - Ecological Information

Ecological Toxicity

CAS# 7664-93-9

LC50 : 16-28mg/L- fishes (Bluegill)- 96h
Persistence and degradability : No data available.
Bioaccumulative Potential : No data available.
Mobility in Soil : No data available.
Other adverse effects : No data available.

Section 13 - Disposal Considerations

Disposal methods:

Recommendation : Consult state, local or national regulations to ensure proper disposal.

Uncleaned packaging

Recommendation : Disposal must be made according to official regulations.

Section 14 - Transport Information

UN or ID Number

IATA : UN2800
IMDG : UN2800

Proper Shipping Name/Description

IATA : Batteries, wet, non-spillable
IMDG : BATTERIES, WET, NON-SPILLABLE

Packing Group

IATA : N/A
IMDG : N/A

Hazard Label

IATA : N/A
IMDG : N/A

Environmental hazards

Marine pollutant : No
IMDG EmS : F-A, S-8
Special precautions for user : No information available.
Transport information : Sealed Lead Acid Battery 6V Battery has passed the Vibration test , Pressure differential test, Non-spillable test, according to the report ID: MQIKB2QG2402597U5.

According to the Special Provisions A67 of IATA DGR 641h Edition, special provision 238 of IMDG (40-20), the goods are not subject to other provision of this code.

Separate batteries when shipping to prevent short-circuiting. They should be packed in strong packaging for support during transport.

Transport Fashion : By air, by sea.

Section 15 - Regulatory Information

Safety, health and environmental regulations/legislation specific for the substance or mixture

CAS No.	TSCA	IECSC	DSL/NDL	EINECS/ ELINCS/ NLP
12013-69-3	Listed	Listed	Listed DSL	Listed
9003-56-9	Listed	Listed	Listed DSL	Listed
65997-17-3	Listed	Listed	Listed DSL	Listed
7664-93-9	Listed	Listed	Listed DSL	Listed

Section 16 - Other Information

Modification record:

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Other Information:

CAS: (Chemical Abstracts Service);

EC: (European Commission);

ACGIH: (American Conference of Governmental Industrial Hygienists);

NIOSH: (US National Institute for Occupational Safety and Health);

Safety Data Sheet



OSHA: (US Occupational Safety and Health);
TLV: (Threshold Limit Value)
TWA: (Time Weighted Average);
STEL: (Short Term Exposure Limit);
PEL: (Permissible Exposure Level);
REL: (Recommended Exposure Limit);
PC-STEL: (Permissible concentration-short time exposure limit);
PC-TWA: (Permissible concentration-time weighted average);
IARC: (International Agency for Research on Cancer);
LC50: (Lethal concentration, 50 percent kill);
LD50: (Lethal dose, 50 percent kill);
EC50: (Median effective concentration);
BCF: (Bioconcentration Factor);
BOD: (Biochemical oxygen demand);
IECSC: (Inventory of Existing Chemical Substances in China);
NOEC: (No observed effect concentration);
NTP: (US National Toxicology Program);
RTECS: (Registry of Toxic Effects of Chemical Substances);
TOC: (Total Organic Carbon);
TSCA: (Toxic Substances Control Act of USA);
DSL: (the Domestic Substances List of Canada);
NDSL: (the Non-domestic Substances List of Canada);
IATA: (International Air Transport Association);
IMDG: (International Maritime Dangerous Goods);
TOG: (Recommendations on the TRANSPORT OF DANGEROUS GOODS Model Regulations)

Part Number
PEL01433
PEL01434
PEL01435
PEL01436
PEL01437
PEL01438

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

